

Epson WorkForce AL-M300D



DATASHEET



The WorkForce AL-M300D is one of Epson's most hardworking and reliable A4 monochrome laser printers, thanks to its 100,000-page duty cycle - the highest in its class¹. This model has a compact footprint that suits individual desktop users and comes with a 300-sheet paper capacity as standard - expandable up to 550-sheets.

Aimed at desktop users who are looking for high productivity, this model offers reliable, high-performance printing as well as fast, double-sided printing as standard.

The Workforce AL-M300D also offers consistently fast printing up to 35ppm², with a first-page-out time of 5.5 seconds, as well as high-quality results up to 1,200dpi resolution. Internal memory can also be increased to 1152Mb, to help process all business printing needs.

High-performance is teamed up with reliable printing, thanks to high-yield toners and a heavy-duty output, which provides an excellent return on investment.

The reliability of the WorkForce AL-M300D allows businesses to concentrate on their work without the inconvenience of downtime, enhancing productivity and providing greater peace of mind.

KEY FEATURES

- 100,000-page duty cycle
- 35ppm monochrome printing
- 5.5 second first-page-out time
- Double-sided printing and low CPP
- Increase 300-sheet capacity to 550

Epson WorkForce AL-M300D

PRODUCT SPECIFICATIONS

TECHNOLOGY

| | |
|---------------------|-----------|
| Printing Resolution | 1,200 dpi |
| Toner System | AcuBrite |

PRINT

| | |
|----------------|--|
| Printing Speed | 35 Pages/min Monochrome single-sided, 21 Pages/min Monochrome double-sided |
| First Page Out | Monochrome 6 Seconds |
| Warm Up time | 18 s |
| Max Duty cycle | 100,000 Pages per month |

CONNECTIVITY

| | |
|------------|---------------------------|
| Interfaces | USB 2.0 Type B, IEEE 1284 |
|------------|---------------------------|

PAPER / MEDIA HANDLING

| | |
|----------------------|---|
| Paper Formats | A4, A5, A6, B5, C6 (Envelope), DL (Envelope), LT, HLT, LGL, GLG, GLT, EXE, F4, MON, Custom: Width: 76.2 - 215.9mm / Length: 127 - 355.6mm |
| Duplex | Yes |
| Output Tray Capacity | 150 Sheets |

GENERAL

| | |
|----------------------|---|
| Supply Voltage | AC 220 V - 240 V, 50 Hz - 60 Hz |
| Product dimensions | 393 x 426 x 277 (Width x Depth x Height) |
| Product weight | 12 kg |
| Temperature | Operation 5° C - 32° C, Storage 20° C - 40° C |
| Humidity | Operation 15% - 85%, Storage 15% - 85% |
| Safety Standards | IEC60950-1, EN60950-1, IEC60825-1, EN60825-1 |
| Electrical Standards | Energy Star Compliant |
| EMI Standard | EN55022, EN55024, EN61000-3-3 |

OTHER FEATURES

| | |
|-----------------|--|
| Processor Speed | 600 MHz |
| Memory | 128 MB included, 1152 MB maximum |
| Emulations | PCL5c, PCL6, ESC/P, ESC/P2, ESC/Page, PostScript 3, PDF 1.6, FX, I239X |

OTHER

| | |
|------------|---|
| Warranty | 12 months On site service |
| LCD screen | Type: Monochrome, 22 characters x 5 Lines |

LOGISTICS INFORMATION

| | |
|--------------------------|--------------------|
| SKU | C11CC63011BY |
| Barcode | 8715946527369 |
| Dimensions Single Carton | 530 x 504 x 402 mm |
| Carton Weight | 14.6 Kg |

WHAT'S IN THE BOX

- Initial toner cartridges
- Main unit
- Power cable
- Setup guide
- Software (CD)
- Warranty Documents

SUPPLIES

- AL-M300 Photoconductor Unit 100k C13S051228 (100,000 pages)
- AL-M300 High Capacity Toner Cartridge 10k C13S050689 (10,000 pages)
- AL-M300 Fuser Unit 100k C13S053049 (100,000 pages)
- AL-M300 Return High Capacity Toner Cartridge 10k C13S050691 (10,000 pages)
- AL-M300 Standard Capacity Toner Cartridge 2.7k C13S050690 (2,700 pages)
- 128 MB Additional Memory for C9300N series 7106919
- 256 MB Additional Memory for C9300N series 7106920
- 512 MB Additional Memory for C9300N series 7106921
- 1 GB Additional Memory for C9300N series 7106922
- 3yr CoverPlus Pack 30 LP SESHQ2180
- COVERPLUS-Paket (36 month On-Site-Service)
- Service Pack N° 35
- 3yrs on-site swap
- 3yrs return to base

OPTIONAL ACCESSORIES

- 128 MB Additional Memory for C9300N series 7106919
- 256 MB Additional Memory for C9300N series 7106920

For more information please contact:

Telephone: 0871 222 6702 (UK)+
01 436 7742 (Republic of Ireland)
E-mail: enquiries@epson.co.uk
Chat: etalk.epson-europe.com
Fax: 0871 222 6740

Web: www.epson.co.uk
www.epson.ie

1. - Comparison made against the top 10 workgroup monochrome laser printers (31ppm to 39ppm) sold in Western Europe in Q4 2012 as tracked by IDC. Duty cycle information as published by manufacturers in January 2013. 2 - Determined in accordance with ISO/IEC 24734 showing the average of ESAT / FSOT from the Office Category Test for default simplex /duplex. For more information visit www.epson.eu/testing

+ Calls cost 10p per minute plus network extras.

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners.
Product information is subject to change without prior notice.

EPSON®