

CS72-2MS2

Dual Pole Floor Stand with Back-to-Back Adapter and Two Tilting Mounts

LIST \$1270.00	Color: Black
Weight	131.00 lb. 59.4 kg
Weight Cap. per Head	160 lb. 72.6 kg
Height	72.00 in. 1828.8 mm
Mounting Pattern	200 x 200 (Min) - 800 x 505 (Max) mm
Display Range	37.00 - 63.00 in
Tilt	+12.00°
Pipe Size	72.00 in. 2.8 mm

Downloads at Mounts.com



[Data Sheet](#)



[Bid Specification Document](#)



160 lb.



+72.00



200 x 200 min.



800 x 505 max.



37-63 in

DESCRIPTION

This floor stand combination features a heavy duty base with 72 in. chrome poles and two tilting flat-panel mounts with a back-to-back adapter. The PSD-CS72 allows two CTM-MS2 mounts to be installed anywhere along the vertical poles to achieve the perfect viewing height. The poles also serve as a conduit for cabling. Both CTM-MS2 mounts feature 12° of continuous tilt and built-in lateral shift.

FEATURES

- Carries two flat-panels back-to-back on CTM-MS2 mounts
- Cable management inside poles
- 12° of continuous tilt places flat-panel at the perfect viewing angle
- Base plate can be bolted to floor
- Patented Griplates™ (US Patent number 8,035,757 B2) support the flat-panel and hold the display tight on its mounting brackets



CS72-2MS2

Dual Pole Floor Stand with Back-to-Back Adapter and Two Tilting Mounts

[DOWNLOAD FULL SIZE CAD FILES AND DIMENSIONAL DRAWINGS AT MOUNTS.COM](#)