

Aficio™ SP 5200s/5210SR



Compact print power with 4-in-1 functionality



Where space is at a premium, our compact A4 black & white multifunctional printers, the Aficio™SP 5200s and Aficio™SP 5210SR are ideal. They deliver 4-in-1 printing, copying, colour scanning and faxing* to meet all your document needs. Packed with features usually expected only from larger printers, these units are solid performers. Your busy office or workgroup gets fast, affordable and versatile devices that can expand from desktop models to mighty four-tray, floor-standing powerhouses.



Black & White

These mono devices have a resolution of 1200 x 600dpi which produces quality black & white prints.



45/50 pages per minute (ppm)

Fast printing of up to 45 ppm on the SP 5200s and 50 ppm on the SP 5210SR for single sided printing – quickly handling even the most demanding jobs.



Easy on the environment

These devices are Energy Star compliant and include double-sided (duplex) printing as standard.



Reduce your costs

With its low Total Cost of Ownership (TCO) and high toner yield, these devices are competitively priced printers that small to medium workgroups will quickly find indispensable.



Enhanced security

The SP 5200s and 5210SR offer a full suite of security tools to keep your data safe.



Maximise productivity

The SP 5200s and 5210SR will manage all print jobs with efficiency and speed. With the first-page-out time being a mere 7.5 seconds, these devices won't keep you waiting.

The SP 5200s and SP 5210_{SR} are compact and powerful black & white multifunction laser printers.



We've reduced our carbon footprint, have you?

At Ricoh we are using our expertise in innovation to deliver products that exceed in both performance and environmental sustainability. From green product design and energy efficient office solutions, right down to the collection and recycling of our products; everything we do helps reduce usage of energy and resources, even as we push the limits of technology and productivity.

Machine Recycling Program

We have a free program designed for our customers to recycle their Ricoh machines once they have reached the end of their life. Since launching in 2002, we have successfully recycled over 180 tonnes of Ricoh machines into reusable materials.

Consumables Recycling Program

Ricoh's Consumables Recycling Program – the first established in Australia – will ensure your toner cartridges and other consumable products used and returned will be recycled, achieving a recycling ratio of 98%.



Boost your productivity

Time is money, and our devices waste neither. With a 7.5 second first print speed, you have a copy in less than 10 seconds after machine warm-up and with print speeds of 45 ppm on the SP 5200s and 50 ppm on the SP 5210s^{SR}, you can step up your workflow significantly. Both devices also intuitively detect paper size, handle a wide range of paper weights from 52 – 220 gsm are capable of colour scanning and consistently deliver superb quality reproduction.

Versatile and flexible

The standard configuration offers a single tray with 550-sheet capacity, which is great for either a desktop or a small office environment. Larger workgroups can extend the devices with three further paper trays to a maximum 2300-sheet capacity for different paper types. The SP 5210s^{SR} also includes an inner finisher that can staple for superb professional results.



Reduce your costs

Our range is designed to minimise TCO with many money-saving features to reduce unnecessary paper consumption. Double-sided (duplex) printing, for example, is automatic and cuts down on paper use and costs. Print volumes can also be controlled to prevent unauthorised use or over-use to save on costs and to assist security.

Beyond scanning

Move beyond simple scanning with optional software that can:

- Provide OCR (Optical Character Recognition) capabilities with **ESA TransFormer** – you can scan a hardcopy document into an editable format such as Microsoft Word, Excel, PowerPoint, PDF and more.
- Automate your document scanning and routing. **GlobalScan NX*** makes it easier to incorporate paper documents (such as invoices, purchase orders and bills) into your digital workflows including personalised 'project-based' scanning.

* Version 1.4.4.0 or later



ESA TransFormer
Graphical icons for ease of use



GlobalScan NX
Project based scanning meets the needs of different business documents

Spend time working, not waiting

You can access the copying, scanning or faxing* functions whenever you need them, whether or not other jobs are being printed. Stacks of loose paper documents can be scanned straight to your desktop, email, USB device, SD card or a folder. You'll also have no problem faxing* from your PC and organising, editing and sending files with the onboard scanning tools, while a standard USB print connection saves valuable time and enhances productivity.

* Optional faxing card required



Maximise your workspace and minimise the effort

Space-efficient, our compact A4 multifunction printers don't intrude on valuable workspace in the office. Set-up and operation are simple and straightforward. They also give you a large dimension touch panel and the SP 5210sR also features a tilting function that can be adjusted for ease of use.



Keep confidential documents confidential

You have the choice of a full suite of security tools to keep your data safe. For example, hard copies that won't print until a PIN is entered and you can restrict the use of the multifunctional printers to approved groups or individuals.

- Data encryption and overwrite security (standard on SP 5210sR)
- HDD with Locked Print (SP 5210sR)

Count your carbon

The Ricoh @Remote Intelligent Management System monitors Ricoh networked printers to track a variety of environmental metrics related to how much energy and paper each Ricoh device consumes:

- Learn how many sheets of paper are used from month to month
- Track the percentage of jobs that use duplex or combined printing or copying, which can help cut paper consumption and paper expenses significantly. The data is presented in CO₂, trees & savings
- Analyse how much electricity the SP 5200s/5210sR consume monthly* and track energy saver setting changes to ensure a minimal environmental impact

* Formulas obtained from US Environmental Protection Agency - US Department of Energy



Track trends in energy consumption over time




Translate usage data into reports that detail CO₂ reduction trends



Protect the environment

Sustainability is a strong part of our heritage, touching every part of our company, from manufacturing to distribution, business sites to recycling. Maximising efficiency is a firm commitment, and the Aficio™ SP 5200s/5210sR are Energy Star compliant and offer duplex printing, paperless faxing and all-in-one toners reducing energy usage and costs.

Solutions



Business Solutions Group

When you buy a Ricoh device you gain access to our Business Solutions Group – a dedicated software support centre. Come to us with your challenge and we will identify the solution, source it internally, or develop one specifically to suit your business and integrate into your existing systems.

The Business Solutions Group works closely with customers and application developers to extend the efficiencies of Ricoh's software-enabled copiers and printers in order to meet specific business needs.

Environment




Green Vision

Ricoh's environmental management policy is one of our highest corporate priorities and places us amongst the leaders in environmental management and corporate social responsibility.

Our vision as a global organisation is to reduce our environmental footprint collectively to 1/8th of our year 2000 level by 2050. To achieve this target, we are harnessing our expertise, capability and capacity for technical innovation and combining it with our human and financial resources to execute meaningful initiatives in support of this vision both globally as well as locally.

Service



Responsive Service

At Ricoh we are dedicated to offering our customers the highest level of service and maintenance; that is why our service response times average a mere four hours and you have access to over 500 manufacturer-trained technicians across the country.

To place a service call or to speak with one of our friendly customer service agents, simply phone our national contact centre on 1800 181 002 between 8am – 8pm EST.

Manage your printing

- Secure your information
- Cut costs and increase efficiency
- Centralise frequently used documents
- Improve your customer relationship management with personalised printing

Manage your documents

- Share information quickly and easily through your business
- Save time by scanning directly into applications used by your organisation
- Easily consolidate paper and electronic documents and processes

Manage your devices

- Meter reads and billing
- Usage reporting
- Matching device location to workload
- Efficiency optimisation and cost reduction

Environmentally friendly solutions

Ricoh solutions can help your organisation minimise its impact on the environment and promote sustainability. Here are just some ways it can be done:

- Document management software allows users to store, retrieve, deliver, revise and manage documents without ever printing a hardcopy.
- Rules-based printing can automatically redirect print jobs to the most suitable device to minimise energy consumption, ensure the use of resource saving features, and control access to colour output.
- Managing your devices and obtaining centralised reports helps to establish printing benchmarks, analyse inefficiencies, justify fleet consolidation and device reduction and help change user behaviour.

3 year Printer Warranty

Ricoh's award winning range of colour and black & white laser printers come with a standard three year on-site warranty. This sets a new industry benchmark in Australia.

We are proud of our excellent reputation in customer service. You can feel confident that in the unlikely event that you encounter an issue, Ricoh will quickly and easily rectify it. Our contact centre is available to assist you for the life of the printer's warranty and if an issue cannot be resolved over the phone, one of our qualified service technicians will come to you and fix the printer on site, usually by the next business day.



Believe in a better way

Specifications

Copier

Copy speed:	
SP 5200s:	45cpm
SP 5210SR:	50cpm
Copy resolution:	600 x 600dpi
Multiple copy:	Up to 999
Warm-up time:	20 sec or less
First copy speed:	10 sec or less
Zoom (in 1% step):	
Platen:	25% to 400%
ARDF:	25% to 200%
Memory:	1GB
HDD:	128GB
Paper input capacity:	
Std:	550 sheets
Bypass:	100 sheets
Max:	2300 sheets
ARDF capacity:	50 sheets
Paper output capacity:	
SP 5200s:	Up to 500 sheets
SP 5210SR:	Up to 250 sheets
Paper size:	
Std:	A4 - A6
Bypass:	A4 - A6
Optional tray:	A4 - B6
ARDF:	A4 - A5
Paper weight:	
Std/Opt:	52 - 220gsm
Bypass:	52 - 220gsm
Duplex:	60 - 163gsm
Dimensions (WxDxH):	
SP 5210SR:	460 x 615 x 686mm
SP 5200s:	460 x 510 x 686mm
Weight:	
SP 5210SR:	less than 53kg
SP 5200s:	less than 45kg
Power source:	220-240V, 50/60Hz
Power consumption:	1500W or less
Energy saver:	8W or less

Printer

Print speed:	
SP 5200s:	45ppm
SP 5210SR:	50ppm
Warm-up time:	20 sec or less
First print speed:	7.5 sec or less
Duplex:	Automatic
Printer language:	PCL5e/6, Postscript 3, IPDS (option)
Print resolution:	1200 x 600dpi
Interface:	Ethernet 10BASE-T/100BASE-TX/USB 2.0
Network Protocol:	TCP/IP (IPv4, IPv6), IPX/SPX, Bonjour
Supported environments:	Windows XP Windows Vista Windows Server 2003 Windows Server 2008 Windows 7 MacOS X (v10.2 or later)

Scanner

Scan speed:	over 30ipm
Scan resolution:	600dpi (maximum)
Protocol:	
Network:	TCP/IP
Scan to Email:	POP, SMTP
Scan to folder:	SMB, FTP, NCP

Fax (Option)

Circuit:	PSTN/PBX
Compatibility:	ITU_T, G3
Modem speed:	33.6K - 2400bps with Auto Fallback
Fax resolution:	200 x 100, 200 x 200, 200 x 400, 400 x 400dpi (with optional memory)
Compression method:	MH/MR/MMR/JBIG
Scan speed:	
Platen:	less than 2 sec
ARDF:	less than 1 sec
Scan speed (PPM):	40 spm (A4 SEF)
Memory capacity:	
Std:	approx 320 pages
With optional SAF memory:	approx 2240 pages
Memory backup:	1 hour

Software

Standard:	@Remote Intelligent Management System SmartDeviceMonitor Web Image Monitor
Optional:	GlobalScan NX ESA TransFormer

Other options

550 sheet paper tray¹
550 sheet paper tray with casters¹
IPDS unit
IEEE 802.11a/g interface unit
Gigabit Ethernet Board
Bluetooth Interface Unit
Browser unit
Media link board
Fax option
SAF Memory unit (32MB)

¹ Please consult your local Ricoh supplier for configuration options

RICOH

Ricoh Australia Pty. Ltd. 8 Rodborough Road, Frenchs Forest, NSW 2086. Phone: 1800 181 002 Fax: 02 8977 1100 Web: ricoh.com.au
Ricoh New Zealand Pty. 60 Stanley Street, Parnell, Auckland New Zealand. Phone 0800 2 Ricoh (0800 2 74264) Fax: 09 915 1401 Web: ricoh.co.nz

Product code: B950582

