

3 Bay Aluminum Trayless Hot Swap Mobile Rack Backplane for 3.5in SAS II/SATA III - 6 Gbps HDD

StarTech ID: HSB3SATASBA



The HSB3SATASBA Removable 3-drive backplane lets you quickly install and hot-swap 3.5" drives from the front of your computer, by turning two 5.25" bays into a hot-swappable interface for you to connect up to three 3.5" SATA or SAS hard drives (HDD).

For added versatility, the hard drive bay can interface with SATA I/II/III and SAS I/II hard drives -- an ideal accomodation for enterprise system applications.

For a quick and secure method of installing and removing drives, the backplane features ejection levers and a key-lock design. To help prevent drive failure, the bay provides excellent heat dissipation with a built-in fan, and a vented solid aluminum enclosure.

The HSB3SATASBA is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Imaging - for new system builds or configurations, use the hot swap bay in your master system to quickly copy the Windows OS to multiple blank hard drives
- Add a hot-swap bay to a server or workstation computer that you can use as a removable backup solution
- IT environments where you need to quickly insert/replace hard drives with no external HDD enclosure required

Features

- Solid aluminum construction
- Key lock design
- Built-in fan
- 3 drive bay design
- Installs in two 5.25" drive bays
- Trayless design for hot swap support
- Support for SATA revision I/II/III (1.5/3.0/6.0 Gbps)
- Support for SAS revision I/II (3.0/6.0 Gbps)
- Power and Activity LEDs for each drive

Technical Specifications

Warranty	2 Years
Drive Installation	Removable
Drive Size	3.5in
Drive Type	SAS & SATA
Fan Bearing Type	Sleeve Bearing
Fan(s)	Yes
Fans	1 - 70 mm
Interface	SATA
Key Lock	Yes
Number of Drives	3
Number of internal 3.5 inch bays	3
Drive Connectors	3 - SFF-8482 (29 pin; Data & Power; Internal SAS) Receptacle
Host Connectors	2 - SATA Power (15 pin) Receptacle
Host Connectors	3 - SATA (7 pin; Data) Receptacle

Fan Specifications

Speed: 3000 RPM+10% **Airflow:** 27.60CFM (At zero static pressure) **Noise level:** 26.72dB-A

Max Drive Capacity Currently tested with up to 4TB 7200 RPM hard drives

Maximum Data Transfer Rate 6 Gbit/s

Type and Rate SATA III (6 Gbps)

Color Black

Enclosure Type Aluminum

Product Height 43.3 in [1100 mm]

Product Length 7.6 in [194.1 mm]

Product Weight 42.4 oz [1200 g]

Product Width 5.7 in [145 mm]

LED Indicators 1 - Power LED

LED Indicators 1 - Drive 1 Activity LED

LED Indicators 1 - Drive 2 Activity LED

LED Indicators 1 - Drive 3 Activity LED

Humidity 5%~85% RH

Operating Temperature 0°C to 55°C (23°F to 95°F)

Storage Temperature -20°C to 60°C (-4°F to 122°F)

Shipping (Package) Weight 42.4 oz [1200 g]

Included in Package 1 - 3 SATA HDD Backplane

Included in Package 1 - Installation screw kit

Included in Package 1 - Instruction Manual

Included in Package 2 - Bay Key

Included in Package 3 - 18" SATA Cable

Certifications, Reports and Compatibility

