

Product data sheet

Specifications



APC Smart-UPS X, Line Interactive, 3kVA, Rack/tower convertible 4U, 100V-127V, 6x 5-15R+3x 5-20R+1x L5-30R NEMA, NMC, Extended runtime, Short depth

SMX3000LVNC

Product availability: Stock - Normally stocked in distribution facility

Overview




Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually Ships within 2 Weeks

Main

Main Input Voltage	120 V
Other Input Voltage	100 V 110 V 127 V
Main Output Voltage	120 V
Other Output Voltage	100 V 110 V 127 V
Kw Rating	2700 W
Rated power in VA	2880 VA
Product or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	NEMA L5-30P
output connection type	6 NEMA 5-15R 3 NEMA 5-20R 1 NEMA L5-30R
number of rack unit	4U
Cable length	8 ft (2.4 m)
Number of cables	1
Battery Type	Lead-Acid battery
Provided equipment	CD with software Documentation CD Installation guide Rack mounting hardware Rack Mounting brackets Rack Mounting support rails Removable support feet Smart UPS signalling RS-232 cable USB cable Web/SNMP Management Card
Range of Product	Smart-UPS

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Batteries & Runtime

Run Time	View Runtime Graph 
Efficiency	View Efficiency Graph 
Extendable Run Time	1
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1
Battery life	3...5 year(s)
Replacement battery	APCRBC143 
Battery Charge Power (Watts)	245 W rated

General

Number of power module	2400
Number of power module filled slots	0
Number of power module free slots	0
product web sub-family	Network card pre-installed
Redundant	No

Physical

color	Black
Height	17.008 in (43.2 cm)
Width	7.008 in (17.8 cm)
Depth	19.02 in (48.3 cm)
Net Weight	85.19 lb(US) (38.64 kg)
Mounting Location	Front
Mounting preference	Lower
Mounting Mode	Rack-mounted
Two post mountable	1
USB compatible	Yes

Input

Efficiency at full load	70...153 V
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic distortion	Less than 5%
Maximum configurable power in VA	2880 VA
Max Configurable Power (Watts)	2700 W
Maximum output current	15 A
Transfer Time	2-4 ms 4ms typical : 8ms maximum

Topology	Line Interactive
Waveform Type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	BSMI CSA NOM TÜV VCCI Class A
Equipment protection policy	Lifetime : \$150000

Environmental

Acoustic level	55 dBA
Online Thermal Dissipation	276 Btu/h
Operating altitude	0...10000 ft
Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)
Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %

Communications & Management

Control panel	Multi-function LCD status and control console
Emergency Power Off (EPO)	Yes
Free slots	0
Pre-Installed SmartSlot™ Cards	Network management card 3 with environmental monitoring
Control panel	LED status display with on line : on battery : replace battery and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

Surge Protection and Filtering

Surge energy rating	540 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	731304292654
Returnability	No
Country of origin	PH

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Height	13.0 in (33 cm)
Package 1 Width	24.9 in (63.3 cm)
Package 1 Length	23.07 in (58.6 cm)
Package 1 Weight	105.23 lb(US) (47.73 kg)
Pallet unit layers	2
Pallet layers	4

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery, optional extended warranties available, optional on-site warranties available
-----------------	--

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back Transparency RoHS/REACH

Resource performance

Energy Efficient Product

Take-Back Program Available

Well-being performance

Mercury Free

Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)

California Proposition 65 WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov