

Product data sheet

Specifications



Magnum VS 50 W/SNMP -- 1X60A CB Distribution

DCM00K03S1X60

⚠ Discontinued on: Jun 14, 2022

⚠ Discontinued

Overview

Lead time Usually Ships within 4 Weeks

Main

Main Input Voltage	100 V 120 V 200 V 208 V 230 V
Kw Rating	500 W
Rated power in VA	10 VA
Number of rack unit	3U
Battery Type	External battery system
Provided Equipment	Rack Mounting brackets User Manual

Physical

Color	Black
Height	5.2 in (13.3 cm)
Width	17.2 in (43.8 cm)
Depth	13.0 in (33 cm)
Net Weight	20.9 lb(US) (9.5 kg)
Mounting Mode	Rack-mounted

Input

Input Frequency	47...63 Hz
Number of input connectors	1 Hard Wire 3-wire
Input Power Factor at Full Load	0.99
Maximum Input Current per Phase	5.5 A
DC Overcurrent Protection	Integral fuse in each rectifier
Efficiency at full load	88...264 V

Output

Max Configurable Power (Watts)	2500 W
Grounding Polarity	Positive ground

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Grounding option	Positive ground
Low Voltage Disconnect	Battery circuit
LVD Options	Battery circuit None
Factory Set Voltage	54 V

Conformance

Product Certifications	CE
Standards	EN 55022 Class A EN 55024 EN 61000-3-2 EN 61000-3-3 FCC Part 15 class A UL 1950

Communications & Management

control panel	LED status display of rectifier healthy Network link status LED
Visible Alarms	Current Limit Distribution Failure Input OK Major Alarm Minor Alarm Output OK Over Voltage User Defined
Form C Relay Alarms	Major Alarm Minor Alarm User Defined

Ordering and shipping details

GTIN	731304252344
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.8 in (24.8 cm)
Package 1 Width	22.008 in (55.9 cm)
Package 1 Length	18.5 in (47 cm)
Package 1 Weight	27.500 lb(US) (12.474 kg)

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Under investigation
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.