
EVF-1151S

Single 15” Front Loaded Bass Element

Key Features:

- EVS15SB 15” (381mm) LF Transducer
- 103 dB Sensitivity, 135 dB Maximum SPL
- System Rating: 400W Continuous, (1600W Peak)
- (22) M10 Threaded Suspension Points



General Description:

The Electro-Voice® EVF-1151S is a high power, front-loaded bass element that can be used in a variety of applications where high quality sound reinforcement is required in a lightweight package.

The EVF-1151S utilizes the EVS15SB 15” woofer used FEA optimization for motor, suspension, and electrical design for very low distortion and maximum intelligibility at high SPL levels.

The EVF-1151S features make it a professional loudspeaker for any fixed install application. The trapezoidal enclosure is constructed out of weather resistant birch, and coated with EVCoat™ for maximum protection from the elements. The unique acoustic and rigging design allows for vertical and horizontal clusters to be built using any combination of loudspeakers from the entire EVF & EVH Series, with an assortment of Full-Range, Low Frequency and Subwoofer loudspeakers, it gives you the tools to maximize flexibility of system design, no matter what the application and budget. The innovative input panel provides choice of phoenix style connector (included in all standard models) or the ability to add; a dual NL4 type connector cover plate or gland nut cover plate (for weatherizing applications). An available 70.7/100 Volt transformer kit simply mounts to the input panel for use in distributed systems. All these features give you the flexibility to do a large range of venues with fewer items in inventory and quickly support your customer’s requirements.

⚠ CAUTION ⚠


This EVF Loudspeaker should be suspended overhead only in accordance with the procedures and limitations specified in the *EVF User Manual* and possible manual update notices. This system should be suspended with certified rigging hardware by an authorized rigging professional and in compliance with local, state, and federal overhead suspension ordinances.

Technical Specifications:

Freq. Response[1] (-3 dB):	67 Hz - 95 Hz	
Freq. Range[1] (-10 dB):	46 Hz - 124 Hz	
Rec. Hipass Frequency:	35 Hz	
Axial Sensitivity[1]:	103 dB (1W/1m)	
Max. Calculated SPL[1]:	135 dB	
Horizontal Coverage:	Omnidirectional	
Vertical Coverage:	Omnidirectional	
Power Handling:	400W Continuous, 1600W Peak	
LF Transducer:	EVS15SB, 15 in (381mm) Driver	
Nominal Impedance:	4 Ohms (Passive), 8 Ohms (Biamp)	
Connectors:	(2) 4 Contact 10 AWG Phoenix/ EuroBlock Style Screw Terminal	PI Version - Gland Nut with Included Input Panel Cover
Enclosure Material:	13 Ply Weather Resistant Birch	
Grille:	16 GA Galvanneal, Powdercoat, with Rotatable Logo	PI Version - Stainless Steel with Hydrophobic Cloth
Suspension:	(22) M10 Threaded Points	
Dimensions (H x W x D):	30.26” x 18.50” x 18.37” (768.6mm x 469.8mm x 466.6mm)	
Net Weight:	62.6 lb (28.4 kg)	
Shipping Weight:	72.9 lb (33.1 kg)	


[1] Half Space Measurement.

Dimension Drawings:




End View **Front View** **Side View** **Rear View**

Frequency Response:



Impedance:



Performance Match

PRD000199	EVF-1122S/64, 60° x 40° Coverage
PRD000200	EVF-1122S/66, 60° x 60° Coverage
PRD000201	EVF-1122S/94, 90° x 40° Coverage
PRD000202	EVF-1122S/96, 90° x 60° Coverage
PRD000203	EVF-1122S/99, 90° x 90° Coverage
PRD000204	EVF-1122S/126, 120° x 60° Coverage
PRD000205	EVF-1152S/43, 40° x 30° Coverage
PRD000206	EVF-1152S/64, 60° x 40° Coverage
PRD000207	EVF-1152S/66, 60° x 60° Coverage
PRD000208	EVF-1152S/94, 90° x 40° Coverage
PRD000209	EVF-1152S/96, 90° x 60° Coverage
PRD000210	EVF-1152S/99, 90° x 90° Coverage
PRD000211	EVF-1121S, 12" Bass Element
PRD000213	EVF-1181S, 18" Bass Element
PRD000214	EVH-1152S/64, Coaxial 60° x 40° Coverage
PRD000215	EVH-1152S/66, Coaxial 60° x 60° Coverage
PRD000216	EVH-1152S/94, Coaxial 90° x 40° Coverage
PRD000217	EVH-1152S/96, Coaxial 90° x 60° Coverage
PRD000218	EVH-1152S/99, Coaxial 90° x 90° Coverage
F.01U.076.843	CPS2.9, 120V Power Amplifier, 2 x 900W
F.01U.076.844	CPS2.12, 120V Power Amplifier, 2 x 1200W
D170469	CPS4.5, 120V Power Amplifier, 4 x 500W
D170466	CPS4.10, 120V Power Amplifier, 4 x 1000W

EVF-1151S Part Numbers

PRD000212-001	EVF-1151S-BLK, Black Finish
PRD000212-002	EVF-1151S-WHT, White Finish
PRD000212-003	EVF-1151S-PIB, Black, Weather Resistant
PRD000212-004	EVF-1151S-PIW, White, Weather Resistant
PRD000212-005	EVF-1151S-FGB, Black, Weather Resistant Fiberglass
PRD000212-006	EVF-1151S-FGW, White, Weather Resistant Fiberglass

Accessories

ACC000084-000	CDNL4, Cover Plate, Dual NL4
ACC000085-000	CSG, Cover Plate, Single Gland Nut
ACC000086-000	CDG, Cover Plate, Dual Gland Nut
ACC000087-000	TK-150, 70V Transformer, 150W
ACC000089-001	HRK-1B, Horiz. Rigging Kit, EVF, Black
ACC000089-002	HRK-1W, Horiz. Rigging Kit, EVF, White
ACC000090-001	HRK-2B, Horiz. Rigging Kit, EVF-SUB, Black
ACC000090-002	HRK-2W, Horiz. Rigging Kit, EVF-SUB, White
ACC000092-001	VRK-1B, Vert. Rigging Kit, EVF, Black
ACC000092-002	VRK-1W, Vert. Rigging Kit, EVF, White
ACC000093-001	VRK-2B, Vert. Rigging Kit, EVF-SUB, Black
ACC000093-002	VRK-2W, Vert. Rigging Kit, EVF-SUB, White

Electro-Voice®

12000 Portland Avenue South, Burnsville, MN 55337
Phone: 952/884-4051, Fax: 952/884-0043

www.electrovoice.com

© Bosch Communications Systems 06/2009

Part Number LIT000344000 Rev A

U.S.A. and Canada only. For customer orders, contact Customer Service at:
800/392-3497 Fax: 800/955-6831
Europe, Africa, and Middle East only. For customer orders, contact Customer Service at:
+ 49 9421-706 0 Fax: + 49 9421-706 265
Other Internatonal locations. For customer orders, Contact Customer Service at:
+ 1 952 884-4051 Fax: + 1 952 887-9212
For warranty repair or service information, contact the Service Repair department at:
800/685-2606
For technical assistance, contact Technical Support at: **866/78AUDIO**

Specifications subject to change without notice.