




Novus B8fc

Power-On-Demand Flat Clinch Stapler

The Novus B8fc Stapler uses an innovative hinged handle for stapling up to 50 sheets with 70% less effort. It presses staples flat for 30% more filing space, is designed with steel components for durability, and includes a dual staple guide to reduce jams. This premium German engineered stapler is ideal for quality-conscious office professionals.

Features | Benefits

- Hinged handle can extend for greater leverage and 70% less stapling effort
- Staple legs are pressed flat to provide 30% more binder & filing storage
- Internal steel components for greater performance and durability
- Dual staple guide reduces jams and ensures even clinches
- Use it 2 ways- for stapling and pinning
- Push-button access for pinch-free front loading of staples
- Rubber padding on the base holds the stapler in place
- Gentle pressure allows for easy operation
- German engineered for quality



Staples are pressed flat to save filing and binder space.



Adjustable anvil rotates for more stapling options.



Sheet Capacity



Anti-Blocking System



FC Staple + Pin



Front Loading



25 Year Warranty



German Engineered



Increase leverage and power with the innovative hinged handle to staple up to 50 sheets with 70% less effort.



Steel components offer durability and smooth stapling.



Dual staple guide reduces jams and ensures even clinches.



Flat clinch stapling takes up 30% less filing and binder space.

Novus B8fc Flat Clinch Stapler

Item No.	Color	Capacity	Clinch Type	Throat Depth	Dimensions (length x width x height)	Warranty
020-1673	Black	50 Sheets	Flat	2.625"	7.875" x 1.875" x 3.875"	25 Years

*Staplers tested using the recommended Novus staples. Results will vary if using a lesser staple.

Recommended Staples

Item No.	Staple	Quantity
040-0026	24/6 Super	1000
040-0038	24/8 Super	1000



(800) 995-1379
www.NovusOffice.com