



DataTraveler Vault Privacy 3.0
DataTraveler Vault Privacy 3.0 Anti-Virus
DataTraveler Vault Privacy 3.0 Management-Ready

Data security to safeguard your sensitive business information.

Kingston's DataTraveler® Vault Privacy 3.0 (DTVP 3.0) USB Flash drive provides affordable business-grade security with 256-bit AES hardware-based encryption using XTS block cipher mode, which offers stronger protection than CBC and ECB modes. It protects 100 per cent of stored data and enforces complex password protection with minimum characteristics to prevent unauthorised access. For additional peace of mind, the drive locks down and reformats after 10 intrusion attempts. It also features a read-only access mode to avoid potential malware risks.

DTVP 3.0 is available with optional, easy-to-deploy anti-virus protection from ESET* that protects the drive's content from viruses, spyware, Trojans, worms, rootkits, adware and other Internet-borne threats. The ESET NOD32® anti-virus engine provides instant alerts, requires no installation and comes with a five-year pre-activated licence.

DataTraveler Vault — Privacy is available with a SafeConsole Management option. IT administrators can initially deploy the drive as a standalone secure USB Flash drive and then have the option of adding the drive to a central management solution. The management software is available from Blockmaster and requires a valid licence to enable drive management. It allows administrators to enable specific features, configure password and device policies, remotely reset passwords and activate audit for compliance.

Companies can add DTVP 3.0 to their standards list with confidence since its industry-leading NAND and controller design allow for NAND to be interchanged without requalification and certification of security features. Plus, they no longer have to compromise transfer speeds for safety, due to DTVP 3.0's SuperSpeed USB 3.0 technology and backwards compatibility with USB 2.0.

Companies can also customise the DTVP 3.0 in a variety of ways to meet specific needs and the most frequently requested internal corporate IT requirements, such as serialisation numbering (via standard characters or as 2D and 3D barcodes), number of attempted password entries, minimum password length and customised product identifier (PID) for standard end-point management software (white-listing).

DTVP 3.0 is backed by a five-year warranty, free technical support and legendary Kingston® reliability.



- > Mobile business security
- > 256-bit AES hardware-based encryption
- > Complex password protection
- > Optional anti-virus software protection & optional SafeConsole Management

Features/specs on reverse >>



DataTraveler Vault Privacy 3.0
DataTraveler Vault Privacy 3.0 Anti-Virus
DataTraveler Vault Privacy 3.0 Management-Ready

FEATURES/BENEFITS

- > **Business-grade security** — 100 per cent of stored data is protected by hardware-based, 256-bit Advanced Encryption Standard (AES) in XTS mode
- > **USB 3.0** — latest USB standard guarantees backwards compatibility with USB 2.0
- > **Read-only access mode** — when selected, access files in read-only mode to avoid potential malware risks
- > **Enforced password protection** — complex password is user set with minimum characteristics to prevent unauthorised access
- > **Secure** — drive locks down and reformats after 10 intrusion attempts
- > **Easy to use** — no admin rights or application installation required
- > **Customisable**¹ — preload content, password length, maximum number of password attempts and internal/external serialisation numbering
- > **Co-logo**¹ available
- > **Durable** — resilient protection for data in a waterproof⁵ aluminium casing
- > **TAA compliant**

SPECIFICATIONS

- > **Capacities**² 4GB, 8GB, 16GB, 32GB, 64GB
- > **Speed**³ USB 3.0: 4GB: 80MB/s read, 12MB/s write
 8GB, 16GB: 165MB/s read, 22MB/s write
 32GB: 250MB/s read, 40MB/s write
 64GB: 250MB/s read, 85MB/s write
 USB 2.0: 4GB: 30MB/s read, 12MB/s write
 8GB–64GB: 30MB/s read, 20MB/s write
- > **Dimensions** 77.9mm x 22mm x 12.05mm
- > **Operating temperature** 0°C to 60°C
- > **Storage temperature** -20°C to 85°C
- > **Minimum system requirements**
 - USB 3.0 compliant and 2.0 compatible
 - Two (2) free drive letters required for use⁴
- > **Warranty/support** 5-year warranty with free technical support



FLASH DRIVE STORAGE
 SECURE ENCRYPTED FILES
 USB 3.0
 MEMORY ENCRYPTED FILES
 AES-256
 USB FILES
 FLASH DRIVE
 SECURE
 USB 3.0
 ENCRYPTED



COMPATIBILITY TABLE

DataTraveler Vault Privacy 3.0

	🔒
Windows® 8.1, 8, 7(SP1), Vista®(SP2)	✓
Windows 8.1 RT, 8 RT	
Mac OS X v. 10.6-10.9	✓
Linux v. 2.6 +	✓

DataTraveler Vault Privacy 3.0 Anti-Virus & Management-Ready

	DTVP30AV		DTVP30M-R	
	🔒	Anti-Virus	🔒	Safe-Console*
Windows® 8.1, 8, 7(SP1), Vista®(SP2)	✓	✓	✓	✓
Windows 8.1 RT, 8 RT				
Mac OS X v. 10.6-10.9	✓		✓	✓
Linux v. 2.6 +	✓			

KINGSTON PART NUMBERS

Standard	Anti-virus
DTVP30/4GB	DTVP30AV/4GB
DTVP30/8GB	DTVP30AV/8GB
DTVP30/16GB	DTVP30AV/16GB
DTVP30/32GB	DTVP30AV/32GB
DTVP30/64GB	DTVP30AV/64GB

Management-Ready
 DTVP30M-R/4GB
 DTVP30M-R/8GB
 DTVP30M-R/16GB
 DTVP30M-R/32GB
 DTVP30M-R/64GB

*SafeConsole Secure USB Management Server Version 4.7.3+

1 Minimum quantity required. Performed at the factory.

2 Some of the listed capacity on a Flash storage device is used for formatting and other functions and is thus not available for data storage. As such, the actual available capacity for data storage is less than what is listed on the products. For more information, go to Kingston's Flash Memory Guide at kingston.com/flashguide.

3 Speed may vary due to hardware, software and usage.

4 First free drive letters after physical devices such as system partition, optical drives etc.

5 Up to 4 ft.; conforms to IEC 60529 IPX8. Product must be clean and dry before use.

THIS DOCUMENT SUBJECT TO CHANGE WITHOUT NOTICE.

©2014 Kingston Technology Europe Co LLP and Kingston Digital Europe Co LLP, Kingston Court, Brooklands Close, Sunbury-on-Thames, Middlesex, TW16 7EP, England. Tel: +44 (0) 1932 738888 Fax: +44 (0) 1932 785469. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. MKD-272.2EN

