



VP-470

3G HD-SDI ProScale™ Digital Scaler

| 3G HD-SDI - BNC



The VP-470 is a high-performance digital scaler for 3G HD-SDI signals. It up- or down-scales the incoming SDI signal to resolutions up to 1080p and routes it to two identical SDI outputs

FEATURES

Max. Data Rate - 3Gbps

HDTV Compatible

Multi-Standard Operation - SDI (SMPTE 259M), HD-SDI (SMPTE 292M) and 3G HD-SDI (SMPTE 424M)

Looping Input - Reclocked and equalized

Selectable Output Size & Aspect Ratio - Full, panscan, letterbox, underscan and overscan settings

Built-In ProcAmp Features - Color hue, sharpness, contrast and brightness

Freeze Button

Non-Volatile Memory - Saves final settings

USB Port - For firmware upgrade

Controls - Front panel buttons with OSD (on screen display)

Compact MegaTOOLS™ - 2 units can be rack mounted side-by-side in a 1U rack space with the recommended rack adapter



KRAMER

TECHNICAL SPECIFICATIONS

| | |
|-----------------------|---|
| INPUT: | 1 SD/HD/3G HD-SDI with reclocked and equalized loop on a BNC connector |
| OUTPUTS: | 2 SD/HD/3G HD-SDI on BNC connectors |
| INPUT RESOLUTIONS: | SDTV: 480i @59.94Hz, 576i @50Hz; HDTV: 720p @50/59.94/60Hz, 1080i @50/59.94/60Hz, 1080p @23.98/24/25/29.97/30Hz, 1080sF @23.98/24/25/29.97/30Hz; 3G: 1080p @50/59.94/60. 1080sF @23.98/24 inputs don't support 480i/576i output for 1080sF25/29.97/30 inputs, the OSD info. shows 1080i50/59.94/60 |
| OUTPUT RESOLUTIONS : | SDTV: 480i @59Hz, 576i @50Hz; HDTV: 720p @50/59.94/60Hz, 1080i @50/59.94/60Hz, 1080p @23.98/24/25/29.97/30Hz; 3G: 1080p @50/59.94/60Hz |
| OUTPUT SIZE: | Full, panscan, letterbox, underscan, overscan |
| PROCESSING DELAY: | 30ms |
| CONTROLS: | Menu, OSD, Reset to 1080p or 720p and Freeze front panel buttons |
| POWER CONSUMPTION: | 5V DC, 440mA |
| INCLUDED ACCESSORIES: | Power supply |
| Product Dimensions | 21.46cm x 16.30cm x 4.36cm (8.45" x 6.42" x 1.72") W, D, H |
| Product Weight | 0.4kg (1.0lbs) approx |
| Shipping Dimensions | 35.10cm x 21.20cm x 7.20cm (13.82" x 8.35" x 2.83") W, D, H |
| Shipping Weight | 0.9kg (2.0lbs) approx |

