

## Swingline® Stack-and-Shred™ 100M Auto Feed Shredder, Micro-Cut, 100 Sheets, 1-2 Users

Spend less time shredding.

1758571

### Product Description

The Swingline® Stack-and-Shred™ shredder with anti-jam from America's #1 Selling Brand in Auto Feed Shredders works without your supervision; just stack, shut and you're done. Stack up to 100 sheets in the auto feed tray and let the micro-cut 100M automatically shred for you. Manual feed shreds up to 6 sheets including glossy, folded or crumpled paper.

### Features

- Spend less time shredding versus a traditional shredder - just stack, shut and you're done
- Auto shreds documents, paper clips, staples. Credit cards must be manually inserted into rollers in auto feed chamber.
- 2 year warranty on machine, 10 years on cutters
- 17.5"L x 12"W x 16.25"H
- Micro-cut shredder meets high security needs (Level P-5)
- Shred up to 100 sheets with automatic shredding and up to 6 sheets at a time during manual feed shredding.
- 7-gallon pull-out waste bin with bin full indicator
- Runs consecutively for 15 minutes on with 10 minutes off to ensure longevity of the motor
- Ultra quiet (=60dB) to ensure minimal disruption in the office environment
- Intelligent Auto+® Jam Clearance reverses and re-feeds stuck papers
- Intelligent Self-Cleaning Cutters® automatically remove shreds that cause build-up and lead to jams
- Intelligent Power Save® auto shut down with automatic wake-up conserves energy

### Specifications

- **Bin Capacity (gallons)** 7
- **Cut Type** Micro-cut
- **Detailed Color** Black
- **Entry Width** 9"
- **Jam Free Type** Auto+® Jam Clearance
- **Number of Shreds Per Page** 2000 or more
- **Period of Warranty** 2 years for machine, 10 years for cutters
- **Run Time/Cool Down Time** 15/10

### Other information

- **Dimensions** 16.25"H x 12"W x 17.5"D

### Each information

Depth	19.63"
Width	14.5"
Height	19.63"
Gross weight	27.20lbs
UPC#	033816585713
Unit quantity	1

### Case information

Depth	19.63"
Width	14.5"
Height	19.63"
Gross weight	27.20lbs
UPC#	033816585713
Unit quantity	1

### Shipping Information

Country of origin	CN
Minimum Order Quantity	1
Lowest possible unit	Each

### General information

Color	Unknown
Layer/Pallet	2
Cases/Layer	6