



# Novus B54

## Professional Heavy Duty Long Arm Stapler

The Novus B54 Heavy Duty Long Arm stapler is designed for high-volume stapling of up to 170 sheets with minimal effort. It features an anti-blocking system to prevent jams, a 9.75" throat depth for stapling booklets, and a bypass system that prevents staple overlap when stapling fewer sheets. This stapler is German engineered and works best when paired with Novus 23-gauge premium staples.

### Features | Benefits

- Anti Blocking System prevents staple jams
- Long handle with 2-point leverage provides more power with less effort
- 9.75" throat depth for stapling across documents & binding booklets
- Rotating anvil for bypass or parallel stapling
- Dual staple guide provides even stapling pressure for superior performance
- Heavy-duty base provides support and durability for extended use
- Adjustable depth guide for repetitive stapling
- Convenient front-loading staple compartment
- Bypass system prevents overlap of staple legs when stapling smaller quantities
- German engineered for quality and durability



*Anti-Blocking System prevents jams and the hassle of stuck documents.*



*Adjustable depth guide keeps your clinches in the right spot with every stack.*



Sheet Capacity



Anti-Blocking System



Bypass System




Front Loading



25 Year Warranty



German Engineered



The 9.75" throat depth allows for saddle stitching booklets and stapling large documents.



The B54 is designed to easily staple large stacks of documents with minimal effort.



The long handle features 2-points of leverage for more power with less effort.



The rotating anvil offers the choice of bypass or parallel stapling depending on your stack size.

## Novus B54 Heavy Duty Long Arm Stapler

Item No.	Capacity	Bypass	Throat Depth	Dimensions (length x width x height)	Warranty
023-0038	20-170 Sheets	•	9.75"	17.75" x 4" x 11.25"	25 Years

## Recommended Staples

Item No.	Staple	Quantity	Item No.	Staple	Quantity
042-0040	23/8 Super	1000	042-0044	23/15 Super	1000
042-0531	23/10 Super	1000	042-0045	23/17 Super	1000
042-0533	23/13 Super	1000	042-0240	23/20 Super	1000

\*Staplers tested using the recommended Novus staples. Results will vary if using a lesser staple.



(800) 995-1379  
www.NovusOffice.com