



# INDIVIDUAL LOUDSPEAKERS

## 30C25Z450T



The 30C25Z80T is a 3" O.D., square frame loudspeaker with a 2.35 oz. magnet, 8 Ohm impedance and a moisture resistant cone.

## Additional Specs

### APPLICATION

Intended Use:	Indoor and protected outdoor environment
Program Material:	Signal tones, voice, and music

### AUDIO SPECIFICATIONS

Average Sensitivity:	87dB SPL, 1W/ 1M
Loudspeaker Power Rating:	4W RMS, EIA 426A Standard
Maximum Power Rating:	5W @ 45 Ohms
Calculated Output:	93dB SPL, 5W/ 1M
Magnet Type & Weight:	BeFe Ceramic, 2.35 oz. Nominal
Frequency Response:	300Hz - 10kHz, EIA 426A Standard

Nominal Coverage Angle:

90° Included Angle, -6dB/2kHz, Half Space

---

Audio Connection:

0.205 Spade Lugs

---

## Technical Documents

---



30C25Z45OT Drawing File

---



Quam Design Guide

---