Product data sheet
Characteristics

ACECFR40200SE7
EcoBreeze Frame 40' (12m) 480/3/60 VAC Schneider Electric 7 Modules Installed

Purchase

Purchase	ACECFR40200SE7

Overview

Model Name	EcoBreeze Frame 40' (12m) 480/3/60 VAC Schneider Electric 7 Modules Installed
Includes	Door key,Operations and maintenance manual,User Manual
Standard Lead Time	Special Order - Call for Quoted Lead Times
Product Distribution	Canada,Mexico,United States

Input

Input Frequency	60 Hz

Communications & Management

Control panel	Multi-function LCD status and control console

Physical

Maximum Height	3048 mm
Maximum Width	2438 mm
Maximum Depth	12192 mm
Net Length	12.2 meters
Net Weight	13040.91 kg
Shipping Weight	13177.27 kg
Shipping Height	3048 mm
Shipping Width	2438 mm
Shipping Depth	12192 mm
Color	Grey

Conformance

Regulatory Approvals	ETL
Standard Warranty	1 year (parts only)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.