



3/6/7 dBi Outdoor Tri-Band Omni Antenna Kit

TEW-AO57 (v2.0R)

- · Pair of outdoor omni-directional tri-band antennas
- 2.4GHz: 3 dBi
- 5GHz: 6.2 dBi
- 6GHz: 7 dBi
- N-Type male connector
- Compatible with 802.11be/ax/ac/n/g/b/a routers and access points with N-Type female connectors
- NDAA / TAA compliant (U.S. and Canada only)

TRENDnet's 3/6/7 dBi Outdoor Tri-Band Omni Antenna Kit, model TEW-AO57, comes with a pair of high-performance outdoor antennas supporting 2.4GHz, 5GHz, and 6GHz radio transmissions for both WiFi 7 and legacy bands. Provide reliable, blanket wireless coverage with these outdoor omni-directional antennas. The outdoor antennas have N-Type male connectors, and works with 802.11be/ax/ac/n/g/b/a routers and access points with N-Type female connectors.





Tri-Band Support Supports the latest 6GHz band for WiFi 7 and legacy bands of 2.4GHz and 5GHz.



N-Type Connector Compatible with routers and access points with N-Type female connectors.

Outdoor Ready Built for outdoor installations with an operating temperature range of -40° - 70° C (-40° - 158° F).

FEATURES



Antenna Kit

Comes with a pair of outdoor omnidirectional tri-band antennas



Tri-Band Support (2.4GHz + 5GHz + 6GHz)

Compatible with 802.11be/ax/ac/n/ g/b/a routers and access points



Outdoor

Durable antenna construction for extreme outdoor conditions with an operating temperature range of -40° - 70° C (-40° - 158° F)



Antenna Gain

2.4GHz peak gain: 3dBi, 5GHz peak gain: 6.2dBi, 6GHz peak gain: 7dBi



Omni-Directional


Omni-directional antennas for reliable, blanket wireless coverage



N-Type Connector

N-Type male connectors on the antennas are compatible with routers and access points with N-Type female connectors





Polarization 6 GHz

TRENDNET

SPECIFICATIONS

Antenna

 Omni-directional tri-band (2.4GHz + 5GHz + 6GHz)

Frequency

- 2.4GHz: 2.4 5GHz
- 5GHz: 5.15 5.85GHz
- 6GHz: 5.92 7.12GHz

Peak Gain

- 2.4GHz: 3 dBi max
- 5GHz: 6.2 dBi max
- 6GHz: 6.9 dBi max

Polarization

· Linear, vertical

Connector Type

N-Type male

Half-Power Beam Width (HPBW)

- Horizontal: 360°
- Vertical: 45°

Voltage Standing Wave Radio (VSWR)

• 2.0 max: 1

Nominal Input Impedance

50 Ohms

Power Handling

2 Watts

Operating Temperature • -40° - 70° C (-40° - 158° F)

Operating Humidity

Max 95% non-condensing

Compatibility

• Compatible with 802.11be/ax/ac/n/g/b/a routers and access points with N-type female connectors

Dimensions

• Individual antenna: 20 x 178mm (0.78 x 7 in.)

Weight

- Individual antenna: 58g (2.04 oz.)
- Both antennas: 116g (4.09 oz.)

Warranty

3 year

Package Contents

- TEW-AO57 (2 x antennas)
- Quick Installation Guide

*Effective wireless coverage may vary depending on the wireless device's output power, antenna gain, antenna alignment, receiving sensitivity, and radio interference. Additionally environmental factors such as weather conditions, physical obstacles, and other considerations may affect performance. For optimal results, we recommended consulting a professional installer for site survey, safety precautions, and proper installation.

All references to speed are for comparison purposes only. Product specifications, size, and shape are subject to change without notice, and actual product appearance may differ from that depicted herein.

20675 Manhattan Place • Torrance • CA 90501 • USA • T: 1-888-326-6061 • sales@trendnet.com • www.TRENDnet.com

TRENDnet is a registered trademark. Other Brands and product names are trademarks of their respective holders. Information provided in this document pertain to TRENDnet products and is subject to change at any time, without notice. For the most recent product information please visit http://www.trendnet.com. Copyright © TRENDnet. All Rights Reserved.