

Slim USB 3.0 to VGA External Video Card Multi Monitor Adapter – 1920x1200 / 1080p

StarTech ID: USB32VGAES



The USB32VGAES Slim USB 3.0 to VGA Adapter turns a USB 3.0 port into a VGA output port with 1920x1200/1080p video support. The adapter minimizes clutter with a slim design that seamlessly blends with your video cable – an ideal space-saving solution for multi-monitor applications on Ultrabook Wednesday, December 04, 2013 6:40:40 AMrade;, laptop, or desktop computers.

Functioning as an external graphics card, this USB to VGA adapter provides a convenient way to add multi-monitor capability to a USB 3.0-enabled desktop or laptop computer (optimal performance from USB 3.0, backward compatible with USB 2.0).

To save space while travelling, this ultra-portable USB to VGA adapter features a lightweight, small footprint design that fits easily in a laptop carrying bag

Leveraging the high-bandwidth (5 Gbps) SuperSpeed USB 3.0 interface, the adapter delivers smooth, high-definition content to your VGA display/projector. The adapter can be used to mirror your primary desktop, showing the same image on each display, or to extend your desktop to double your workspace and increase your productivity.

The USB32VGAES is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Recommended System Requirements:

CPU: Quad Core 2.4GHz or Higher (i5 recommended)

RAM: 4GB or higher

USB 3.0 port (Backwards compatible with USB 2.0)

Applications

- Add a secondary VGA display with full HD capability
- View large or multiple spreadsheets across several displays
- Use the adapter to connect your PC to your VGA-equipped projector or display for viewing family pictures and movies
- Add multi-monitor capability to a single computer, to create engaging multimedia presentations
- Have reference material on one display and a working document copy on the other
- Run multiple applications on different screens - check your email on one display and search the web on the other

Features

- Slim lightweight design
- Ultra-portable
- SuperSpeed USB 3.0 (5 Gbps)
- Supports High-Definition video resolutions up to 1920x1200/1080p
- USB-powered - No external power adapter required
- Supports Mirrored, Extended or Primary display configurations
- Supports display rotation

Technical Specifications

Warranty	2 Years
Chipset ID	T5-302/MCT
Ports	1
USB Pass-Through	No
Connector A	1 - USB 3.0 A (9 pin; SuperSpeed) Male
Connector B	VGA (15 pin; High Density D-Sub) Female
Maximum Analog Resolutions	1920x1200/1080p
Supported Resolutions	Widescreen(16/32 bit): 1920x1200, 1920x1080, 1680x1050, 1600x900, 1440x900, 1360x768, 1280x800, 1280x768, 1280x720 Standard(16/32 bit): 1600x1200, 1400x1050, 1280x1024, 1280x960, 1152x864, 1024x768, 800x600
Wide Screen Supported	Yes
Microsoft WHQL Certified	Yes
OS Compatibility	Windows® 8 / 8.1 (32/64) Windows 7(32/64) Windows Vista (32/64) Windows XP (32/64)
Cable Length	2.4 in [62 mm]
Color	Black
Enclosure Type	Plastic
Product Height	0.5 in [12 mm]
Product Length	2.4 in [62 mm]
Product Weight	0.1 oz [2.4 g]
Product Width	1 in [25 mm]
Power Adapter Included	USB-Powered
Humidity	< 85% non-condensing
Operating Temperature	0°C to 50°C (32°F to 122°F)
Storage Temperature	-10°C to 75°C (14°F to 167°F)
Note	Connect a maximum of five USB32VGAES adapters on a single PC - See manual for system requirements
System and Cable Requirements	CPU: i3 Dual core 2.8GHz RAM: 2GB or higher Full HD Video: CPU: Quad Core 2.4GHz or Higher (i5 recommended) RAM: 4GB or higher
Shipping (Package) Weight	0 lb [0 kg]

- Included in Package 1 - Slim USB 3.0 Video Adapter
- Included in Package 1 - Driver CD
- Included in Package 1 - Instruction Manual

Certifications, Reports and Compatibility

