Quam system 12/25RSRJ

SYSTEM 12/25RSRJ is a complete, shallow depth, lightweight, 2' x 2' ceiling tile replacement loudspeaker system consisting of an 8" O.D. loudspeaker with a 5 oz. magnet, a 4W, 25V rotary select transformer, and a dual RJ45 input connection jack. The molded fiber enclosure is 1,283 CID. The SYSTEM 12/25RSRJ has a powder coated steel baffle with standard perforation and four (4) seismic tie-off points. No assembly required.



APPLICATION Intended Use: Indoor environment

> **Program Material:** Signal tones, voice, and music

Installation: Mounted parallel to floor plane in a 24" wide suspended ceiling tile grid

Average Sensitivity: 92dB SPL, 1W/1M AUDIO

12W RMS, EIA 426A Standard **Loudspeaker Power Rating: PERFORMANCE**

> **Maximum Power Rating:** 15W @ 8 Ohms

Calculated Output: 98dB SPL, 4W/1M

BeFe Ceramic, 5 oz. Nominal Magnet Type & Weight: **Frequency Response:** 65Hz - 17kHz, EIA 426A Standard

Nominal Coverage Angle: 100° Included Angle, -6dB/2kHz, Half Space

Audio Connection: Integrated dual RJ45 Sockets (audio input to pins 1 and 2)

Dimension: $3 \frac{1}{2}$ " (H) x $23 \frac{13}{16}$ " (W) x $23 \frac{13}{16}$ " (D) COMPONENT

Weight: 6.25 lbs. Loudspeaker Model: 8C5PAX

Loudspeaker Specs: 8" O.D. loudspeaker, 5 oz. magnet

Transformer: 4W, 25V, rotary select with 5 taps (0.25W, 0.50W, 1W, 2W, 4W)

Integral Enclosure: 1,283 CID molded fiber

Grille: Standard perforated steel with four (4) seismic tie-off points

Finish: White powder coat finish









