


EH-TW570

DATASHEET



Epson's brightest home cinema product, this great value 3,000 lumen projector uses 3LCD technology for sharp, smooth images in 2D and 3D.

Boasting 3,000 lumens brightness and colourful 3D images, this HD-ready resolution projector is a great value way of creating immersive big screen images at home. Exceptional picture quality is assured by 3LCD technology, while both lag-free gaming¹ and 2D-to-3D conversion make this an exciting introduction to home cinema.

Bright 2D & 3D images

At 3,000 lumens the EH-TW570 is Epson's brightest home cinema projector. Producing exceptional images whatever the ambient light levels, the EH-TW570 projects in both 2D and 3D, even converting 2D video into 3D. Choose from four colour modes (Living room, Dynamic, Theatre and Game) and two colour modes while watching in 3D, with three brightness levels available.

Improved contrast

An improved contrast ratio of 15,000:1 allows the EH-TW570 to deliver sharp images, while 3LCD technology ensures a equally high White and Colour Light output and no rainbow effect for beautiful colour images.

Easy to use

Vertical and horizontal keystone correction and 1.2x zoom make it simple to position the projector where you want it. Integrated stereo 2W speakers lessen the need for a separate sound system, while audio outputs on the EH-TW570 bring more versatility. It also benefits from a long lamp life of 5,000 hours in normal mode, and 6,000 hours in eco mode.

Great gaming

Big screen gaming has never been so responsive; a special game mode called Turbo¹ reduces lag time so you'll never miss that shot.

Greater sharing

Epson's iProjection app² allows touchscreen devices to easily share content, while a QR code displayed by the projector makes connecting devices even easier. HDMI-MHL connectivity makes it easy to directly connect smart devices.

KEY FEATURES

- **HD-ready images**
720p high definition resolution
- **2D to 3D conversion**
3D depth adjustment
- **Reduced lag**
Turbo mode for gaming
- **Integrated sound**
2W speakers built-in
- **Less hassle**
Lamp lasts 5,000-6,000 hours



EPSON
WORLD LEADER
IN PROJECTORS

Source: Futuresource Consulting Ltd.

EPSON
EXCEED YOUR VISION

PRODUCT SPECIFICATIONS

TECHNOLOGY

Projection System	3LCD Technology, RGB liquid crystal shutter
LCD Panel	0.59 inch with MLA (D8)

IMAGE

Colour Light Output	3,000 lumen-2,100 lumen (economy)
White Light Output	3,000 lumen - 2,100 lumen (economy)
Resolution	WXGA, 1280 x 800, 16:10
Contrast Ratio	15,000 : 1
Lamp	200 W, 5,000 h durability, 6,000 h durability (economy mode)
Keystone Correction	Auto vertical: ± 30 °, Manual horizontal ± 30 °

OPTICAL

Projection Ratio	1.30 - 1.56:1
Zoom	Manual, Factor: 1 - 1.2
Projection Size	33 inches - 320 inches
Projection Distance Wide	2.8 m (100 inch screen)
Projection Distance Tele	3.4 m (100 inch screen)
Projection Distance Wide/Tele	1.68 m - 2.02 m (60 inch screen)
Focal Distance	16.9 mm - 20.28 mm
Focus	Manual

CONNECTIVITY

Interfaces	USB 2.0 Type A, USB 2.0 Type B, VGA in, HDMI 1.4, S-Video in, MHL, Stereo mini jack audio out, Cinch audio in
------------	---

OTHER

Warranty	24 months Carry in, Lamp: 36 months or 3,000 h Optional warranty extension available
----------	---

LOGISTICS INFORMATION

SKU	V11H664040
EAN code	8715946542584
Multiple Order Quantity	1 Units
Country of Origin	China
Pallet Size Euro	78 Units

EH-TW570

WHAT'S IN THE BOX

- Main unit
- Power cable
- User's Manual Set
- Remote control incl. batteries

OPTIONAL ACCESSORIES

- Lamp - ELPLP78
V13H010L78
- Air Filter - ELPAF32
V13H134A32
- 3D Glasses (Active, RF) - ELPGS03
V12H548001
- Soft Carry Case - ELPKS63
V12H001K63
- Ceiling Mount (White) - ELPMB23
V12H003B23
- Ceiling Pipe (450mm) - ELPFP13
V12H003P13
- Ceiling Pipe (700mm) - ELPFP14
V12H003P14
- Wireless LAN Adapter (b/g/n) - ELPAP07
V12H418P13
- Quick Wireless Connect USB key - ELPAP09
V12H005M09



* Warranty offers are not available for all countries. Please contact your local Epson representative.

For further information please contact your local Epson office or visit www.epson-europe.com
 Austria 01 253 49 78 333 Belgium +32 (0)2 792 04 47 Czech 800/142 052 Denmark 44 50 85 85 Finland 0201 552 091 France 09 74 75 04 04
 (Cost of local call, operator charges may apply) Germany +49 (0) 2159/92 79 500 Greece 210-8099499 Hungary 06800 147 83
 Ireland 01 436 7742
 Italy 02-660321 10 (0,12 /min) Luxembourg +352 27860692 Middle East +971 4 8872172 Netherlands +31 (0)20 708 5099 Norway +47 67 11 37 00 Poland 0-0-800 4911299 (0,16 zł/min) Portugal 707 222 111 Russia (095) 777-03-55 Slovakia 0850 111 429
 South Africa (+2711) 465-9621
 Spain 93 582 15 00 Sweden 0771-400135 (Mobilisamtal – 0,99 kr/min, Lokala samtal – 0,30 kr/min, Utlandssamtal – 0,89 kr/min) Switzerland 022 592 7923 Turkey (0212) 3360303 United Kingdom 0871 222 6702

1. – Turbo mode is only compatible with the Game Mode colour setting. Horizontal keystone corrections are not possible when using Turbo mode.

2. – iProjection App available on Android and iOS devices. Network projection function is not capable of video transmission

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners.
 Product information is subject to change without prior notice.