



## ezFrame 2 Series Product Brochure

The ezFrame 2 Series uses both front and rear materials within a velveteen coated frame. A new design feature for the material is a rubber-edge border that makes installation a lot easier and a lot less time consuming.



# ezFrame 2 Series



The ezFrame 2 Series uses both front and rear materials within a velveteen coated frame. A new design feature for the material is a rubber-edge border that makes installation a lot easier.



## Screen Material:

- Award Winning CineWhite® 1.1 Gain front projection material with black backing and full tension uniformity across entire viewing surface
- Outstanding picture quality at any viewing angle with no compromise in resolution or brightness
- Active 3D, 4K Ultra HD, and HDR Ready
- Compatible with Ultra/Short and Standard throw projectors (**Only on CineWhite® and CineGrey Models**)
- Available in the following range of diagonal sizes:
  - 84" - 200" in 16:9 format
  - 109" - 144" in 16:10 format

## Design and Installation:

- 2.4" width frame and is velvet coated
- Elegant velvet covered frame absorbs projector overshoot and increases picture contrast
- Assembles in minutes and includes installation hardware
- Split-frame design facilitates lower shipping costs without sacrificing quality
- Wall brackets allow screen to slide horizontally for properly centered installation
- Installation kit includes: Wood screws & anchors, Wall Brackets, Screwdriver, Mallet

## Quality and Reliability:

- 2-year Parts & Labor manufacturer's warranty
- 3-year warranty offered through ENR-G program (Education, Non-Profit, Religious and Government)



## ezFrame 2 Series

Model	Screen Diag. & Aspect Ratio	View Height - Chord (in)	View Width - Chord (in)	View Height (cm)	View Width (cm)	N.W. (lbs.)	G.W. (lbs.)	N.W. (kgs)	G.W. (Kgs)	Packaging Dimensions (LxHxW)	Gain	Screen Material
R100H2	100" (16:9)	49.0	87.0	124.0	221.0	24.9	34.3	11.3	15.6	61.42"x6.7"x11.81"	1.0	CineGrey
R120H2	120" (16:9)	59.0	104.7	167.6	297.2	29.3	39.7	13.3	18.0	69.7"x6.7"x11.8"	1.0	CineGrey
R135H2	135" (16:9)	66.2	117.7	168.1	299.0	31.4	42.0	14.3	19.1	78.15"x5.7"x15.8"	1.0	CineGrey
R84WH2	84" (16:9)	41.2	73.3	105.2	186.2	21.1	29.2	9.6	13.3	52.8"x6.7"x11.81"	1.1	CineWhite®
R100WH2	100" (16:9)	49.0	87.0	124.5	221.0	24.3	33.6	11.0	15.2	51.42"x6.7"x11.81"	1.1	CineWhite®
R106WH2	106" (16:9)	52.0	92.2	132.1	234.2	25.5	35.2	11.6	16.0	63.5"x6.7"x11.8"	1.1	CineWhite®
R110WH2	110" (16:9)	54.0	96.0	137.2	243.8	26.6	37.0	12.1	16.8	65.51"x6.7"x11.81"	1.1	CineWhite®
R120WH2	120" (16:9)	59.0	104.7	167.6	297.2	28.4	38.4	12.9	17.4	69.7"x6.7"x11.8"	1.1	CineWhite®
R135WH2	135" (16:9)	66.2	117.7	168.1	299.0	33.4	43.9	15.1	19.9	78.2"x6.5"x15.2"	1.1	CineWhite®
R150WH2	150" (16:9)	73.6	130.7	186.9	332.0	36.6	48.5	16.6	22.0	85.6"x6.5"x15.2"	1.1	CineWhite®
R165WH2	165" (16:9)	81.0	144.0	205.7	365.8	39.7	51.4	18.0	23.3	92.9"x5.7"x15.75"	1.1	CineWhite®
R180WH2	180" (16:9)	88.3	156.9	224.3	398.5	43.1	57.8	19.6	26.2	100.2"x7.7"x15.7"	1.1	CineWhite®
R200WH2	200" (16:9)	98.0	174.0	248.9	442.0	48.4	63.9	21.9	29.0	110.04"x7.9"x15.75"	1.1	CineWhite®
R109WX2	109" (16:10)	57.5	92.0	146.1	233.7	26.0	36.4	11.8	16.5	69.4"x6.7"x11.8"	1.1	CineWhite®
R114WX2	114" (16:10)	60.0	96.0	152.4	243.8	27.6	39.1	12.5	17.7	72.0"x6.7"x11.8"	1.1	CineWhite®
R125WX2	125" (16:10)	66.2	105.9	168.1	269.0	30.6	40.3	13.9	18.3	77.17"x5.51"x15.8"	1.1	CineWhite®
R144WX2	144" (16:10)	76.3	122.0	193.8	309.9	36.0	46.1	16.3	20.9	88.4"x6.7"x15.2"	1.1	CineWhite®
R100RH2	100" (16:9)	48.8	87.0	124.0	221.0	23.0	32.4	10.4	14.7	61.4"x6.7"x11.8"	2.2	WraithVeil
R120RH2	120" (16:9)	58.7	104.7	167.6	297.2	27.6	36.4	12.5	16.5	69.7"x6.7"x13.6"	2.2	WraithVeil
R135RH2	135" (16:9)	66.2	117.7	168.1	299.0	30.7	41.5	13.9	18.8	78.2"x6.7"x15.2"	2.2	WraithVeil

**ezFrame 2 Dimensions Table**

Model	Screen Diag. & Aspect Ratio	Overall Width (A)	View Width (A1)	Overall Height (B)	View Height (B1)	Frame Width (C)	Frame Depth(D)
R100H2	100"(16:9)	2329	2210	1359	1240	61	41
R120H2	120"(16:9)	2779	2659	1610	1491	61	41
R135H2	135"(16:9)	3109	2990	1801	1679	61	41
R84WH2	84"(16:9)	1981	1862	1171	1052	61	41
R100WH2	100"(16:9)	2329	2210	1359	1240	61	41
R106WH2	106"(16:9)	2461	2342	1440	1321	61	41
R110WH2	110"(16:9)	2555	2436	1491	1369	61	41
R120WH2	120"(16:9)	2779	2659	1610	1491	61	41
R135WH2	135"(16:9)	3109	2990	1801	1679	61	41
R150WH2	150"(16:9)	3442	3320	1991	1869	61	41
R165WH2	165"(16:9)	3772	3653	2174	2055	61	41
R180WH2	180"(16:9)	4105	3985	2360	2240	61	41
R200WH2	200"(16:9)	4519	4397	2611	2489	61	41
R109WX2	109"(16:10)	2456	2337	1580	1461	61	41
R114WX2	114"(16:10)	2558	2438	1643	1524	61	41
R125WX2	125"(16:10)	2809	3101	2060	1938	61	41
R144WX2	144"(16:10)	3223	3683	2423	2301	61	41
R100RH2	100"(16:9)	2329	2210	1359	1240	61	41
R120RH2	120"(16:9)	2779	2659	1610	1491	61	41
R135RH2	135"(16:9)	3109	2990	1801	1682	61	41

Unit: mm

Model	Screen Diag. & Aspect Ratio	Overall Width (A)	View Width (A1)	Overall Height (B)	View Height (B1)	Frame Width (C)	Frame Depth(D)
R100H2	100"(16:9)	91.7	87.0	53.5	48.8	2.4	1.6
R120H2	120"(16:9)	109.4	104.7	63.4	58.7	2.4	1.6
R135H2	135"(16:9)	122.4	117.7	70.9	66.1	2.4	1.6
R84WH2	84"(16:9)	78.0	73.3	46.1	41.4	2.4	1.6
R100WH2	100"(16:9)	91.7	87.0	53.5	48.8	2.4	1.6
R106WH2	106"(16:9)	96.9	92.2	56.7	52.0	2.4	1.6
R110WH2	110"(16:9)	100.6	95.9	58.7	53.9	2.4	1.6
R120WH2	120"(16:9)	109.4	104.7	63.4	58.7	2.4	1.6
R135WH2	135"(16:9)	122.4	117.7	70.9	66.1	2.4	1.6
R150WH2	150"(16:9)	135.5	130.7	78.4	73.6	2.4	1.6
R165WH2	165"(16:9)	148.5	143.8	85.6	80.9	2.4	1.6
R180WH2	180"(16:9)	161.6	156.9	92.9	88.2	2.4	1.6
R200WH2	200"(16:9)	177.9	173.1	102.8	98.0	2.4	1.6
R109WX2	109"(16:10)	96.7	92.0	62.2	57.5	2.4	1.6
R114WX2	114"(16:10)	100.7	96.0	64.7	60.0	2.4	1.6
R125WX2	125"(16:10)	110.6	122.1	81.1	76.3	2.4	1.6
R144WX2	144"(16:10)	126.9	145.0	95.4	90.6	2.4	1.6
R100RH2	100"(16:9)	91.7	87.0	53.5	48.8	2.4	1.6
R120RH2	120"(16:9)	109.4	104.7	63.4	58.7	2.4	1.6
R135RH2	135"(16:9)	122.4	117.7	70.9	66.2	2.4	1.6

Unit: inch

The listed measurements are for general reference only. Please contact Elite Screens to verify product design and dimensions before attempting to integrate its products with any structural or furniture modification. Although a manufacturer may offer product advice, it may be taken or disregarded at the integrator's discretion. Elite Screens will not be held responsible or be otherwise liable for faulty installations.

