



Evanesce B Series

The Evanesce is an In-Ceiling Front Projection Screen for non-dedicated media rooms with MaxWhite FG front projection screen material.

www.elitescreens.com/evansceb



Member

Evanesce B Series



The Evanesce is an In-Ceiling Front Projection Screen for non-dedicated media rooms with MaxWhite FG front projection screen material.



Screen Material

- MaxWhite FG front projection material
- 1.1 Gain with wide 160° viewing angle
- Black masking borders enhance picture contrast
- Flame Resistant: Complies with NFPA 701 Standards

Housing Finish and Installation

- Aluminum housing with white finish is slim yet strong and moisture resistant
- Concealed in-ceiling front projection screen for multi-use rooms
- Below and above ceiling access installation design
- Installation kit included

Control System

- Internal Radio Frequency and Infrared receivers with IR and RF remotes included
- Low voltage 3-way position wall switch
- Optional in-wall up/down switch, wireless 5-12 volt trigger
- RJ45 port allows 3rd party control systems integration

Quality and Reliability

- Tubular motor allows swift operation with a superior weight tolerance and operational lifespan
- 2-year warranty
- 3-year warranty for ENR-G (Educational, Non-profit, Religious or Government/Military) - US only

Certified

- GREENGUARD® Indoor Air Quality and GREENGUARD® Children & Schools Certified



MaxWhite FG Screen Material is the enhanced version of our most versatile front projection screen surface with fiberglass backing for enhanced flatness. Fiber glass backing provides unlimited viewing angles with perfectly flat uniformity while giving precise definition and color reproduction with black and white contrast. Screen Surface is durable, mildew resistant and easy to clean.

Evanesce B Series: In-ceiling Electric/Motorized Screen with IR/RF Remote & 3 Way on-wall switch

Model	Nominal Diagonal	View Height (in)	View Width (in)	View Height (cm)	View Width (cm)	Net Weight (lbs)	Gross Weight (lbs)	Net Weight (kgs)	Gross Weight (kgs)	Packaging Dimension (LxHxW)	Gain	Screen Material
EB100VW-E8	100" (4:3)					Please visit www.elitescreens.com					1.1	MaxWhite-FG
EB120VW-E8	120" (4:3)					Please visit www.elitescreens.com					1.1	MaxWhite-FG
EB100HW-E8	100" (16:9)	49.0	87.2	115.2	204.9						1.1	MaxWhite-FG
EB110HW-E8	110" (16:9)					Please visit www.elitescreens.com					1.1	MaxWhite-FG
EB120HW-E8	120" (16:9)	58.9	104.6	138.4	245.8						1.1	MaxWhite-FG

Evanesce B Series Dimension Table | Above Ceiling

Model	Screen Diag. & Aspect Ratio	Full Housing Length (A)	View Width (A1)	L/R Black Masking (A2)	Weight Bar Length (A3)	Case Length (A4)	A5	Overall Height (B)	View Height (B1)	Top Black Masking Border (B2)	B3	Case Height (B4)	Screen Fully Deployed Height (B5)	Case Width (C)	C1	C2	C3	C4
EB100VW-E8	100" (4:3)							Please visit www.elitescreens.com										
EB120VW-E8	120" (4:3)							Please visit www.elitescreens.com										
EB100HW-E8	100" (16:9)	2471	2214	50	2406	2411	2441	2544	1245	203	76	95	1524	80	925	145	180	50
EB110HW-E8	110" (16:9)							Please visit www.elitescreens.com										
EB120HW-E8	120" (16:9)	2914	2657	50	2849	2854	2884	2793	1494	203	76	95	1773	80	925	145	180	50

Unit: mm

Can't find size and ratio you're looking for? Visit elitescreens.com/csr to create your own

Model	Screen Diag. & Aspect Ratio	Full Housing Length (A)	View Width (A1)	L/R Black Masking (A2)	Weight Bar Length (A3)	Case Length (A4)	A5	Overall Height (B)	View Height (B1)	Top Black Masking Border (B2)	B3	Case Height (B4)	Screen Fully Deployed Height (B5)	Case Width (C)	C1	C2	C3	C4
EB100VW-E8	100" (4:3)							Please visit www.elitescreens.com										
EB120VW-E8	120" (4:3)							Please visit www.elitescreens.com										
EB100HW-E8	100" (16:9)	97.3	87.2	2.0	94.7	94.9	96.1	100.2	49.0	8.0	3.0	3.7	60.0	3.1	36.4	5.7	7.1	2.0
EB110HW-E8	110" (16:9)							Please visit www.elitescreens.com										
EB120HW-E8	120" (16:9)	114.7	104.6	2.0	112.2	112.4	113.5	110.0	58.8	8.0	3.0	3.7	69.8	3.1	36.4	5.7	7.1	2.0

Unit: inch

Can't find size and ratio you're looking for? Visit elitescreens.com/csr to create your own

Evanesce B Series Dimension Table | Below Ceiling

Model	Screen Diag. & Aspect Ratio	Full Housing Length (A)	View Width (A1)	L/R Black Masking (A2)	Weight Bar Length (A3)	Case Length (A4)	A5	Overall Height (B)	View Height (B1)	Top Black Masking Border (B2)	B3	Case Height (B4)	Screen Fully Deployed Height (B5)	C	C1	C2	C3
EB100VW-E8	100" (4:3)							Please visit www.elitescreens.com									
EB120VW-E8	120" (4:3)							Please visit www.elitescreens.com									
EB100HW-E8	100" (16:9)	2471	2214	50	2406	2411	2441	1619	1245	203	76	95	1524	110	80	120	2461
EB110HW-E8	110" (16:9)							Please visit www.elitescreens.com									
EB120HW-E8	120" (16:9)	2914	2657	50	2849	2854	2884	1868	1494	203	76	95	1773	110	80	120	2904


Unit: mm

Can't find size and ratio you're looking for? Visit elitescreens.com/csr to create your own

Model	Screen Diag. & Aspect Ratio	Full Housing Length (A)	View Width (A1)	L/R Black Masking (A2)	Weight Bar Length (A3)	Case Length (A4)	A5	Overall Height (B)	View Height (B1)	Top Black Masking Border (B2)	B3	Case Height (B4)	Screen Fully Deployed Height (B5)	C	C1	C2	C3
EB100VW-E8	100" (4:3)							Please visit www.elitescreens.com									
EB120VW-E8	120" (4:3)							Please visit www.elitescreens.com									
EB100HW-E8	100" (16:9)	97.3	87.2	2.0	94.7	94.9	96.1	63.7	49.0	8.0	3.0	3.7	60.0	4.3	3.1	4.7	96.9
EB110HW-E8	110" (16:9)							Please visit www.elitescreens.com									
EB120HW-E8	120" (16:9)	114.7	104.6	2.0	112.2	112.4	113.5	73.5	58.8	8.0	3.0	3.7	69.8	4.3	3.1	4.7	114.3

Unit: inch

Can't find size and ratio you're looking for? Visit elitescreens.com/csr to create your own



Note: Data Error ±1". The listed measurements are for general reference only. Please contact Elite Screens to verify product design and dimensions before attempting to integrate its products with any structural or furniture modification. Although a manufacturer may offer product advice, it may be taken or disregarded at the integrator's discretion. Elite Screens will not be held responsible or be otherwise liable for faulty installations.