

## 3.8kW Single-Phase Metered PDU, 200/220/230/240V Outlets (8 C13, 2 C19) IEC-309 16A Blue, 8 ft. (2.43 m) Cord, 1U Rack-Mount, TAA

MODEL NUMBER: PDUMH16HV



### Highlights

- Metered single phase 16A 200/220/230/240V PDU
- 1U horizontal rackmount; digital current meter
- C20 input with IEC-309 Blue 16A input; 2.5m line cord
- 10 total outlets (8 C13, 2 C19); 6.5 in. / 16.5 cm depth
- TAA Compliant

### Package Includes

- Rackmount PDU
- Rack mounting brackets
- Plug lock inserts
- IEC-309 Blue 16A input cord

### Features

- 3.8kW 16A single phase 200/220/230/240V Metered Power Distribution Unit / PDU
- Built-in 2 digit visual meter continuously reports PDU load level in amps
- C20 inlet with IEC-309 Blue 16A input; 2.5m line cord
- 1U horizontal rackmount format installs in one rack space
- 10 total outlets (8 C13 / 2 C19)
- Mounting flanges support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Mounting ears are reversible for front or rear facing rackmount installation
- Front panel grounding lug
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

| OVERVIEW          |                    |
|-------------------|--------------------|
| UPC Code          | 037332182791       |
| PDU Type          | Metered            |
| INPUT             |                    |
| PDU Input Voltage | 200; 220; 230; 240 |



|  |   |
|--|---|
| Recommended Electrical Service               | 16A 230V  |
| Maximum Input Amps                           | 16  |
| PDU Plug Type                                | IEC-309 16A BLUE (2P+E)   |
| Input Phase                                  | Single-Phase  |
| Input Cord Length (ft.)                      | 8.2   |
| Input Cord Length (m)                        | 2.50  |
| <b>OUTPUT</b>                                |   |
| Output Capacity Details                      | 3.84kW (240V), 3.68kW (230V), 3.52kW (220V), 3.2kW (200V) / 16A total capacity; 16A max per C19 outlet; 12A (10A CE) max per C13 outlet |
| Frequency Compatibility                      | 50 / 60 Hz  |
| Output Receptacles                           | (8) C13; (2) C19  |
| Output Nominal Voltage                       | 200; 220; 230; 240  |
| Overload Protection                          | n/a   |
| <b>USER INTERFACE, ALERTS &amp; CONTROLS</b> |   |
| Front Panel LCD Display                      | Digital display reports total PDU output current in amps  |
| Switches                                     | n/a   |
| <b>PHYSICAL</b>                              |   |
| Form Factors Supported                       | 1U rackmount. Includes mounting accessories for 2-4 post racks  |
| Material of Construction                     | Metal   |
| Minimum Required Rack Depth (cm)             | 25.40   |
| Minimum Required Rack Depth (inches)         | 10  |
| PDU Form Factor                              | Horizontal (1U)   |
| Shipping Dimensions (hwd / cm)               | 7.70 x 51.99 x 27.79  |
| Shipping Dimensions (hwd / in.)              | 3.03 x 20.47 x 10.94  |
| Shipping Weight (kg)                         | 2.95  |
| Shipping Weight (lbs.)                       | 6.50  |
| Unit Dimensions (hwd / cm)                   | 2.87 x 44.4 x 16.5  |
| Unit Dimensions (hwd / in.)                  | 1.75 x 17.5 x 6.5   |
| Unit Weight (kg)                             | 3.08  |
| Unit Weight (lbs.)                           | 6.8   |
| <b>ENVIRONMENTAL</b>                         |   |
| Storage Temperature Range                    | -30°C to +50°C (-22°F to +122°F)  |
| Relative Humidity                            | 5-95% non-condensing  |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

| <b>SPECIAL FEATURES</b>             |  |
|-------------------------------------|--|
| TVSS Grounding                      | Front panel grounding lug  |
| <b>STANDARDS &amp; COMPLIANCE</b>   |  |
| Certifications                      | Class A (Emissions), CE (IEC / EN60950-1), GOST, RoHS compliant, TAA Compliant |
| <b>WARRANTY</b>                     |  |
| Product Warranty Period (Worldwide) | 2-year limited warranty  |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>