

4-port Gigabit midspan - PoE+ injector - 802.3at/af

StarTech ID: POEINJ4G



This Gigabit midspan PoE+ injector is a cost-effective alternative to upgrading your existing network switch to a PoE-capable model.

It supplies up to 30 Watts output to each port, so you can easily power and access up to four high-power PoE-compliant devices — such as IP cameras — using standard Ethernet cable.



More power, with less cost and hassle

This versatile midspan PoE+ injector is suited for almost all PoE device classes, including wireless access

points, as well as IP phones and cameras. The high-power PoE+ injector offers 120W total power distribution and delivers full power — up to 30.8W — from each port. Now, you can easily scale and power your PoE+ devices across long distances, even in remote locations where a typical power outlet is unavailable.

Plus, the cost-effective Power over Ethernet+ injector lets you connect your PoE-powered devices (PDs) to a non-PoE-capable switch, avoiding the expense and aggravation of upgrading your existing switch to a PoE-enabled model.

Easy to set up in mixed environments

This injector is the perfect solution for a variety of environments. It features a wall-mountable rugged metal casing, but is palm-sized making it perfect for desktop placement too.

With plug-and-play operation, you can enjoy fast and hassle-free setup without disrupting your workflow.

Convenient, protected connections

Not sure which class your PoE devices are? The Gigabit midspan PoE+ injector automatically detects the power requirements of your PoE PDs, and delivers the appropriate level of power without damaging your devices.

With integrated circuit protection between each port, your devices are also protected from power interference.

The POEINJ4G is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Ideal for high-power PoE+ devices requiring Gigabit speeds such as PTZ (Pan, Tilt, Zoom) cameras and Wi-Fi® access points (WAP)
- Enable remote installation of touchscreens, information kiosks, and phones in locations where a power connection is not available
- Perfect for SOHO, SMB, system integrators, and IT administrators

Features

- Easily connect, power, and operate up to four Gigabit PoE-powered devices (PD)
- Delivers full power to each port up to 30.8 watts (802.3at) or 15.4 watts (802.3af) to your connected devices
- Flexible setup, with a desktop-sized, or wall-mountable metal housing
- Plug-and-play setup and operation
- Automatically detects the powered device to provide the appropriate level of power output
- Circuit protection prevents power interference between each port
- Support for 10/100/1000 Mbps networks and devices, as well as Auto-Negotiation and auto-MDIX

Technical Specifications

Warranty	2 Years
Industry Standards	IEEE 802.3af PoE, IEEE 802.3at PoE+
Industry Standards	IEEE 802.3 10BASE-T, IEEE 802.3u 100BASE-TX, IEEE 802.3ab 1000BASE-T
Ports	4
Maximum Cable Length	328 ft [100 m]
Maximum Data Transfer Rate	2 Gbps (Full-Duplex)
MTBF	50,000 Hours
Power Output	52V DC at 30.8W (PoE+)
Connector Type(s)	8 - RJ-45 Female

Note If your connected devices do not meet the IEEE 802.3af or IEEE 802.3at PoE standard, then the POEINJ4G will not inject power to the connected device(s) / Ethernet cable(s)

Color	Black
Enclosure Type	Steel
Product Height	1 in [26 mm]
Product Length	3.8 in [97 mm]
Product Weight	7.8 oz [220 g]
Product Width	2.8 in [70 mm]
LED Indicators	1 - Power
LED Indicators	4 - PoE In-Use
Center Tip Polarity	Positive
Input Current	2-1 A
Input Voltage	100 ~ 240 AC
Output Current	2.31 A
Output Voltage	52 DC
Plug Type	M
Power Consumption	120 W Max
Power Source	AC Adapter Included
Humidity	5~95% RH (Non-Condensing)

Operating Temperature	0°C to 50°C (32°F to 122°F)
Storage Temperature	-10°C to 70°C (14°F to 158°F)
Shipping (Package) Weight	3 lb [1.4 kg]
Included in Package	1 - 4 Port Gigabit PoE+ Injector
Included in Package	1 - Universal Power Adapter
Included in Package	3 - Power Cords (NA/UK/EU)
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

