

Server Technology Technical Data Sheet

PRO2™ Switched Rack PDU

C2W36CE-()MFA[]00: 5.7kW - 8.6kW 3-phase input with
(36)C13 HDOT® outlets



Oct 2015 | Version 1.1

The Server Technology® PRO2 Switched PDU provides control of outlet power and local LED input current monitoring, allowing IT personnel to determine safe levels of loading on a per-phase basis while installing equipment into the rack/cabinet. The integral PIPS® technology provides billing-grade accurate measurement of current, voltage, active power, apparent power, power factor, crest factor, and accumulated energy at the input. These power data points, along with temperature and humidity measurements (provided via optional probes), are accessible through the built-in Web and CLI interfaces as well as through SNMP. The PRO2 Switched "Master" PDU can be connected to as many as three PRO2 Switched "Link" PDUs to extend the network access to the redundant or secondary power feed without the risks of a daisy chain linking configuration.




Server Technology
Quality Rack Power Solutions

Features




Network Monitoring

The PRO2 hot-swappable network card provides for HTTP(S), SSH, Telnet, SNMP, (S)FTP, SMTP, Syslog, LDAP(S), RS-232 serial, and more.




ST Eye Bluetooth Ready

The best PDU LCD is the one in your hand. Attach the ST Eye® Bluetooth module to access power data and system settings. (sold separately)




Hot-Swap Network Card

Network access is ensured when power is lost to the Master unit with backup power provided by the primary link unit.



Star Multi-Linking

PRO2 provides the ability to link up to four power circuits using one IP address. Primary link provides backup power to network card. (sold separately)



Temperature/Humidity Monitoring

PRO2 Master and Link units each support two external 10' (3m) T/H probes. Receive SNMP-based alerts and email notifications.



Auto-flip Current Display

Easy-to-read LEDs display current per phase to help prevent overloads and simplify three-phase load balancing in high-density cabinets.



Per-Inlet Power Sensing

Meets ANSI C12.1 for billing-grade accuracy of Current per phase. PIPS includes voltage, active power, apparent power, power factor, and energy.




Branch Current Monitoring

PRO2 monitors current at each breaker branch and provides SNMP-based alerts and emails on high usage that risks a tripped circuit.



Branch Circuit Protection

PRO2 meets the UL and IEC 60950-1 requirement for branch circuit protection through use of UL489 rated magnetic-hydraulic circuit breakers.




Outlet Control

On PRO2 Switched PDUs, cycle power to individual outlets or groups of outlets to reboot servers. Or, power off unused receptacles.



Alternating-Phase Outlets

3-phase power is wired in an alternating fashion per outlet for simplified load balancing, reduced cord lengths, and better airflow.




High Temperature Rating

This product has been tested and approved for safe and reliable operation in 60°C (140°F) data center environments.



High Retention Locking Outlets

PRO2 receptacles have high retention and are compatible with many locking power cords



Flexible Mounting

PRO2 includes standard button mounts along with provisions for custom mounting brackets (contact ServerTechnology for details).



Color Identification

Choose from six colors to designate circuits for PDUs in the data center. Color options include Blue, Red, Green, White, Yellow, and Black



Cisco EnergyWise¹ Compliant

PRO2 meets the requirements set forth by Cisco System, Inc. for its EnergyWise program for monitoring of device energy.

Specifications

North America

Master PDU	Link PDU	Input Plug	Input Current	Input Voltage	Rated Power
C2W36CE-DBMFA[]00	C2X36CE-DBMFA[]00	NEMA L15-20P, 10ft, 4-C, 12AWG	≤ 16A (20 peak)	208V 3-ph Delta 50/60Hz	5.7kW @208V
C2W36CE-DCMFA[]00	C2X36CE-DCMFA[]00	NEMA L15-30P, 10ft, 4-C, 10AWG	≤ 24A (30 peak)	208V 3-ph Delta 50/60Hz	8.6kW @208V
C2W36CE-YBMFA[]00	C2X36CE-YBMFA[]00	NEMA L21-20P, 10ft, 5-C, 12AWG	≤ 16A (20 peak)	120/208V 3-ph Wye 50/60Hz	5.7kW @208V
C2W36CE-YCMFA[]00	C2X36CE-YCMFA[]00	NEMA L21-30P, 10ft, 5-C, 10AWG	≤ 24A (30 peak)	120/208V 3-ph Wye 50/60Hz	8.6kW @208V

*Note: replace the [] with 9 for front entry cord or M for base entry cord.

Outputs

- Connector: (36) x IEC 60320/C13
- North America Rating (C13): ≤ 12A @208V L-L (15A peak)
- Connector: (3) x NEMA 5-15/20R (on L21 input designs only)
- North American Rating (5-15/20R): ≤ 16A @120V L-N (20A peak)
- Locking outlets provide high-retention even for non-locking cords

Input measurement accuracy

- LED Current = ± 10% 0.1 amp (0.3 – 9.9amps) and 1 amp (>9.9 amps) resolution
- GUI Current = ± 1% at 0.01 amp resolution (above 0.25 amp)
- Voltage = ± 1% at 0.1 volt resolution (nominal ± 10%)
- Active Power = ± 1% at 1 watt resolution
- Apparent Power = ± 1% at 1 volt-amp resolution
- Power Factor = ± 3% at 0.01 resolution
- Crest Factor = ± 10% at 0.1 resolution
- Energy = ± 1% at 0.1 kilowatt-hour resolution

Branch measurement accuracy

- Current = ± 3% at 0.01 amp resolution (above 0.5 amp)

Branch Circuit Protection

- UL489 compliant 2-pole, 20A trip circuit breakers, three (3) branches, rating: ≤ 16A @208V

Specifications Cont.

Physical/Environmental

- Dimensions: 70.0" (1778 mm) tall x 2.2" (56 mm) wide x 2.5" (64 mm) deep | Weight: 22 lbs (10 kg)
- Shipping Dimensions: 79" x 7" x 7" (200 cm x 17.8 cm x 17.8 cm) | Weight: 25 lbs (11.4 kg)
- Highlight Color: Choose Black, White, Red, Green, Blue, Yellow
- Operating Environment: 32°F to 140°F / 0°C to 60°C | 8%RH to 90%RH non-condensing | 6,500ft/2000m elevation
- Storage Environment: -40°F to 185°F / -40°C to 85°C | 8%RH to 90%RH non-condensing | 50,000ft/15km elevation
- Quiescent / Unloaded Power Draw: <15W for all configurations

Communications and Security

- 10/100 Mbps Ethernet (RJ-45 connector), RS-232 serial (RJ-45 connector)
- Aux connector for connection of Star Multi-Linking module or ST Eye™ Bluetooth module
- Two (2) temperature/humidity sensor inputs (4P4C), Link port (RJ-12) – {also on Link CDU}
- Web-browser GUI and command-line-interface (CLI): HTTP/HTTPS, TLSv1, SSHv2, Telnet, SNMPv2c and v3 (GET, SET, Traps), IPv4 and IPv6, LDAPv3/LDAPS, TACACS+, RADIUS, FTP/SFTP

North American Certifications

- cTUVus Mark to UL 60950-1:2007 and CAN/CSA 22.2 No. 60950-1-07 + A1:2011
- EMC to EN 55022 Class A, EN 55024, CISPR 22 Class A
- FCC Class A, Part 15
- RoHS/WEEE


Optional Accessories

- EMTH-1-1 Combination Temperature/Humidity Probe, 10ft (3m)
- EMCU-1-1B Environmental Monitor adding:
 - Two (2) EMTH-1-1 temperature/humidity ports (one probe included)
 - One (1) EMWS-1-1 water sensor port (probe sold separately)
 - Four (4) dry contact (NO/NC) monitoring points
 - One (1) 8-bit analog-to-digital converter (0 to 5VDC)
- KIT-PRO2LINK-01M Star Multi-Linking module provides ability to link (2) additional expansion units.
- KIT-STEYE-10 Bluetooth module with Android and IOS support.
- KIT-SUS-01 StartUp Stick™ for rapid configuration.
- SPM (Sentry® Power Manager):
 - Monitor and manage multiple PDUs from a single point
 - Monitor and manage alarm conditions
 - Create reports and trends on stored data
 - Analyze power usage per phase
 - Optional appliance or virtual version
 - VMware Ready²




- Mounting Brackets
 - Buttons (KIT-0020) included for tool-less mounting (see diagram).
 - See the Mounting Bracket Guide for further suggestions.
 - Custom mounting options available. Contact your local Server Technology representative.
- Cable Retention Devices for non-locking cords
 - EZip™
 - Cable Sleeve

Dimensional Specifications




Wiring and Breaker Trip Curve



Part Number		Certification	Input		Output		
Master	Expansion	Rating Standard	Rating	Input Type	Total Output Rating	Outlet Type and Ratings	Branch Circuit Rating
C2WxxCE-DBMFA9yy	C2XxxCE-DBMEA9yy	cTUVus and/or cULus	208V 3P+PE, 50/60Hz; 16A	NEMA L15-20P	208V, 50/60Hz; <= 27.7A	IEC 60320: C19 <= 16A each, C13 <= 12A each	3 branches, each <= 16A
C2WxxCE-DCMFA9yy	C2XxxCE-DCMEA9yy	cTUVus and/or cULus	208V 3P+PE, 50/60Hz; 24A	NEMA L15-30P	208V, 50/60Hz; <= 41.5A	IEC 60320: C19 <= 16A each, C13 <= 12A each	3 branches, each <= 16A
C2WxxCE-YBMFA9yy	C2XxxCE-YBMEA9yy	cTUVus and/or cULus	120/208V 3P+N+PE, 50/60Hz; 16A	NEMA L21-20P	208V, 50/60Hz; <= 27.7A	IEC 60320: C19 <= 16A each, C13 <= 12A each, NEMA 5-20R <= 16A each	3 branches, each <= 16A
C2WxxCE-YCMFA9yy	C2XxxCE-YCMEA9yy	cTUVus and/or cULus	120/208V 3P+N+PE, 50/60Hz; 24A	NEMA L21-30P	208V, 50/60Hz; <= 41.5A	IEC 60320: C19 <= 16A each, C13 <= 12A each, NEMA 5-20R <= 16A each	3 branches, each <= 16A

Note: "xx" designates total number of outlets and "yy" designates code for number of C19 outlets in each of the two outlet modules



Additional Information

Warranty: Server Technology offers a standard 2-year limited parts & labor warranty. Extended support is available at the time of purchase. See the Support Options on the website, or contact your local Server Technology representative for more information.

Patents: Information on Server Technology patents is available on the website at:

www.servertech.com/products/patents

HDOT, PIPS, POPS, CDU, Sentry, Server Technology, the ST Eye logo, and the globe logo are U.S. registered trademarks of Server Technology, Inc. Power Pivot, EZip, StartUp Stick and PRO2 are trademarks of Server Technology, Inc.

Information in this document is current as of time of publishing. Contact your Server Technology representative for the most up-to-date information. © 2015 Server Technology, Inc.

¹ Cisco EnergyWise is a U.S. registered trademark of Cisco Technology, Inc.

² VMware and VMware Ready is a registered trademark or trademark of VMware, Inc. in the United States and/or other jurisdictions.



HEADQUARTERS -
NORTH AMERICA
Server Technology, Inc.
1040 Sandhill Drive
Reno, NV 89521
United States
1.775.284.2000 Tel
1.775.284.2065 Fax
sales@servertech.com
www.servertech.com
www.servertechblog.com

Western Europe, Middle East and
Africa
Server Technology
Fountain Court
2 Victoria Square
Victoria Street
St. Albans
AL1 3TF
United Kingdom
+44 (0) 1727 884676 Tel
+44 (0) 1727 220815 Fax
salesint@servertech.com

Central Europe, Eastern Europe and
Russia
Niederlassung Deutschland
Server Technology LLC
42119 Wuppertal
Germany
Tel: + 49 202 693917 x 0
Fax: + 49 202 693917-10
salesint@servertech.com

APAC
Server Technology
Room 2301, 23/F, Future Plaza
111-113 How Ming Street,
Kwun Tong, Hong Kong
Direct line: +852 3916 2048
Fax Line: +852 3916 2002
salesint@servertech.com