

# Stellar performance. Down-to-earth price.

**Print. Copy. Scan. Fax.**

The Xerox WorkCentre PE120i packs robust multifunction capabilities into a compact, convenient package — scaled perfectly for the single user or a small network office. It provides a full range of powerful features, yet is exceptionally easy to use. And best of all, it's very affordable.



WorkCentre® PE120i	
<b>Speed</b>	Up to 22 ppm
<b>Duty Cycle</b>	Up to 15,000 pages / month
<b>Paper Handling</b>	
Paper input Standard	<b>ADF:</b> 50 sheets; Custom sizes: 5 x 5.8 in. to 8.5 x 14 in. / 127 x 148 mm to 216 x 356 mm <b>Main Tray:</b> 250 sheets; 5 x 7 in. to 8.5 x 14 in. / 98 x 148 mm to 216 x 356 mm <b>Bypass Tray:</b> 50 sheets; 3 x 5 in. to 8.5 x 14 in. / 76 x 127 mm to 216 x 356 mm
Optional	<b>Additional Tray:</b> 250 sheets; 5 x 7 in. to 8.5 x 14 in. / 98 x 148 mm to 216 x 356 mm
Paper output	150 sheets
<b>Copy</b>	
Resolution	600 x 600 dpi
Copy features	ID Card Copy / Clone copies, Scan Once - Print Many, Electronic Pre-Collation
<b>Print</b>	
First page out time	As fast as 10 seconds
Resolution	600 x 600 dpi, 1200 x 1200 dpi (emulated)
Memory (std / max)	32 MB / 160 MB
Processor	166 MHz
Page Description Language	PCL6, PostScript
Connectivity	USB 2.0, Parallel, 10/100 BaseT Ethernet
Features	Reduce/Enlarge, Watermark, Fit to Page, Poster printing, Custom-size pages, Scaling, N-up
<b>Scan</b>	
Resolution	600 x 1200 dpi, 4800 x 4800 enhanced
Features	Compatibility: TWAIN standard (driver included); Technology: Flat-bed CCD; Interface: Direct Connect to PC (USB 2.0 / IEEE1284 Parallel)
<b>Fax</b>	33.6 Kbps with MH/MR/MMR/JBIG/JPEG compression
Speed	3 seconds transmission speed at 33.6 Kbps
Resolution	203 x 98 dpi (std), 203 x 196 (fine), 300 x 300 (superfine), 203 x 146 (photo), 200 x 200 (color)
Features	4 MB (320 pages) <sup>1</sup> memory; Speed Dials: Up to 200 settings; Halftones: 256 levels; Color Fax Send, TollSave, Junk Fax Barrier
<b>Warranty</b>	One year warranty, Xerox Total Satisfaction Guarantee

**Device Management**  
ControlCentre™ 5.0, CentreWare® Internet Services, CentreWare® Web

**Print Drivers**  
Print Drivers: Windows98/ME/NT4.0/2000/XP/2003, Mac

**Media Handling**  
Main Tray: 16-24 lb. bond / 60-90 gsm  
Bypass Tray: 16-43 lb. bond / 60-163 gsm  
Automatic Document Handler: 12.5-28 lb. bond / 50-105 gsm  
Media Types: Plain paper, envelopes, labels, transparencies

**Operating Environment**  
Temperature: Maximum Range: 50° - 89°F/10° - 32°C  
Recommended Range: 60.8° - 86°F / 16° - 30°C  
Humidity: Maximum Range: 20 - 80%  
Recommended Range: 30 - 70%

**SCAN**  
**Resolution Settings**  
Optical Resolution 600 x 1200 dpi (optical, black-and-white and color)  
Enhanced Resolution up to 4800 dpi interpolated  
Pre-scan: 75 dpi

**Depth**  
Color: 24 bit  
Black-and-White: 1 bit (text) / 8 bit (grayscale)  
**Bundled OCR Software**  
ScanSoft OmniPage® SE 2.0  
Bundled Image Management and Enhancement Software: ScanSoft PaperPort® SE 9.0

**Electrical**  
Power: 100 to 127 VAC, 50/60 Hz  
220 to 240 VAC, 50/60 Hz  
Average Power Consumption: 400 watts  
Power Saver Mode: 19 watts  
Energy Saver: ENERGY STAR® Compliant

**Dimensions (WxDxH):**  
450 x 435 x 457 mm / 17.7 x 17.1 x 18.0 in.  
Weight with cartridge: 16.7 kg / 37 lbs.  
Weight without cartridge: 15.9 kg / 35 lbs.  
Gross weight with packaging: 21.0 kg / 46 lbs.

**Certifications**  
Safety Agency Approvals:  
UL Safety

**Supplies**  
Standard Capacity Print Cartridge:  
3,500 pages<sup>2</sup>  
High Capacity Print Cartridge:  
5,000 pages<sup>2</sup>



TOTAL SATISFACTION SERVICES



<sup>1</sup> Assumes standard resolution and text image setting using ITU-T test chart No. 1

<sup>2</sup> Average standard pages. Declared yield in accordance with ISO/IEC 19752. Yield will vary based on image, area coverage and print mode.

## Impressive Features

### Powerful

**Copying, printing, faxing, and scanning in a single device**

- Fast, crisp and clear laser printing at 22 ppm
- Fast 3 seconds fax transmission
- Scan high-quality color or black-and-white direct to desktop through direct USB connection
- Industry leading document management software

### Convenient and easy to use

**These tools fit comfortably on a small desktop. And you'll be just as comfortable with their simple operation.**

- Two paper trays for a large 300-sheet capacity, plus media flexibility. Add optional additional tray for 550 sheets total.
- Network printing to meet needs of small groups
- Optical Character Recognition (OCR) and Image Editing Software are included to convert scanned images into editable text documents

### Economical

**Attractively priced to exceed your expectations, but not your budget**

- Affordable for even the most cost-conscious users
- Provides single device simplicity