

# EB-X27

## DATASHEET



Small and light enough to be moved and used across several rooms, this high-quality projector produces clear bright images and comes with a range of easy-to-use features

This portable projector comes with a carry bag included to make for easy transport and storage of the projector when not in use. Ideal for use in meeting rooms, classrooms and home offices, the EB-X27 can display presentations with bright images and vibrant colours thanks to 3LCD technology. It also has a range of flexible installation options and connectivity features.

The EB-X27 uses 3LCD technology and an equally high White and Colour Light Output to deliver exceptional image quality and accurate colours. A 10,000:1 contrast ratio produces clearer image detail.

Epson understands that being in control is important when presenting in a corporate or education environment. The EB-X27 comes with multi-PC projection software, which allows content from up to four devices, including PCs, tablets and smartphones, to be displayed simultaneously. The moderator function allows the host, whether it is the teacher, lecturer or leader of the meeting, to take control of displayed content from the devices.

Set up is easy and flexible with horizontal and vertical keystone correction, helping you achieve a perfectly shaped image without distortion. This means projectors can be quickly moved and set up in different classrooms and meeting rooms.

This projector has enhanced connectivity, giving choice and flexibility however you intend to present. The EB-X27 can connect to the latest digital devices or legacy analogue products, meaning older hardware doesn't necessarily need to be replaced. Connecting smart devices couldn't be easier with the iProjection QR code connectivity<sup>1</sup> - simply scan a projected QR code using your smart device to connect and start working.

## KEY FEATURES

- **Portable**  
Small and light enough to be carried and used across several rooms
- **High-quality, bright image**  
3LCD technology and equally high 2,700lm White and Colour Light Output
- **Enhanced connectivity and networking**  
HDMI input; RJ-45 Ethernet; optional WiFi; iProjection via QR code
- **Flexible installation**  
Horizontal and vertical keystone correction and optical zoom for flexible placement
- **Low Total Cost of Ownership (TCO)**  
Long lamp life; A/V mute function pauses presentation and conserves power by 70%



Source: Futuresource Consulting Ltd.

**EPSON®**  
EXCEED YOUR VISION

## PRODUCT SPECIFICATIONS

### IMAGE

Colour Reproduction	Upto 1.07 billion colours
Colour Light Output	2,700 lumen-1,890 lumen (economy)
White Light Output	2,700 lumen - 1,890 lumen (economy) In accordance with ISO 21118:2012
Resolution	XGA, 1024 x 768, 4:3
Contrast Ratio	10,000 : 1
Lamp	200 W, 5,000 h durability, 10,000 h durability (economy mode)
Keystone Correction	Auto vertical: ± 30 °, Manual horizontal ± 30 °

### TECHNOLOGY

Projection System	3LCD Technology, RGB liquid crystal shutter
LCD Panel	0.55 inch with MLA (D8)

### OPTICAL

Projection Ratio	1.48 - 1.77:1
Zoom	Manual, Factor: 1.2
Projection Size	30 inches - 300 inches
Projection Distance Wide/Tele	1.8 m - 2.17 m (60 inch screen)
Projection Lens F Number	1.58 - 1.72
Focal Distance	16.9 mm - 20.28 mm
Focus	Manual
Offset	8 : 1

### CONNECTIVITY

USB Display Function	3 in 1: Image / Mouse / Sound
Epson iProjection App	Ad-Hoc / Infrastructure

### OTHER

Warranty	36 months On site service, Lamp: 12 months or 1,000 h Optional warranty extension available
----------	--

## EB-X27

### WHAT'S IN THE BOX

- Carrying bag
- Computer cable
- Main unit
- Power cable
- Remote control incl. batteries

### OPTIONAL ACCESSORIES

- Active Speakers - ELPSP02  
V12H467040DA
- Control and Connection Box - ELPCB02  
V12H614040DA
- Adapter - ELPAP10 Wireless LAN b/g/n  
V12H731P01
- Air Filter - ELPAF32  
V13H134A32
- Ceiling Mount (White) - ELPMB23  
V12H003B23
- Lamp - ELPLP88 - EB-9xxH/S27/X27/W29  
V13H010L88
- Quick Wireless Connect USB key - ELPAP09  
V12H005M09
- Screen (80" Multi-Aspect) - ELPSC26  
V12H002S26

## LOGISTICS INFORMATION

SKU	V11H692041
EAN code	8715946545172
Dimensions Single Carton	364 x 409 x 157 mm
Carton Weight	4.32 Kg
Multiple Order Quantity	1 Units
Country of Origin	Philippines



For more information please contact:

Telephone: 01952 607111 (UK)+  
01 436 7742 (Republic of Ireland)  
E-mail: [enquiries@epson.co.uk](mailto:enquiries@epson.co.uk)  
Chat: [etalk.epson-europe.com](http://etalk.epson-europe.com)  
Fax: 0871 222 6740  
+ Local call rate.

Web: [www.epson.co.uk](http://www.epson.co.uk)  
[www.epson.ie](http://www.epson.ie)

1. – QR code function requires iProjection app, available on Android and iOS devices

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners.  
Product information is subject to change without prior notice.

