

HSM® PET CP 4988 crusher press combination

Powerful compression makes compact PET/UBC bales!

- Low space requirement and easy to operate
- Large loading hopper
- The drainage system controls the discharge of residual fluid
- 2000 bottle capacity (1 liter bottle)
- Results in a compact PET bale



Specifications

HSM part #	HSMCP4988	Bale size (W x H x L)	19.67" x 19.67" x 47.2"
Motor in Hp (at max. output)	Crusher 2.95 / Press 5.36	Bale weight	220 lbs.
Voltage / Frequency	3 x 220V / 60 Hz	Throughput per hour PET bottles (1 liter)	up to 4000
Pressing power	11 tons	Machine dimensions (H x W x D)	70.87" x 37.4" x 145.3"
Working width	19.29"	Machine weight	2535 lbs.
Loading height	59.5"		

(All technical specifications are approximate values. Technical and design modifications reserved.)

HSM of America, LLC
419 Boot Road
Downingtown, PA 19335
www.hsmofamerica.com
Customer Service / 800.613.2110

HSM®
Great Products,
Great People.