



Powering Business Worldwide

Eaton 9PX 180V Extended Battery Module (EBM) for 9PX6KUS UPS, 3U Rack/Tower, TAA

MODEL NUMBER: 9PXEBM180RTUS



Sealed lead-acid extended battery module (EBM) provides extended runtime for compatible UPS system in small business, education, retail, financial or healthcare applications.

Features

Backup Battery Module Gives Your Compatible Eaton UPS System Extended Runtime

The 9PXEBM180RTUS offers extended battery runtime when used in conjunction with Eaton's TAA-compliant 9PX6KUS 9PX UPS system. It can also be daisy-chained for a maximum of four matching battery packs to deliver even longer extended-run operation. Heavy-gauge cabling with high-current DC connectors is included for safe, simple installation.

Supports 3U Rack or Tower Installation

This backup battery pack's multi-use form factor supports mounting in 3U of space in an EIA-standard 19-inch rack using the included 4-post rail kit. You can also adapt it for tower installation using the included support stands.

TAA-Compliant for GSA Schedule Purchases

The 9PXEBM180RTUS is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Versatile Installation Options

For installation in 2-post rackmounts, one RK2PC mounting kit is required for each UPS, EBM, PPDM, or transformer.

Highlights

- Connects to expandable TAA-compliant Eaton 9PX UPS system for extended runtime
- Daisy-chain connector supports additional battery packs for even longer runtime
- Includes heavy-gauge cabling with high-current 180V DC connectors
- Supports 3U rack mounting or upright tower installation using included kit accessories
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

Compatible only with Eaton's TAA-compliant 9PX6KUS UPS system

Package Includes

- 9PXEBM180RTUS 180V Extended Battery Module
- External battery cable, 1 ft. (0.3 m)
- Tower support stands
- Rack-mounting hardware
- Quick start guide

Specifications

OVERVIEW	
UPC Code	743172082558
INPUT	
Input Phase	Single-Phase
UPS Input Cord Length (ft.)	1
UPS Input Cord Length (m)	0.3



Powering Business Worldwide

OUTPUT	
Individually Controllable Load Banks	No
BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
Expandable Runtime	No
DC System Voltage (VDC)	180
Replacement Battery Cartridge	744-A1974
Battery Management	ABM technology (3-stage charging extends battery service life by 50% and provides advance warning for battery replacement)
PHYSICAL	
Primary Form Factor	Rackmount; Tower
Rack Height	3U
External Battery Pack Form Factor	Rack/Tower
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount (RK2PC)
Minimum Required Rack Depth (cm)	73.66
Minimum Required Rack Depth (inches)	29
Unit Dimensions (hwd / in.)	5.100 x 17.300 x 25.400
Unit Weight (lbs.)	150.000
Unit Weight (kg)	68.04
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Relative Humidity	0-95% non-condensing
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; NOM (Mexico)
Product Compliance	ENERGY STAR Qualified; RoHS; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	3-year limited warranty
Extended Service Plans	ADVANCED DEPOT EXCHANGE Service Part Number: 9SW5Y-3000BC Expedited parts coverage for 5 years Parts, electronics and UPS batteries coverage Next business day shipping Technical support 5-YEAR ON-SITE PLAN (US ONLY) Service Part Number: WEBN75XX-7000BC On-site parts and labor coverage for years 5 Parts, electronics and UPS batteries coverage 24x7 on-site labor coverage, next-day response Next-day shipping Technical support



Powering Business Worldwide

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.