

Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

1.4kW Single-Phase Metered PDU, 120V Outlets (14 5-15R), 5-15P, 15 ft. (4.57 m) Cord, 0U Vertical, 36 in.

MODEL NUMBER: PDUMV15-36



Features

- 15A single phase 120V Metered Power Distribution Unit / PDU (Agency de-rated to 12A continuous)
- Two-digit lighted meter reports combined total output current in amps
- Attached NEMA 5-15P 15A 120V input plug with 15-ft. (4.57 m) line cord
- 0U 36in / 91cm vertical rackmount format installs using no rack spaces
- 14 NEMA 5-15R outlets
- Includes 15A circuit breaker and lighted power switch inside a transparent protective cover
- Toolless installation supported in button-mount compatible equipment racks
- Bolt-down installation brackets support installation in other racks and additional surfaces

Specifications

OVERVIEW		
UPC Code	037332182869	
PDU Type	Metered	
INPUT		
PDU Input Voltage	100; 120; 127	
Recommended Electrical Service	15A 120V	
Maximum Input Amps	15	
Maximum Input Amps Details	Agency de-rated to 12A continuous	

Highlights

- Metered single phase 15A 120V
 0U 36in / 91cm vertical
 rackmount PDU
- Two-digit current meter reports output current in amps
- Attached 15-ft. (4.57 m) cord with NEMA 5-15P input plug
- 14 NEMA 5-15R outlets
- Toolless button mount and boltdown bracket installation hardware included

Package Includes

- Metered Vertical PDU
- Mounting hardware and spare mounting buttons
- Owner's manual with warranty information



Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

PDU Plug Type	NEMA 5-15P
Input Phase	Single-Phase
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
OUTPUT	
Output Capacity Details	1.52kW (127V), 1.44kW (120V), 1.2kW (100V) / 15A total capacity (Agency de-rated to 12A); 12A max per outlet
Frequency Compatibility	50 / 60 Hz
Output (VA)	1800
Output Receptacles	(14) 5-15R
Output Nominal Voltage	100; 120; 127
Overload Protection	15A circuit breaker
USER INTERFACE, ALERTS & CO	NTROLS
Front Panel LCD Display	Digital meter reports PDU output current in amps
Switches	Lighted on/off switch with integrated safety cover
PHYSICAL	
Form Factors Supported	Vertical (0U) mounting in rack enclosures, horziontal mount in raceways and a variety of other applications
Material of Construction	Aluminum
PDU Form Factor	Vertical (0U)
Shipping Dimensions (hwd / cm)	5.61 x 98.88 x 14.12
Shipping Dimensions (hwd / in.)	2.21 x 38.93 x 5.56
Shipping Weight (kg)	1.72
Shipping Weight (lbs.)	3.79
Unit Dimensions (hwd / cm)	91.4 x 4.45 x 3.2
Unit Dimensions (hwd / in.)	36 x 1.75 x 1.25
Unit Weight (kg)	1.45
Unit Weight (Ibs.)	3.2
ENVIRONMENTAL	
Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)
Relative Humidity	5-95% non-condensing
STANDARDS & COMPLIANCE	
Certifications	Tested to UL60950-1 (USA) and CSA60950-1 (Canada), NOM (Mexico), Class A (Emissions), RoHS Compliant



WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies