



THE SIGHTS & SOUNDS
OF EDUCATION

Powered Whiteboard Array Speaker

Model PI31-PS

This powered array speaker enhances presentations with superior sound. Array speaker technology focuses the sound pattern more directly at the audience with a narrower dispersion angle. This makes for a clearer and more evenly balanced message by not bouncing its sound off walls, so it doesn't contribute to existing ambient noise levels. Single 3.5mm input enables connecting audio from smartphones. Fixed & variable line-outs for adding speakers and other connected capabilities.

1. Protective steel grille
2. Three x 3" transducers
3. Rugged steel bracket
4. Tone control
5. DC input
6. Fixed and variable line-outs allows unit to function as master volume control for other daisy-chained speakers
7. Single 3.5mm or dual RCA line in connects audio from smartphones & other devices
8. 1/4" mic input

- * Delivers superior audio enhancement for up to 300 people from smartphones, projectors, computers, media players & other devices
- * Designed for installation in classroom and meeting facilities

“Project Intercept”


Please contact us immediately if you experience any difficulties with your PI31-PS speaker. Our “Project Intercept” customer service program will quickly repair or replace items under warranty. Simply contact us via phone or email warranty@califone.com

Visit our website to register your product and to learn more about the complete line of *Califone®* audio enhancing and visual technology products including: Wired and Wireless public address systems, wireless microphones, headphones & headsets, group listening centers, multimedia players and computer peripheral products.

We are proud of helping teachers enhance student understanding and achievements since 1947, with your satisfaction as our first priority.

The PI31-PS has a limited six-year warranty and service support available through authorized dealers nationwide. Its warranty covers school use - unlike some other PA products whose warranties would be voided if used in schools.

Distributed by:



Specifications

Array Speaker

Rated Power Output:	25 watts RMS
Sensitivity for Rated Output:	Line:100 mVrms, mic: 4 mVrms Auxiliary: 240 mVrms
Frequency Response:	100 Hz – 3 kHz
Sensitivity:	93 dB 1 Watt @ 1 meter
Speakers:	3 x 3" with 16 Ohm Transducers
Inputs:	Line inputs (2): 3.5mm, dual RCA (summing L+R), Unbalanced mic: Lo –Z, 1/4"–phone
Outputs	Line outputs (2); fixed and variable
THD	10% at 40hm load, power output 25W
Power Source:	Wall adapter with D.C. output to amp.
Dimensions (HWD), weight:	12.5" x 5" x 4.5", 3.2 pounds
Dynamic Range:	100 dB
Material	ABS plastic with protective steel grille
Mounting Bracket	Included
Weight:	4.9 lbs each with bracket, ship 5 lbs.; Master pack - 2 units, Ship weight 14 lbs.
Warranty	6 years from date of purchase
CPSIA	Click here to view the safety compliances for this product under the Consumer Product Safety Improvement Act