



BOSCH



Bosch
WTE84106GB
Tumble dryer

Predecessor:
WTE84105GB

Successor:

EAN code:
4242002764603

sales programme:

Classixx 7

Condenser dryer
WTE84106GB

Performance

- Energy efficiency class: B
- Rated capacity for standard programme Cotton at full load: 7 kg
- Energy consumption 504.0 kWh per year, based on 160 drying cycles of the standard cotton programme at full and partial load, and the consumption of the low-power modes. Actual energy consumption per cycle will depend on how the appliance is used
- Energy consumption of the standard cotton programme at full load 4.2 kWh and energy consumption of the standard cotton programme at half load 2.3 kWh
- Programme time of the standard cotton programme at full load 124 min and programme time of the standard cotton programme at partial load 76 min.
- Condensation efficiency class B on a scale from G (least efficient) to A (most efficient).
- standard cotton programme at full load 89 % and average condensation efficiency of the standard cotton programme at partial load 89 %.
- Power consumption in off-mode 0.1 W and in left-on mode 1 W
- Duration of left-on mode: 30 min
- Noise level: 66 dB (A) re 1 pW

Programmes/functions

- Fully electronic control dial for sensor programmes and timed programmes
- Special programmes: Sportswear, Timed Programme 20 minutes warm, Super Quick 40
- Touch control buttons: Start/Stop, Low heat

Key features

- Sensitive drying: large galvanised drum and revolution drying system
- AntiVibration design: for greater stability and quietness

Additional features

- LED programme progress indicator and warning for fluff filter and condensed water container
- Anti crease cycle 120 minutes at the end of the programme
- Metal door catch

Technical Information

- Dimensions (H X W X D): 84.2 x 59.8 x 63.9 cm
- Can be built-under
- Large white Round solid door

Included accessories

Optional accessories

- WMZ20500 Platform with pull-out
- WTZ10290 Cover plate
- WTZ1110 Condenser drainage kit
- WTZ11300 Stacking kit with pullout shelf
- WTZ11310 Connection set

Technical Data

Characteristics

Built-in / Free-standing : Free-standing
Removable top : Yes
Door hinge : Right
Color / Material body : White
Length electrical supply cord (m) : 145.0
Height of removable worktop (mm) : 819
Dimensions of the product (mm) : 842 x 598 x 639
Net weight (kg) : 45
Drum volume (l) : 112

Consumption and connection features

Connection Rating (W) : 2600
Current (A) : 13
Voltage (V) : 220-240
Frequency (Hz) : 50
Approval certificates : CE, VDE
Drying process : automatic
Capacity cotton (kg) - NEW (2010/30/EC) : 7.0
Standard cotton programme : SCT
Energy efficiency class - NEW (2010/30/EC) : B
Energy consumption electric dryer, full load - NEW (2010/30/EC) : 4.20
Standard cotton programme time at full load : 124
Energy consumption electric dryer, partial load - NEW (2010/30/EC) : 2.30
Standard cotton programme time at partial load : 76
Weighted annual energy consumption, electric dryer - NEW (2010/30/EC) : 504.0

Power consumption in off-mode - NEW (2010/30/EC) : 0.10

Power consumption in left-on mode - NEW (2010/30/EC) : 1.00

Duration of the left-on mode - NEW (2010/30/EC) : 30

Weighted programme time : 97

Condensation efficiency class - NEW (2010/30/EC) : B

Average condensation efficiency full load : 89

Average condensation efficiency partial load : 89

Weighted condensation efficiency : 89

Alternative colors available



BOSCH

Classixx 7
Condenser dryer
WTE84106GB

