



2016 Starling 2 Series Product Brochure


Our most comprehensive electric projection screen lines. Its list of standard features include Infrared and Radio Frequency remote controls, 5-12 volt trigger and RS-232 capability, wall/ceiling mount kit, and extra top black masking leader.



Starling 2 Series



Our most comprehensive electric projection screen lines. Its list of complimentary standard features include Infrared and Radio Frequency remote controls, 5-12 volt trigger and RS-232 capability, wall/ceiling mount kit, and extra top black masking leader.



Screen Material:

- Spectra White FG (fiberglass backed) matte white surface
- 180° wide viewing angle with 1.1 Gain
- Active 3D and 4K Ultra HD Ready
- Standard black masking borders and black backing
- Diagonal sizes include 100", 120" and 135" in 16:9 HD format
- Extra top black border for high ceiling installation
- Flame Retardant: Complies with NFPA 701 Standards

Control System:

- Internal Radio Frequency/Infrared receivers with IR, RF remotes included
- Infrared IR "eye" extension sensor - ideal for concealed installation but still require infrared control
- 5-12 volt trigger capable for synchronized screen operation with the projector's power cycle
- Manual UP/DOWN buttons on exterior of case
- RS-232 capable for serial communication

Design and Installation:

- Steel case in white or black finish
- Includes pair of brackets and hardware for wall or ceiling installation
- Wall mountable remote control cradle included
- Plug & play, hardwire installation not required

Quality and Reliability

- Tubular motor allows swift operation with a superior weight tolerance and operational lifespan
- Low power consumption
- 2-year warranty from defects in workmanship
- 3rd year warranty offered through ENR-G program (Education, Non-Profit, Religious, and Government/Military)

