



SL-88-NV

NVIS-COMPLIANT BACKLIT KEYBOARD

The SL-88-NV has NVIS-compliant Green B backlighting. Constructed in a small-footprint compact case, the SL-88-NV allows for space saving and mobility, while NVIS backlighting makes this keyboard ideal for aviation or vehicle applications where night vision goggles are necessary. The new generation of SL-88-NV keyboards are specially designed to have night vision-friendly backlighting that eliminates the "bloom" effect of LED lights. The SL-88-NV includes a secondary legend accessed with NumLock and Fn keys. Feature: 12 Function Keys 88-Key Functionality NVIS Compliant - Green B backlighting Polycarbonate Case with Mounting Holes USB and PS/2 configurations available

Product Code SL-88-NV

CERTIFICATIONS	NEMA 4X UL60950, FCC Part 15 Class B
SHOCK	3x11 ms pulses of 50g on each of 3 axes
CABLE	LENGTH: 4 ft coiled (1.2m)
KEY SWITCH	MATERIAL: Industrial silicone rubber LIFE: 10 million cycles TRAVEL: 0.055 in. (1.4mm) ACTUATION FORCE: 7.05 oz +/- 0.71 oz (200g +/- 20g) FEEDBACK: Tactile with mechanical snap
VIBRATION	POWER SPECTRAL DENSITY: 0.04g/Hz FREQUENCY RANGE: 20Hz - 2 kHz DURATION OF TEST PER AXIS: 3 hours
POWER	PS2: Keyboard: 200mA@5V (from Keyboard port) USB: 200mA@5V (from CPU port)
FLAMMABILITY	PRINTED CIRCUIT BOARD: 94 VO SILICONE OVERLAY: 94 HB INTERFACE CABLE: 94 VO
COMPATABILITY	PS/2: All Windows Operating Systems USB: All Windows and Macintosh OS
TEMPERATURE RANGE	STORAGE: -40C to +90C (-40F to +194F) OPERATING: -40C to +70C (-40F to +158)
WEIGHT	2 lbs +/- 0.10 lbs (0.91 kg +/- 0.05 kg)
WARRANTY	1 year limited warranty
HUMIDITY	100%
DIMENSIONS	11.40" x 6.30" x 1.86" (w-h-d) 289.6mm x 160mm x 47.2mm
MODEL NUMBERS	SL-88-NV-PS2: With PS/2 cable SL-88-NV-USB: With USB cable SL-88-STD: With AT cable