


## 12-Outlet Power Strip with Surge Protection, 15 ft. (4.57 m) Cord, 1050 Joules, 36 in. length

MODEL NUMBER: **SS3612**



### Highlights

- 12 outlets
- 15-ft. (4.57 m) cord
- 36-in. length
- 1050-joule rating

### Package Includes

- SS3612 Power Strip/Surge Suppressor
- Set of adjustable mounting clips
- Warranty information
- Instruction manual

### Description

The SS3612 power strip with AC surge suppression offers a convenient method of horizontal or vertical power distribution in equipment racks, computer rooms, workbenches, raceways and more. Includes 12 NEMA 5-15R outlets with 2.48-in. center-to-center spacing, 15-ft. (4.57 m) AC line cord and adjustable mounting clips for installation in a wide variety of applications. Protects connected equipment from transient surges and line noise with built-in surge suppression rated at 1050 joules. This corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features rugged all-metal housing, lighted power switch with transparent guard to prevent accidental shutoff, 15A resettable circuit breaker and attractive gray housing with black output receptacles.

PLUG/OUTLETS: Input: NEMA 5-15P Output: 12 NEMA 5-15R

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)

FORMAT: 3-ft. corded vertical/raceway power distribution strip

SURGE SUPPRESSION: 1050 joules

### Features

- 3-ft. power strip with AC surge suppression offers a convenient method of horizontal or vertical power distribution in equipment racks, computer rooms, workbenches, raceways and more
- Protects connected equipment from transient surges and line noise with built-in surge suppression rated at 1050 joules
- 12 NEMA 5-15R outlets with 2.48-in. center-to-center spacing
- 15-ft. (4.57 m) AC line cord
- Adjustable mounting clips for installation in a wide variety of applications
- Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket



- Rugged all-metal housing
- Lighted power switch with transparent guard to prevent accidental shutoff
- 15A resettable circuit breaker
- Attractive gray housing with black output receptacles

## Specifications

| OVERVIEW                           |  |
|------------------------------------|--|
| UPC Code                           | 037332186409   |
| INPUT                              |  |
| Nominal Input Voltage(s) Supported | 120V AC  |
| Recommended Electrical Service     | 120V   |
| Voltage Compatibility (VAC)        | 120  |
| Maximum Surge Amps                 | 22000  |
| Input Plug Type                    | NEMA 5-15P   |
| Input Cord Length (ft.)            | 15   |
| Right-Angle Plug                   | No   |
| Input Cord Length (m)              | 4.57   |
| Integrated Cord Clip               | No   |
| OUTPUT                             |  |
| Frequency Compatibility            | 60 Hz  |
| Output (Watts)                     | 1800   |
| Output Receptacles                 | (12) 5-15R   |
| Circuit Breaker (amps)             | 15   |
| Outlet Spacing                     | 2.48-in. center-to-center spacing  |
| USER INTERFACE, ALERTS & CONTROLS  |  |
| Diagnostic LED(s)                  | No   |
| Switches                           | Combination AC circuit breaker and lighted 2-position power switch controls power to all outlets |
| Locking Switch Cover               | Transparent locking switch cover   |
| SURGE / NOISE SUPPRESSION          |  |
| AC Suppression Joule Rating        | 1050   |
| UL1449 Let Through Rating          | 500V UL verified   |
| Automatic Shut-Off                 | No   |



| <b>DATALINE SURGE SUPPRESSION</b>      |                                   |
|--|-----------------------------------|
| Telephone/DSL Protection               | No                                |
| Cable (Coax) Protection                | No                                |
| Network (Ethernet) Protection          | No                                |
| <b>PHYSICAL</b>                        |                                   |
| Color                                  | Silver                            |
| Antimicrobial Coating                  | No                                |
| Color (AC Line Cord)                   | Black                             |
| Included Mounting Accessories          | Set of adjustable mounting clamps |
| Integrated Keyhole Mounting Slots      | No                                |
| Outlets Measurement (Center to Center) | 2.48                              |
| Receptacle Color                       | Black                             |
| Shipping Dimensions (hwd / cm)         | 6.35 x 11.68 x 101.09             |
| Shipping Dimensions (hwd / in.)        | 2.50 x 4.60 x 39.80               |
| Shipping Weight (kg)                   | 1.77                              |
| Shipping Weight (lbs.)                 | 3.90                              |
| Unit Dimensions (hwd / cm)             | 3.18 x 4.11 x 91.44               |
| Unit Dimensions (hwd / in.)            | 1.25 x 1.62 x 36                  |
| <b>SPECIAL FEATURES</b>                |                                   |
| Rotatable Outlets                      | No                                |
| <b>STANDARDS &amp; COMPLIANCE</b>      |                                   |
| Canada                                 | cUL                               |
| UL1449 3rd Edition (AC Suppression)    | UL1449 3rd EDITION                |
| UL1363 (Power Tap)                     | UL1363                            |
| <b>WARRANTY</b>                        |                                   |
| Product Warranty Period (Worldwide)    | Lifetime limited warranty         |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>