

L850



DATASHEET



Easily print Epson-quality and low-cost photos from memory cards or directly from cameras using PictBridge with this A4 ITS photo printer. Ideal for photographers using these printers at events or in a studio, the L850 delivers reliable and high-quality photo printing together with more advanced functions such as a scanner, LCD display, and CD/DVD printing.

Ultra-low-cost photo printing

The L850 offers affordable printing and a low cost per print. Each set of ink bottles can print up to 1800 15x10cm photos¹, delivering an ultra-low cost per photo.

Easy to use and reliable

Increase productivity and reduce downtime with hassle-free set up and reliable printing. The purpose-built ink tank is fully integrated into the printer, so you can enjoy reliable colour printing without the mess or hassle often associated with non-genuine refills and third-party ink tank systems. Epson-genuine ink bottles make it easy to refill the ink tank with their clear labelling and drip-free nozzle. The L850 has 70ml ink tanks and comes with a 12 month (or 3,000 page) warranty, providing peace of mind and help should you need it. The 6.9cm LCD screen allows for easy and convenient printing and scanning without a PC.

Epson-quality printing

The L850 utilises genuine Epson ink and Epson's Micro Piezo technology to produce consistent-quality prints. Fast photo print speeds of approximately 12 seconds per 10x15cm photo² ensure that you won't be waiting around for print jobs.

KEY FEATURES

- **Epson Quality**
Purpose-built, refillable ink tank
- **Peace of mind**
Covered by Epson's warranty
- **PC-less printing**
Use the LCD screen to print from memory cards and cameras
- **Value for money**
Ultra-low-cost per print
- **User-friendly**
Hassle-free with simple set-up



PRODUCT SPECIFICATIONS

TECHNOLOGY

Printing Method	On-demand inkjet (Piezo electric)
Minimum Droplet Size	1.5 pl, With Variable-Sized Droplet Technology
Ink Technology	Dye Ink
Printing Resolution	5,760 x 1,440 dpi
All-in-One Functions	Print, Scan, Copy
Nozzle Configuration	90 Nozzles black, 90 Nozzles per colour

PRINT

Printing Speed ISO/IEC 24734	5 Pages/min Monochrome, 4.8 Pages/min Color
Maximum Printing Speed	12 Seconds per 10 x 15 cm photo (Epson Premium Glossy Photo Paper), 38 Pages/min Color (plain paper), 37 Pages/min Monochrome (plain paper)
Colours	Black, Cyan, Light Cyan, Yellow, Magenta, Light Magenta
For detailed information on printing speeds please visit http://www.epson.eu/testing .	

SCAN

Scanning Resolution	1,200 dpi x 2,400 dpi (Horizontal x Vertical)
Scanner type	Contact image sensor (CIS)

PAPER / MEDIA HANDLING

Number of paper trays	1
Paper Formats	A4, A5, A6, B5, C6 (Envelope), DL (Envelope), No. 10 (Envelope), Letter, 9 x 13 cm, 10 x 15 cm, 13 x 18 cm, 13 x 20 cm, 20 x 25 cm, 100 x 148 mm, 16:9, Legal
Duplex	Manual
Print Margin	0 mm top, 0 mm right, 0 mm bottom, 0 mm left (Wherever margin is defined. Otherwise 3mm top, left, right, bottom.)
Paper Tray Capacity	100 Sheets Standard, 100 Sheets maximum, 20 Photo Sheets
Media Handling	Borderless print, CD/DVD print

GENERAL

Energy Use	5.3 W (Ready), 0.4 W (Power off), ENERGY STAR® qualified, 12 W (standalone copying, ISO/IEC 24712 pattern), 1.6 W (sleep mode)
Product dimensions	542 x 386 x 196 mm (Width x Depth x Height)
Product weight	9.1 kg
Noise Level	5.1 B (A) with Epson Premium Glossy Photo Paper / Photo RPM mode - 37 dB (A) with Epson Premium Glossy Photo Paper / Photo RPM mode
Compatible Operating Systems	Mac OS 10.7.x, Mac OS 10.8.x, Mac OS 10.9.x, Mac OS X 10.6.8 or later, Windows 7, Windows 8, Windows 8.1, Windows Vista, Windows XP, XP Professional x64 Edition
Included Software	Epson Easy Photo Print, Epson Scan

OTHER FEATURES

LCD screen	Type: Color, Touch-panel, Diagonal: 6.9 cm
------------	--

LOGISTICS INFORMATION

SKU	C11CE31401
EAN code	8715946540474
Dimensions Single Carton	756 x 507 x 287 mm
Carton Weight	12.59 Kg
Country of Origin	Indonesia
Pallet Size Euro	14 Units (2 x 7)



* Warranty offers are not available for all countries. Please contact your local Epson representative.

For further information please contact your local Epson office or visit www.epson-europe.com
 Austria 01 253 49 78 333 Belgium +32 (0)2 792 04 47 Czech 800/142 052 Denmark 44 50 85 85 Finland 0201 552 091 France 09 74 75 04 04
 (Cost of local call, operator charges may apply) Germany +49 (0) 2159/92 79 500 Greece 210-8099499 Hungary 06800 147 83
 Ireland 01 436 7742 Italy 02-660321 10 (0,12 /min) Luxembourg +352 27860692 Middle East +971 4 8872172 Netherlands +31 (0)20 708 5099 Norway +47 67 11 37 00 Poland 0-0-800 4911299 (0,16 zł/min) Portugal 707 222 111 Russia (095) 777-03-55 Slovakia 0850 111 429
 South Africa (+2711) 465-9621 Spain 93 582 15 00 Sweden 0771-400135 (Mobilisamtal – 0,99 kr/min, Lokala samtal – 0,30 kr/min, Utlandssamtal – 0,89 kr/min) Switzerland 022 592 7923 Turkey (0212) 3360303 United Kingdom 0871 222 6702

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners.
 Product information is subject to change without prior notice.

L850

WHAT'S IN THE BOX

- 6 x 70ml individual ink bottles (Bk,C,Y,M,Lc,LM)
- Driver and utilities (CD)
- Main unit
- Power cable
- Setup guide

INK CARTRIDGE COMPATIBILITY

- T6731
- T6732
- T6735
- T6736
- T6733
- T6734



INK YIELD DATA



6-colour ink bottles for L-Series T6736

● 1,800 photos*

● ● ● ● 1,800 photos*

* Approx. page yield based on ISO/IEC 24711/24712 or ISO/IEC 29102/29103. Actual yield will vary depending on images printed and usage conditions. For more information visit <http://www.epson.eu/pageyield>

1. Quoted yields are extrapolated based on Epson original methodology from the print simulation of Test Patterns provided in ISO/IEC 29103. Quoted yields are NOT based on ISO/IEC 29102. Quoted yields may vary depending on the images that you are printing, the paper type that you are using, the frequency of your prints and environmental conditions such as temperature. 2. For test conditions, please visit www.epson.eu/testing

EPSON®