

HP MSR3000 TAA-Compliant Router Series



Product overview

The HP MSR3000 TAA-Compliant Router Series, the next generation of routers from HP, is a component of the HP FlexBranch solution. These routers feature a modular design that delivers unmatched application services for medium- to large-sized branch offices. Your IT personnel can benefit from reduced complexity and simplified configuration, deployment, and management.

The MSR3000 routers use the latest multicore CPUs, offer Gigabit switching, provide an enhanced PCI bus, and ship with the latest version of the HP Comware software to help ensure high performance with concurrent services. With these routers, you get a full-featured, resilient routing platform, including IPv6 and MPLS, with up to 2.6 Mp/s forwarding capacity and 1.9 Gb/s of IPSec VPN encrypted throughput. In addition, the routers support HP Open Application Platform (OAP) modules to deliver integrated industry-leading HP AllianceOne partner applications such as virtualization, unified communications and collaboration (UC&C), and application optimization capabilities.

Leveraging the MSR3000 series, you can realize an agile, flexible network infrastructure that enables you to quickly adapt to changing business requirements, while delivering integrated concurrent services on a single, easy-to-manage platform.

A summary of the highlights of the MSR3000 TAA-Compliant Router Series:

- Up to 2.6 Mp/s forwarding performance; support for multiple concurrent services
- OAP for HP AllianceOne applications such as WAN acceleration and Microsoft® Lync®
- Embedded security features with hardware-based encryption, firewall, network address translation (NAT), and VPNs
- No additional licensing complexity; no cost for advanced features
- Zero-touch solution with single-pane-of-glass management capabilities

Features and benefits

Performance

- Excellent forwarding performance

Provides forwarding performance up to 2.6 Mp/s (1.7 Gb/s); and meets the bandwidth-intensive application demands of enterprise businesses

- Powerful security capacity

Includes an embedded hardware encryption accelerator to improve encryption performance; the IPSec encryption throughput can be up to 1.9 Gb/s with a maximum of 4,000 IPSec VPN tunnels

Product architecture

- SDN/OpenFlow

OpenFlow is the communications interface defined between the control and forwarding layers of a Software-Defined Networking (SDN) architecture. OpenFlow separates the data forwarding and routing decision functions. It keeps the flow-based forwarding function and employs a separate controller to make routing decisions. OpenFlow matches packets against one or more flow tables. MSR support OpenFlow 1.3.1

- Ideal multiservice platform

Provides a WAN router, Ethernet switch, wireless LAN, 3G/4G WAN, firewall, VPN, and SIP/voice gateway—all in one device

- Advanced hardware architecture

Provides multicore processors, gigabit switching, PCIE bus, external RPS or dual internal power supplies, internal and external CF cards, and support for new high-performance MIM modules (HMIM)

- New version of the operating system

Ships with the new Comware 7 operating system, delivering the latest in virtualization and routing

- OAP architecture

Provides unmatched application and service flexibility, with the potential to deliver the functionality of multiple devices—creating capital and operational expense savings and lasting investment protection

- Field-programmable gate array (FPGA)

Improves the bandwidth of SIC module slots from 100 Mb/s to 1,000 Mb/s; and improves uplink performance from 1 Gb/s to 10 Gb/s

- Multi gigabit fabric (MGF)

Eases utilization of the main processor by transmitting L2 packets directly via the MGF

Connectivity

- Ethernet Virtual Interconnect (EVI)

EVI is a MAC-in-IP technology that provides Layer 2 connectivity between distant Layer 2 network sites across an IP routed network. It is used for connecting geographically dispersed sites of a virtualized large-scale data center that requires Layer 2 adjacency

- Virtual eXtensible LAN (VXLAN)

VXLAN (Virtual eXtensible LAN, scalable virtual local area network) is an IP-based network, using the “MAC in UDP” package of Layer VPN technology. VXLAN can be based on an existing ISP or enterprise IP networks for decentralized physical site provides Layer 2 communication, and can provide service isolation for different tenants

- Virtual Private LAN Service (VPLS)

VPLS delivers a point-to-multipoint L2VPN service over an MPLS or IP backbone. The backbone is transparent to the customer sites, which can communicate with each other as if they were on the same LAN. The following protocols support on MSRs, RFC4447, RFC4761, and RFC4762, BFD detection in VPLS, Support hierarchical HOPE (H-VPLS), MAC address recovery in H-VPLS to speed up convergence

- Network Mobility (NEMO)

NEMO enables a node to retain the same IP address and maintain application connectivity when the node travels across networks. It allows location-independent routing of IP datagrams on the Internet

- High-density port connectivity

Provides up to 6 interface module slots and up to three onboard Gigabit Ethernet ports

- Multiple WAN interfaces
Provides traditional links with E1, T1, serial, and ISDN; Offers high-density Ethernet access with WAN Gigabit Ethernet and LAN 4- and 9-port Fast Ethernet; and enables mobility access with the 3G SIC module, 3G/4G USB modems, and high-speed E3/T3 and 155 Mb/s OC3 access options
- Packet storm protection
Protects against broadcast, multicast, or unicast storms with user-defined thresholds
- Loopback
Supports internal loopback testing for maintenance purposes and an increase in availability; the loopback detection protects against incorrect cabling or network configurations, and it can be enabled on a per-port or per-VLAN basis for added flexibility
- 3G/4G LTE access support
Provides 3G wireless access for primary or backup connectivity via a 3G SIC module that's certified on various cellular networks; optional carrier 3G/4G LTE USB modems are also available
- USB interface
Uses USB memory disk to download and upload configuration/OS image files; and supports an external USB 3G/4G modem for a 3G/4G WAN uplink
- Flexible port selection
Provides a combination of fiber and copper interface modules, 100/1000BASE-X support, 10/100/1000BASE-T auto-speed detection plus auto duplex, and MDI/MDI-X

L2 switching

- Spanning tree protocol (STP)
Supports standard IEEE 802.1D STP, IEEE 802.1w Rapid STP (RSTP) for faster convergence and IEEE 802.1s Multiple STP (MSTP)
- Internet group management protocol (IGMP) and multicast listener discovery (MLD) protocol snooping
Controls and manages the flooding of multicast packets in an L2 network
- Port mirroring
Duplicates port traffic (ingress and egress) to a local or remote monitoring port
- VLANs
Supports up to 4,094 VLANs or IEEE 802.1Q-based VLANs
- sFlow®
Allows traffic sampling
- Capability to define port as switched or routed
Supports command switch to easily change switched ports to routed (maximum of four Fast Ethernet ports)

L3 routing

- Static IPv4 routing
Provides simple manually configured IPv4 routing
- Routing information protocol (RIP)
Uses a distance vector algorithm with UDP packets for route determination; supports RIPv1 and RIPv2 routing; and includes loop protection
- Open shortest path first (OSPF)
Delivers faster convergence; and uses link-state routing with the interior gateway protocol (IGP), which supports ECMP, NSSA, and MD5 authentication for increased security and graceful restart for faster failure recovery

- Border gateway protocol (BGP) 4
Delivers an implementation of the Exterior Gateway Protocol (EGP), utilizing path vectors; uses TCP for enhanced reliability for the route discovery process; reduces bandwidth consumption by advertising only incremental updates; supports extensive policies for increased flexibility; and scales to very large networks
- Intermediate system to intermediate system (IS-IS)
Uses a path-vector IGP, which is defined by the ISO organization for IS-IS routing and extended by IETF RFC 1195 to operate in both TCP/IP and the OSI reference model (integrated IS-IS)
- Static IPv6 routing
Provides simple manually configured IPv6 routing
- Dual IP stack
Maintains separate stacks for IPv4 and IPv6 to ease the transition from an IPv4-only network to an IPv6-only network
- RIP next generation (RIPng)
Extends RIPv2 to support IPv6 addressing
- OSPFv3
Provides OSPF support for IPv6
- BGP+
Extends BGP-4 to support Multiprotocol BGP (MP-BGP), including support for IPv6 addressing
- IS-IS for IPv6
Extends IS-IS to support IPv6 addressing
- IPv6 tunneling
Allows IPv6 packets to traverse IPv4-only networks by encapsulating the IPv6 packet into a standard IPv4 packet; supports manually configured, 6-to-4, and intra-site automatic tunnel addressing protocol (ISATAP) tunnels; and is an important element for the transition from IPv4 to IPv6
- Multiprotocol label switching (MPLS)
Uses BGP to advertise routes across label switched paths (LSPs); but uses simple labels to forward packets from any L2 or L3 protocol, which reduces complexity and increases performance; supports graceful restart for reduced failure impact; and supports LSP tunneling and multilevel stacks
- MPLS L3 VPN
Allows L3 VPNs across a provider network; uses MP-BGP to establish private routes for increased security; supports RFC2547bis multiple autonomous system VPNs for added flexibility; and supports IPv6 MPLS VPN
- MPLS L2 VPN
Establishes simple L2 point-to-point VPNs across a provider network, using only MPLS Label Distribution Protocol (LDP); requires no routing and hence decreases complexity, increases performance, and allows VPNs of non-routable protocols; uses no routing information for increased security; and supports circuit cross connect (CCC), static virtual circuits (SVCs), Martini draft, and Kompella-draft technologies
- Routing policy
Allows custom filters for increased performance and security; and supports ACLs, IP prefix, AS paths, community lists, and aggregate policies

L3 services

- WAN Optimization
MSR performs optimization using TFO and a combination of DRE, Lempel-Ziv (LZ) compression to provide the bandwidth optimization for file service and Web applications. The policy engine module determines which traffic can be optimized and which optimization action should be taken. A pair of WAN optimization equipment can discover each other automatically and complete the negotiation to establish a TCP optimization session.

- NAT-PT

Network Address Translation-Protocol Translation (NAT-PT) enables communication between IPv4 and IPv6 nodes by translating between IPv4 and IPv6 packets. It performs IP address translation, and according to different protocols, performs semantic translation for packets. This technology is only suitable for communication between a pure IPv4 node and a pure IPv6 node

- Address resolution protocol (ARP)

Determines the MAC address of another IP host in the same subnet; and supports static ARPs, gratuitous ARPs—allowing detection of duplicate IP addresses, and proxy ARPs—allowing normal ARP operation between subnets or when subnets are separated by an L2 network

- User datagram protocol (UDP) helper

Redirects UDP broadcasts to specific IP subnets to prevent server spoofing

- Dynamic host configuration protocol (DHCP)

Simplifies the management of large IP networks and supports client and server; DHCP relay enables DHCP operations across subnets

Quality of Service (QoS)

- Traffic policing

Supports the committed access rate (CAR) and line rate

- Congestion management

Supports FIFO, PQ, CQ, WFQ, CBQ, and RTPQ

- Weighted random early detection (WRED)/random early detection (RED)

Delivers congestion avoidance capabilities through the use of queue management algorithms

- Hierarchical QoS (HQoS)/Nested QoS

Manages traffic uniformly; hierarchically schedules traffic by user, network service, and application; and provides more granular traffic control and quality assurance services than traditional QoS

- Other QoS technologies

Supports traffic shaping, MPLS QoS, and MP QoS/LFI

Security

- Enhanced stateful firewall

Application layer protocol inspection, Transport layer protocol inspection, ICMP error message check, and TCP SYN check. Support more L4 and L7 protocols like TCP, UDP, UDP-Lite, ICMPv4/ICMPv6, SCTP, DCCP, RAWIP, HTTP, FTP, SMTP, DNS, SIP, H.323, SCCP.

- Zone based firewall

Zone-based policy firewall changes the firewall configuration from the older interface-based model to a more flexible, more easily understood zone-based model. Interfaces are assigned to zones, and inspection policy is applied to traffic moving between the zones. Inter-zone policies offer considerable flexibility and granularity, so different inspection policies can be applied to multiple host groups connected to the same router interface.

- Auto Discover VPN (ADVPN)

Collects, maintains, and distributes dynamic public addresses through the VPN Address Management (VAM) protocol, making VPN establishment available between enterprise branches that use dynamic addresses to access the public network; compared to traditional VPN technologies, ADVPN technology is more flexible and has richer features, such as NAT traversal of ADVPN packets, AAA identity authentication, IPSec protection of data packets, and multiple VPN domains

- IPsec VPN
Supports DES, 3DES, and AES 128/192/256 encryption and MD5 and SHA-1 authentication
- Access control list (ACL)
Supports powerful ACLs for both IPv4 and IPv6; ACLs are used for filtering traffic to prevent unauthorized users from accessing the network or for controlling network traffic to save resources; rules can either deny or permit traffic to be forwarded; rules can be based on an L2 or L3 protocol header; and rules can be set to operate on specific dates or times
- Terminal access controller access-control system (TACACS)
Delivers an authentication tool using TCP with encryption of the full authentication request, providing additional security
- Unicast reverse path forwarding (URPF)
Allows normal packets to be forwarded correctly, but discards the attaching packets due to the lack of a reverse path route or incorrect inbound interface; and prevents source spoofing and distributed attacks
- Network login
Allows authentication of multiple users per port
- RADIUS
Eases security access administration by using a user/password authentication server
- NAT
Supports one-to-one NAT, many-to-many NAT, and NAT control—enabling NAT-PT to support multiple connections; and also supports blacklist in NAT/NAT-PT—a limit on the number of connections, session logs, and multiple instances
- Secure shell (SSHv2)
Uses external servers to securely log in to a remote device; with authentication and encryption, it protects against IP spoofing and plain-text password interception; and increases the security of SFTP transfers

Convergence

- IGMP
Utilizes any-source multicast (ASM) or source-specific multicast (SSM) to manage IPv4 multicast networks; and supports IGMPv1, v2, and v3
- Protocol independent multicast (PIM)
Defines modes of Internet IPv4 and IPv6 multicasting to allow one-to-many and many-to-many transmission of information; and supports PIM Dense Mode (DM), Sparse Mode (SM), and Source-Specific Mode (SSM)
- Multicast source discovery protocol (MSDP)
Allows multiple PIM-SM domains to interoperate; and is used for inter-domain multicast applications
- Multicast BGP (MBGP)
Allows multicast traffic to be forwarded across BGP networks and kept separate from unicast traffic

Integration

- Embedded NetStream
Improves traffic distribution using powerful scheduling algorithms, including L4–7 services; and monitors the health status of servers and firewalls
- Embedded VPN and firewall
Provides enhanced stateful packet inspection and filtering; and delivers advanced VPN services with triple DES (3DES) and advanced encryption standard (AES) encryption at high performance and low latency, Web content filtering, and application prioritization and enhancement
- SIP trunking
Delivers multiple concurrent calls on one link; the carrier authenticates only the link, rather than carrying each SIP call on the link

Resiliency and high availability

• Intelligent Resilient Framework (IRF)

IRF allows the customer build an IRF stack, namely a logical device, by interconnecting multiple devices through stack ports. The customer can manage all the devices in the IRF stack by managing the logical device, which is cost-effective like a box-type device, and scalable and highly reliable like a chassis-type distributed device

• Backup Center

Acts as a part of the management and backup function to provide backup for device interfaces; and delivers reliability by switching traffic over to a backup interface when the primary one fails

• Virtual router redundancy protocol (VRRP)

Allows groups of two routers to dynamically back each other up to create highly available routed environments; and supports VRRP load balancing

• Embedded automation architecture (EAA)

Monitors the internal event and status of system hardware and software, identifying potential problems as early as possible; and collects field information and attempts to automatically repair the issues; based on the user configuration, onsite information will be sent to technical support

• Bidirectional forwarding detection (BFD)

Detects quickly the failures of the bidirectional forwarding paths between two devices for upper-layer protocols such as routing protocols and MPLS

Management

• HP Intelligent Management Center (IMC)

Integrates fault management, element configuration, and network monitoring from a central vantage point; has built-in support for third-party devices; and enables network administrators to centrally manage all network elements with a variety of automated tasks—including discovery, categorization, baseline configurations, and software images; the software also provides tools for configuration comparison, version tracking, change alerts, and more

• Industry-standard CLI with a hierarchical structure

Reduces training time and expenses; and increases productivity in multivendor installations

• Management security

Restricts access to critical configuration commands and offers multiple privilege levels with password protection; ACLs provide telnet and SNMP access; and local and remote syslog capabilities allow logging of all access

• SNMPv1, v2, and v3

Provide complete support for SNMP and industry-standard management information base (MIB) as well as private extensions; SNMPv3 supports increased security using encryption

• Remote monitoring

Uses standard SNMP to monitor essential network functions; and supports events, alarms, history, and a statistics group as well as a private alarm extension group

• FTP, trivial FTP (TFTP), and secure file transfer protocol (SFTP) support

Offers different mechanisms for configuration updates; FTP allows bidirectional transfers over a TCP/IP network; TFTP is a simpler method using UDP; and SFTP runs over an SSH tunnel to provide additional security

• Debug and sampler utility

Supports ping and traceroute for both IPv4 and IPv6

• Network time protocol (NTP)

Synchronizes timekeeping among distributed time servers and clients; and keeps timekeeping consistent among all clock-dependent devices within the network, so that the devices can provide diverse applications based on the consistent time

- Information center

Provides a central repository for system and network information; aggregates all logs, traps, and debugging information generated by the system and maintains them in the order of severity; and sends the network information to multiple channels, based on user-defined rules

- Management interface control

Provides management access through the modem port and terminal interface; and provides access through the terminal interface, telnet, or SSH

- Network quality analyzer (NQA)

Analyzes network performance and service quality by sending test packets; provides network performance and service quality parameters such as jitter, TCP, or FTP connection delays; and allows the network manager to determine overall network performance as well as diagnose and locate network congestion points or failures

- Role-based security

Delivers role-based access control (RBAC); and supports 16 user levels (0–15)

- Standards-based authentication support for LDAP

Integrates seamlessly into existing authentication services

Investment protection

- Re-use of existing SIC and MIM modules

Supports existing SIC and MIM modules, transceivers, and cables for investment protection

Ease of deployment

- Zero-touch deployment

Supports both USB disk auto deployment and 3G SMS auto deployment

Additional information

- OPEX savings

Simplifies and streamlines deployment, management, and training through the use of a common operating system—cutting costs as well as reducing the risk of human errors associated with having to manage multiple operating systems across different platforms and network layers

- Faster time to market

Allows new and custom features to be brought rapidly to market through engineering efficiencies, delivering better initial and ongoing stability

- Green initiative support

Provides support for RoHS and WEEE regulations

Warranty and support

- 1-year Warranty 2.0

Advance hardware replacement with 10-calendar-day delivery (available in most countries)

- Electronic and telephone support (for Warranty 2.0)

Limited electronic and 24x7 telephone support is available from HP for the entire warranty period; to reach our support centers, refer to hp.com/networking/contact-support; for details on the duration of the support provided with your product purchase, refer to hp.com/networking/warrantysummary

- Software releases

To find software for your product, refer to hp.com/networking/support; for details on the software releases available with your product purchase, refer to hp.com/networking/warrantysummary

HP MSR3000 TAA-Compliant Router Series

Specifications



HP MSR3024 TAA-Compliant AC Router (JG861A)

Ports	2 HMIM slots 4 SIC slots or 2 DSIC slots 1 VPM slot 3 RJ-45 1000BASE-T ports (IEEE 802.3ab Type 1000BASE-T) 1 SFP fixed Gigabit Ethernet SFP port
Physical characteristics	17.32(w) x 18.9(d) x 1.74(h) in. (44 x 48 x 4.42 cm) (1U height) Weight 17.42 lb (7.9 kg)
Memory and processor	RISC, 4 cores @ 1 GHz, 256 MB flash capacity, 2 GB DDR3 SDRAM
Mounting	Desktop or can be mounted on an EIA standard 19-inch telco rack when used with the rack-mount kit in the package
Performance	
Throughput	up to 2.6 Mp/s (64-byte packets)
Routing table size	500,000 entries (IPv4), 500,000 entries (IPv6)
Forwarding table size	500,000 entries (IPv4), 500,000 entries (IPv6)
Environment	
Operating temperature	32°F to 113°F (0°C to 45°C)
Operating relative humidity	5% to 90%, noncondensing
Nonoperating/storage temperature	-40°F to 158°F (-40°C to 70°C)
Nonoperating/storage relative humidity	5% to 90%, noncondensing
Altitude	up to 16,404 ft (5 km)

Electrical characteristics

Maximum heat dissipation	168 BTU/hr (177.24 kJ/hr)
Voltage	100–120/200–240 VAC
Maximum power rating	100 W
Frequency	50/60 Hz

Notes

Maximum power rating and maximum heat dissipation are the worst-case theoretical maximum numbers provided for planning the infrastructure with fully loaded PoE (if equipped), 100% traffic, all ports plugged in, and all modules populated.

Reliability

MTBF (years) 49.61

Safety

UL 60950-1; AS/NZS 60950; EN 60825-1 Safety of Laser Products-Part 1; EN 60825-2 Safety of Laser Products-Part 2; IEC 60950-1; CAN/CSA-C22.2 No. 60950-1-03; EN 60950-1/A11; FDA 21 CFR Subchapter J

Emissions

EN 55022 Class A; ICES-003 Class A; ANSI C63.4 2003; ETSI EN 300 386 V1.3.3; AS/NZS CISPR 22 Class A; EN 61000-4-2; EN 61000-4-3; EN 61000-4-4; EN 61000-4-5; EN 61000-4-6; EN 61000-3-2:2006; EN 61000-3-3:1995 +A1:2001+A2:2005; EMC Directive 2004/108/EC; FCC (CFR 47, Part 15) Class A; EN 55024:1998+ A1:2001 + A2:2003; EN61000-4-11:2004; EN 61000-4-8:2001

Telecom

FCC part 68; CS-03

Management

IMC; command-line interface; limited command-line interface; configuration menu; out-of-band management (RJ-45 Ethernet); SNMP Manager; Telnet; RMON1; FTP; in-line and out-of-band; modem interface; out-of-band management (serial RS-232C or Micro USB); IEEE 802.3 Ethernet MIB

Services

Refer to the HP website at hp.com/networking/services for details on the service-level descriptions and product numbers. For details about services and response times in your area, please contact your local HP sales office.

Standards and protocols

(applies to all products in series)

BGP	RFC 1163 BGP RFC 1267 BGP-3 RFC 1657 Definitions of Managed Objects for BGPv4 RFC 1771 BGPv4 RFC 1772 Application of the BGP RFC 1773 Experience with the BGP-4 Protocol RFC 1774 BGP-4 Protocol Analysis RFC 1965 BGP-4 confederations RFC 1997 BGP Communities Attribute RFC 3107 Support BGP carry Label for MPLS Mesh Internal BGP (IBGP) RFC 4724 Graceful Restart Mechanism for BGP	RFC 1998 PPP Gandalf FZA Compression Protocol RFC 2439 BGP Route Flap Damping RFC 2547 BGP/MPLS VPNs RFC 2796 BGP Route Reflection RFC 2842 Capability Advertisement with BGP-4 RFC 2858 BGP-4 Multi-Protocol Extensions RFC 2918 Route Refresh Capability RFC 3065 Autonomous System Confederations for BGP RFC 3392 Capabilities Advertisement with BGP-4	RFC 4271 A BGP-4 RFC 4273 Definitions of Managed Objects for BGP-4 RFC 4274 BGP-4 Protocol Analysis RFC 4275 BGP-4 MIB Implementation Survey RFC 4276 BGP-4 Implementation Report RFC 4277 Experience with the BGP-4 Protocol RFC 4360 BGP Extended Communities Attribute RFC 4456 BGP Route Reflection: An Alternative to Full
Denial of service protection	CPU DoS Protection Rate Limiting by ACLs		
Device management	RFC 1155 Structure and Management Information (SMIPv1) RFC 1902 (SNMPv2) RFC 2576 (Coexistence between SNMP V1, V2, V3) RFC 1157 SNMPv1/v2c	RFC 1908 (SNMP v1/2 Coexistence) RFC 2578–2580 SMIv2 RFC 1305 NTPv3 RFC 1945 Hypertext Transfer Protocol—HTTP/1.0 RFC 2579 (SMIPv2 Text Conventions)	RFC 1591 DNS (client) RFC 2271 Framework RFC 2580 (SMIPv2 Conformance) RFC 2573 (SNMPv3 Applications) RFC 3416 (SNMP Protocol Operations v2)
General protocols	RFC 768 UDP RFC 760 DoD standard Internet Protocol RFC 764 Telnet Protocol specification RFC 777 Internet Control Message Protocol RFC 783 TFTP Protocol (revision 2) RFC 791 IP RFC 792 ICMP RFC 793 TCP RFC 813 Window and Acknowledgement Strategy in TCP RFC 815 IP datagram reassembly algorithms RFC 826 ARP RFC 854 Telnet Protocol Specification RFC 855 Telnet Option Specifications RFC 856 Telnet Binary Transmission RFC 857 Telnet Echo Option RFC 858 Telnet Suppress Go Ahead Option RFC 862 Echo Service (TCP Echo) RFC 879 TCP maximum segment size and related topics RFC 882 Domain names: Concepts and facilities RFC 883 Domain names: Implementation specification RFC 894 A Standard for the Transmission of IP Datagrams over Ethernet Networks RFC 896 Congestion Control in IP/TCP Internetworks RFC 906 Bootstrap loading using TFTP (Trivial File Transfer Protocol) RFC 917 Internet Subnets RFC 919 Broadcasting Internet Datagrams RFC 922 Broadcasting Internet Datagrams in the Presence of Subnets (IP_BROAD)	RFC 925 Multi-LAN Address Resolution RFC 926 Protocol for providing the connectionless mode network services RFC 950 Internet Standard Subnetting Procedure RFC 951 BOOTP RFC 958 Network Time Protocol (NTP) RFC 959 File Transfer Protocol (FTP) RFC 973 Domain system changes and observations RFC 988 Host extensions for IP multicasting RFC 1027 Proxy ARP RFC 1034 Domain names—concepts and facilities RFC 1035 Domain names—implementation and specification RFC 1048 BOOTP (Bootstrap Protocol) vendor information extensions RFC 1054 Host extensions for IP multicasting RFC 1058 RIPv1 RFC 1059 Network Time Protocol (version 1) specification and implementation RFC 1060 Assigned numbers RFC 1063 IP MTU (Maximum Transmission Unit) discovery options RFC 1071 Computing the Internet Checksum RFC 1072 TCP extensions for long-delay paths RFC 1079 Telnet terminal speed option RFC 1084 BOOTP (Bootstrap Protocol) vendor information extensions RFC 1091 Telnet Terminal-Type Option RFC 1093 NSFNET routing architecture	RFC 1101 DNS encoding of network names and other types RFC 1119 Network Time Protocol (version 2) specification and implementation RFC 1122 Requirements for Internet Hosts—Communication Layers RFC 1141 Incremental updating of the Internet Checksum RFC 1142 OSI IS-IS Intra-domain Routing Protocol RFC 1164 Application of the Border Gateway Protocol in the Internet RFC 1166 Internet address used by Internet Protocol (IP) RFC 1171 Point-to-Point Protocol for the transmission of multi-protocol datagrams over Point-to-Point links RFC 1172 Point-to-Point Protocol (PPP) initial configuration options RFC 1185 TCP Extension for High-Speed Paths RFC 1191 Path MTU discovery RFC 1195 OSI ISIS for IP and Dual Environments RFC 1213 Management Information Base for Network Management of TCP/IP-based internets RFC 1253 (OSPF v2) RFC 1265 BGP Protocol Analysis RFC 1266 Experience with the BGP Protocol RFC 1268 Application of the Border Gateway Protocol in the Internet RFC 1271 Remote Network Monitoring Management Information Base

Standards and protocols (continued)

(applies to all products in series)

General protocols (continued)

RFC 1284 Definitions of Managed Objects for the Ethernet-like Interface Types	RFC 1549 PPP in HDLC Framing	RFC 1971 IPv6 Stateless Address Autoconfiguration
RFC 1286 Definitions of Managed Objects for Bridges	RFC 1570 PPP LCP (Point-to-Point Protocol Link Control Protocol) Extensions	RFC 1972 A Method for the Transmission of IPv6 Packets over Ethernet Networks
RFC 1294 Multiprotocol Interconnect over Frame Relay	RFC 1577 Classical IP and ARP over ATM	RFC 1981 Path MTU Discovery for IP version 6
RFC 1305 NTPv3 (IPv4 only)	RFC 1597 Address Allocation for Private Internets	RFC 1982 Serial Number Arithmetic
RFC 1321 The MD5 Message-Digest Algorithm	RFC 1618 PPP over ISDN	RFC 1989 PPP Link Quality Monitoring
RFC 1323 TCP Extensions for High Performance	RFC 1619 PPP over SONET/SDH (Synchronous Optical Network/Synchronous Digital Hierarchy)	RFC 1990 The PPP Multilink Protocol (MP)
RFC 1331 The Point-to-Point Protocol (PPP) for the Transmission of Multi-protocol Datagrams over Point-to-Point Links	RFC 1624 Incremental Internet Checksum	RFC 1994 PPP Challenge Handshake Authentication Protocol (CHAP)
RFC 1332 The PPP Internet Protocol Control Protocol (IPCP)	RFC 1631 NAT	RFC 2001 TCP Slow Start, Congestion Avoidance, Fast Retransmit, and Fast Recovery Algorithms
RFC 1333 PPP Link Quality Monitoring	RFC 1650 Definitions of Managed Objects for the Ethernet-like Interface Types using SMIv2	RFC 2002 IP Mobility Support
RFC 1334 PPP Authentication Protocols	RFC 1661 The Point-to-Point Protocol (PPP)	RFC 2003 IP Encapsulation within IP
RFC 1349 Type of Service	RFC 1662 PPP in HDLC-like Framing	RFC 2011 SNMPv2 Management Information Base for the Internet Protocol using SMIv2
RFC 1350 TFTP Protocol (revision 2)	RFC 1700 ASSIGNED NUMBERS	RFC 2012 SNMPv2 Management Information Base for the Transmission Control Protocol using SMIv2
RFC 1364 BGP OSPF Interaction	RFC 1701 Generic Routing Encapsulation	RFC 2013 SNMPv2 Management Information Base for the User Datagram Protocol using SMIv2
RFC 1370 Applicability Statement for OSPF	RFC 1702 Generic Routing Encapsulation over IPv4 networks	RFC 2018 TCP Selective Acknowledgement Options
RFC 1377 The PPP OSI Network Layer Control Protocol (OSINLCP)	RFC 1717 The PPP Multilink Protocol (MP)	RFC 2021 Remote Network Monitoring Management Information Base Version 2 using SMIv2
RFC 1393 Traceroute Using an IP Option	RFC 1721 RIP-2 Analysis	RFC 2073 An IPv6 Provider-Based Unicast Address Format
RFC 1395 BOOTP (Bootstrap Protocol) Vendor Information Extensions	RFC 1722 RIP-2 Applicability	RFC 2082 RIP-2 MD5 Authentication
RFC 1398 Definitions of Managed Objects for the Ethernet-Like Interface Types	RFC 1723 RIP v2	RFC 2091 Triggered Extensions to RIP to Support Demand Circuits
RFC 1403 BGP OSPF Interaction	RFC 1724 RIP Version 2 MIB Extension	RFC 2104 HMAC: Keyed-Hashing for Message Authentication
RFC 1444 Conformance Statements for version 2 of the Simple Network Management Protocol (SNMPv2)	RFC 1757 Remote Network Monitoring Management Information Base	RFC 2131 DHCP
RFC 1449 Transport Mappings for version 2 of the Simple Network Management Protocol (SNMPv2)	RFC 1777 Lightweight Directory Access Protocol	RFC 2132 DHCP Options and BOOTP Vendor Extensions
RFC 1471 The Definitions of Managed Objects for the Link Control Protocol of the Point-to-Point Protocol	RFC 1812 IPv4 Routing	RFC 2136 Dynamic Updates in the Domain Name System (DNS UPDATE)
RFC 1473 The Definitions of Managed Objects for the IP Network Control Protocol of the Point-to-Point Protocol	RFC 1825 Security Architecture for the Internet Protocol	RFC 2138 Remote Authentication Dial In User Service (RADIUS)
RFC 1483 Multiprotocol Encapsulation over ATM Adaptation Layer 5	RFC 1826 IP Authentication Header	RFC 2205 Resource ReSeRVation Protocol (RSVP)—Version 1 Functional Specification
RFC 1490 Multiprotocol Interconnect over Frame Relay	RFC 1827 IP Encapsulating Security Payload (ESP)	RFC 2209 Resource ReSeRVation Protocol (RSVP)—Version 1 Message Processing Rules
RFC 1497 BOOTP (Bootstrap Protocol) Vendor Information Extensions	RFC 1829 The ESP DES-CBC Transform	RFC 2210 Use of RSVP (Resource Reservation Protocol) in Integrated Services
RFC 1519 CIDR	RFC 1877 PPP Internet Protocol Control Protocol Extensions for Name Server Addresses	RFC 2225 Classical IP and ARP over ATM
RFC 1531 Dynamic Host Configuration Protocol	RFC 1884 IP Version 6 Addressing Architecture	RFC 2236 IGMP Snooping
RFC 1532 Clarifications and Extensions for the Bootstrap Protocol	RFC 1885 Internet Control Message Protocol (ICMPv6) for the Internet Protocol Version 6 (IPv6) Specification	RFC 2246 The TLS Protocol Version 1.0
RFC 1533 DHCP Options and BOOTP Vendor Extensions	RFC 1886 DNS Extensions to support IP version 6	RFC 2251 Lightweight Directory Access Protocol (v3)
RFC 1534 Interoperation Between DHCP and BOOTP	RFC 1889 RTP (Real-Time Protocol): A Transport Protocol for Real-Time Applications. Audio-Video Transport Working Group	RFC 2252 Lightweight Directory Access Protocol (v3): Attribute Syntax Definitions
RFC 1541 Dynamic Host Configuration Protocol	RFC 1933 Transition Mechanisms for IPv6 Hosts and Routers	RFC 2283 MBGP
RFC 1542 BOOTP Extensions	RFC 1945 Hypertext Transfer Protocol—HTTP/1.0	RFC 2292 Advanced Sockets API for IPv6
RFC 1542 Clarifications and Extensions for the Bootstrap Protocol	RFC 1962 The PPP Compression Control Protocol (CCP)	
RFC 1548 The Point-to-Point Protocol (PPP)	RFC 1966 BGP Route Reflection An alternative to full mesh IBGP	
	RFC 1970 Neighbor Discovery for IP Version 6 (IPv6)	

Standards and protocols (continued)

(applies to all products in series)

General protocols (continued)

RFC 2309 Recommendations on queue management and congestion avoidance in the Internet	RFC 2519 A Framework for Inter-Domain Route Aggregation	RFC 2866 RADIUS Accounting
RFC 2327 SDP: Session Description Protocol	RFC 2529 Transmission of IPv6 over IPv4 Domains without Explicit Tunnels	RFC 2868 RADIUS Attributes for Tunnel Protocol Support
RFC 2338 VRRP	RFC 2543 SIP: Session Initiation Protocol	RFC 2869 RADIUS Extensions
RFC 2344 Reverse Tunneling for Mobile IP	RFC 2548 (MS-RAS-Vendor only) Extensions for IPv6	RFC 2884 Performance Evaluation of Explicit Congestion Notification (ECN) in IP Networks.
RFC 2358 Definitions of Managed Objects for the Ethernet-like Interface Types	RFC 2553 Basic Socket Interface Extensions for IPv6	RFC 2894 Router Renumbering for IPv6
RFC 2364 PPP Over AAL5	RFC 2570 Introduction to Version 3 of the Internet-standard Network Management Framework	RFC 2917 A Core MPLS IP VPN Architecture
RFC 2365 Administratively Scoped IP Multicast	RFC 2581 TCP Congestion Control	RFC 2925 Definitions of Managed Objects for Remote Ping, Traceroute, and Lookup Operations
RFC 2373 IP Version 6 Addressing Architecture	RFC 2597 Assured Forwarding PHB Group	RFC 2961 RSVP Refresh Overhead Reduction Extensions
RFC 2374 An IPv6 Aggregatable Global Unicast Address Format	RFC 2598 An Expedited Forwarding PHB (Synchronous Optical Network/ Synchronous Digital Hierarchy)	RFC 2963 A Rate Adaptive Shaper for Differentiated Services
RFC 2375 IPv6 Multicast Address Assignments	RFC 2615 PPP over SONET/SDH	RFC 2965 HTTP State Management Mechanism
RFC 2385 Protection of BGP Sessions via the TCP MD5 Signature Option	RFC 2616 HTTP Compatibility v1.1	RFC 2966 Domain-wide Prefix Distribution with Two-Level IS-IS
RFC 2427 Multiprotocol Interconnect over Frame Relay	RFC 2617 HTTP Authentication: Basic and Digest Access Authentication	RFC 2973 IS-IS Mesh Groups
RFC 2428 FTP Extensions for IPv6 and NATs	RFC 2618 RADIUS Authentication Client MIB	RFC 2976 The SIP INFO Method
RFC 2433 Microsoft PPP CHAP (Challenge Handshake Authentication Protocol) Extensions	RFC 2620 RADIUS Accounting Client MIB	RFC 2993 Architectural Implications of NAT
RFC 2451 The ESP CBC-Mode Cipher Algorithms	RFC 2644 Changing the Default for Directed Broadcasts in Routers	RFC 3011 The IPv4 Subnet Selection Option for DHCP
RFC 2452 IP Version 6 Management Information Base for the Transmission Control Protocol	RFC 2661 L2TP	RFC 3022 Traditional IP Network Address Translator (Traditional NAT)
RFC 2453 RIPv2	RFC 2663 NAT Terminology and Considerations	RFC 3024 Reverse Tunneling for Mobile IP, revised
RFC 2454 IP Version 6 Management Information Base for the User Datagram Protocol	RFC 2665 Definitions of Managed Objects for the Ethernet-like Interface Types	RFC 3025 Mobile IP Vendor/ Organization-Specific Extensions
RFC 2461 Neighbor Discovery for IP Version 6 (IPv6)	RFC 2668 Definitions of Managed Objects for IEEE 802.3 Medium Attachment Units (MAUs)	RFC 3027 Protocol Complications with the IP Network Address Translator
RFC 2462 IPv6 Stateless Address Autoconfiguration	RFC 2675 IPv6 Jumbograms	RFC 3031 Multiprotocol Label Switching Architecture
RFC 2463 Internet Control Message Protocol (ICMPv6) for the Internet Protocol Version 6 (IPv6) Specification	RFC 2684 Multiprotocol Encapsulation over ATM Adaptation Layer 5	RFC 3032 MPLS Label Stack Encoding
RFC 2464 Transmission of IPv6 Packets over Ethernet Networks	RFC 2685 Virtual Private Networks Identifier	RFC 3036 LDP Specification
RFC 2465 Management Information Base for IP Version 6: Textual Conventions and General Group	RFC 2686 The Multi-Class Extension to Multi-Link PPP	RFC 3037 LDP (Label Distribution Protocol) Applicability
RFC 2466 Management Information Base for IP Version 6: ICMPv6 Group	RFC 2694 DNS extensions to Network Address Translators (DNS_ALG)	RFC 3041 Privacy Extensions for Stateless Address Autoconfiguration in IPv6
RFC 2472 IP Version 6 over PPP	RFC 2698 A Two Rate Three Color Marker	RFC 3046 DHCP Relay Agent Information Option
RFC 2474 Definition of the Differentiated Services Field (DS Field) in the IPv4 and IPv6 Headers	RFC 2702 Requirements for Traffic Engineering Over MPLS	RFC 3063 MPLS Loop Prevention Mechanism
RFC 2507 IP Header Compression	RFC 2711 IPv6 Router Alert Option	RFC 3097 RSVP (Resource Reservation Protocol) Cryptographic Authentication
RFC 2508 Compressing IP/UDP/RTP Headers for Low-Speed Serial Links	RFC 2716 PPP EAP TLS Authentication Protocol	RFC 3115 Mobile IP Vendor/ Organization-Specific Extensions
RFC 2509 IP Header Compression over PPP	RFC 2747 RSVP Cryptographic Authentication	RFC 3137 OSPF Stub Router Advertisement
RFC 2510 Internet X.509 Public Key Infrastructure Certificate Management Protocols	RFC 2763 Dynamic Name-to-System ID mapping	RFC 3168 The Addition of Explicit Congestion Notification (ECN) to IP
RFC 2516 A Method for Transmitting PPP Over Ethernet (PPPoE)	RFC 2784 Generic Routing Encapsulation (GRE)	RFC 3176 InMon Corporation's sFlow: A Method for Monitoring Traffic in Switched and Routed Networks
	RFC 2787 Definitions of Managed Objects for the Virtual Router Redundancy Protocol	RFC 3209 RSVP-TE: Extensions to RSVP for LSP Tunnels
	RFC 2827 Network Ingress Filtering: Defeating Denial of Service Attacks Which Employ IP Source Address Spoofing	RFC 3210 Applicability Statement for Extensions to RSVP for LSP-Tunnels
	RFC 2833 RTP Payload for DTMF Digits, Telephony Tones and Telephony Signals	
	RFC 2865 Remote Authentication Dial In User Service (RADIUS)	

Standards and protocols (continued)

(applies to all products in series)

General protocols (continued)

<p>RFC 3215 LDP State Machine</p> <p>RFC 3220 IP Mobility Support for IPv4</p> <p>RFC 3246 Expedited Forwarding PHB</p> <p>RFC 3261 SIP: Session Initiation Protocol</p> <p>RFC 3262 Reliability of Provisional Responses in Session Initiation Protocol (SIP)</p> <p>RFC 3263 Session Initiation Protocol (SIP): Locating SIP Servers</p> <p>RFC 3265 Session Initiation Protocol (SIP)-Specific Event Notification</p> <p>RFC 3268 Advanced Encryption Standard (AES) Ciphersuites for Transport Layer Security (TLS)</p> <p>RFC 3270 Multi-Protocol Label Switching (MPLS) Support of Differentiated Services</p> <p>RFC 3273 Remote Network Monitoring Management Information Base for High Capacity Networks</p> <p>RFC 3277 IS-IS Transient Blackhole Avoidance</p> <p>RFC 3279 Algorithms and Identifiers for the Internet X.509 Public Key Infrastructure Certificate and Certificate Revocation List (CRL) Profile</p> <p>RFC 3280 Internet X.509 Public Key Infrastructure Certificate and Certificate Revocation List (CRL) Profile</p> <p>RFC 3306 Unicast-Prefix-based IPv6 Multicast Addresses</p> <p>RFC 3307 Allocation Guidelines for IPv6 Multicast Addresses</p> <p>RFC 3311 The Session Initiation Protocol (SIP) UPDATE Method</p> <p>RFC 3319 Dynamic Host Configuration Protocol (DHCPv6) Options for Session Initiation Protocol (SIP) Servers</p> <p>RFC 3323 A Privacy Mechanism for the Session Initiation Protocol (SIP)</p> <p>RFC 3325 Private Extensions to the Session Initiation Protocol (SIP) for Asserted Identity within Trusted Networks</p> <p>RFC 3326 The Reason Header Field for the Session Initiation Protocol (SIP)</p> <p>RFC 3344 IP Mobility Support for IPv4</p> <p>RFC 3345 Border Gateway Protocol (BGP) Persistent Route Oscillation Condition</p> <p>RFC 3359 Reserved Type, Length and Value (TLV) Codepoints in Intermediate System to Intermediate System</p> <p>RFC 3373 Three-Way Handshake for Intermediate System to Intermediate System (IS-IS) Point-to-Point Adjacencies</p> <p>RFC 3392 Support BGP capabilities advertisement</p> <p>RFC 3410 Introduction to Version 3 of the Internet-standard Network Management Framework</p> <p>RFC 3442 The Classless Static Route Option for Dynamic Host Configuration Protocol (DHCP) version 4</p> <p>RFC 3443 Time To Live (TTL) Processing in Multi-Protocol Label Switching (MPLS) Networks</p>	<p>RFC 3446 Anycast Rendezvous Point (RP) mechanism using Protocol Independent Multicast (PIM) and Multicast Source Discovery Protocol (MSDP)</p> <p>RFC 3478 Graceful Restart Mechanism for Label Distribution Protocol</p> <p>RFC 3479 Fault Tolerance for the Label Distribution Protocol (LDP)</p> <p>RFC 3484 Default Address Selection for Internet Protocol version 6 (IPv6)</p> <p>RFC 3493 Basic Socket Interface Extensions for IPv6</p> <p>RFC 3495 Dynamic Host Configuration Protocol (DHCP) Option for CableLabs Client Configuration</p> <p>RFC 3509 OSPF ABR Behavior</p> <p>RFC 3513 Internet Protocol Version 6 (IPv6) Addressing Architecture</p> <p>RFC 3515 The Session Initiation Protocol (SIP) Refer Method</p> <p>RFC 3526 More Modular Exponential (MODP) Diffie-Hellman groups for Internet Key Exchange (IKE)</p> <p>RFC 3527 Link Selection sub-option for the Relay Agent Information Option for DHCPv4</p> <p>RFC 3542 Advanced Sockets Application Program Interface (API) for IPv6</p> <p>RFC 3547 The Group Domain of Interpretation</p> <p>RFC 3564 Requirements for Support of Differentiated Services-aware MPLS Traffic Engineering</p> <p>RFC 3567 Intermediate System to Intermediate System (IS-IS) Cryptographic Authentication</p> <p>RFC 3569 An Overview of Source-Specific Multicast (SSM)</p> <p>RFC 3584 Coexistence between Version 1 and Version 2 of the Internet-standard Network Management Framework</p> <p>RFC 3587 IPv6 Global Unicast Address Format</p> <p>RFC 3590 Source Address Selection for the Multicast Listener Discovery (MLD) Protocol</p> <p>RFC 3596 DNS Extensions to Support IP Version 6</p> <p>RFC 3602 The AES-CBC Cipher Algorithm and Its Use with IPsec</p> <p>RFC 3612 Applicability Statement for Restart Mechanisms for the Label Distribution Protocol (LDP)</p> <p>RFC 3618 Multicast Source Discovery Protocol (MSDP)</p> <p>RFC 3621 Power Ethernet MIB</p> <p>RFC 3623 Graceful OSPF Restart</p> <p>RFC 3630 Traffic Engineering (TE) Extensions to OSPF Version 2</p> <p>RFC 3636 Definitions of Managed Objects for IEEE 802.3 Medium Attachment Units (MAUs)</p> <p>RFC 3646 DNS Configuration options for Dynamic Host Configuration Protocol for IPv6 (DHCPv6)</p>	<p>RFC 3662 A Lower Effort Per-Domain Behavior (PDB) for Differentiated Services</p> <p>RFC 3704 Unicast Reverse Path Forwarding (URPF)</p> <p>RFC 3706 A Traffic-Based Method of Detecting Dead Internet Key Exchange (IKE) Peers</p> <p>RFC 3711 The Secure Real-time Transport Protocol (SRTP)</p> <p>RFC 3719 Recommendations for Interoperable Networks using Intermediate System to Intermediate System (IS-IS)</p> <p>RFC 3736 Stateless Dynamic Host Configuration Protocol (DHCP) Service for IPv6</p> <p>RFC 3737 IANA Guidelines for the Registry of Remote Monitoring (RMON) MIB (Management Information Base) modules</p> <p>RFC 3768 Virtual Router Redundancy Protocol (VRRP)</p> <p>RFC 3782 The NewReno Modification to TCP's Fast Recovery Algorithm</p> <p>RFC 3784 Intermediate System to Intermediate System (IS-IS) Extensions for Traffic Engineering (TE)</p> <p>RFC 3786 Extending the Number of IS-IS LSP Fragments Beyond the 256 Limit</p> <p>RFC 3787 Recommendations for Interoperable IP Networks using Intermediate System to Intermediate System (IS-IS)</p> <p>RFC 3809 Generic Requirements for Provider Provisioned Virtual Private Networks (VPNs)</p> <p>RFC 3810 Multicast Listener Discovery Version 2 (MLDv2) for IPv6</p> <p>RFC 3811 Definitions of Textual Conventions (TCs) for Multiprotocol Label Switching (MPLS) Management</p> <p>RFC 3812 Multiprotocol Label Switching (MPLS) Traffic Engineering (TE) Management Information Base (MIB)</p> <p>RFC 3814 Multiprotocol Label Switching (MPLS) Forwarding Equivalence Class To Next Hop Label Forwarding Entry (FEC-To-NHLFE) Management Information Base (MIB)</p> <p>RFC 3815 Definitions of Managed Objects for the Multiprotocol Label Switching (MPLS), Label Distribution Protocol (LDP)</p> <p>RFC 3826 The Advanced Encryption Standard (AES) Cipher Algorithm in the SNMP User-based Security Model</p> <p>RFC 3847 Restart signaling for IS-IS</p> <p>RFC 3879 Deprecating Site Local Addresses</p> <p>RFC 3898 Network Information Service (NIS) Configuration Options for Dynamic Host Configuration Protocol for IPv6 (DHCPv6)</p>
---	---	--

Standards and protocols (continued)

(applies to all products in series)

General protocols (continued)

RFC 3906 Calculating Interior Gateway Protocol (IGP) Routes Over Traffic Engineering Tunnels	RFC 4242 Information Refresh Time Option for Dynamic Host Configuration Protocol for IPv6 (DHCPv6)	RFC 4447 Pseudowire Setup and Maintenance Using the Label Distribution Protocol (LDP)
RFC 3916 Requirements for Pseudo-Wire Emulation Edge-to-Edge (PWE3)	RFC 4244 An Extension to the Session Initiation Protocol (SIP) for Request History Information	RFC 4448 Encapsulation Methods for Transport of Ethernet over MPLS Networks
RFC 3917 Requirements for IP Flow Information Export (IPFIX)	RFC 4250 The Secure Shell (SSH) Protocol Assigned Numbers	RFC 4451 BGP MULTI_EXIT_DISC (MED) Considerations
RFC 3942 Reclassifying Dynamic Host Configuration Protocol version 4 (DHCPv4) Options	RFC 4251 The Secure Shell (SSH) Protocol Architecture	RFC 4486 Subcodes for BGP Cease Notification Message
RFC 3948 UDP Encapsulation of IPsec ESP Packets	RFC 4252 The Secure Shell (SSH) Authentication Protocol	RFC 4502 Remote Network Monitoring Management Information Base Version 2
RFC 3954 Cisco Systems NetFlow Services Export Version 9	RFC 4253 The Secure Shell (SSH) Transport Layer Protocol	RFC 4541 Considerations for Internet Group Management Protocol (IGMP) and Multicast Listener Discovery (MLD) Snooping Switches
RFC 3973 Protocol Independent Multicast-Dense Mode (PIM-DM): Protocol Specification (Revised)	RFC 4254 The Secure Shell (SSH) Connection Protocol	RFC 4552 Authentication/Confidentiality for OSPFv3
RFC 3985 Pseudo Wire Emulation Edge-to-Edge (PWE3) Architecture	RFC 4272 BGP Security Vulnerabilities Analysis	RFC 4553 Structure-Agnostic Time Division Multiplexing (TDM) over Packet (SAToP)
RFC 4022 Management Information Base for the Transmission Control Protocol (TCP)	RFC 4291 IP Version 6 Addressing Architecture	RFC 4561 Definition of a Record Route Object (RRO) Node-Id sub-Objects
RFC 4023 Encapsulating MPLS in IP or Generic Routing Encapsulation (GRE)	RFC 4292 IP Forwarding Table MIB	RFC 4562 MAC-Forced Forwarding: A Method for Subscriber Separation on an Ethernet Access Network
RFC 4026 Provider Provisioned VPN terminology	RFC 4293 Management Information Base for the Internet Protocol (IP)	RFC 4568 Session Description Protocol (SDP) Security Descriptions for Media Streams
RFC 4061 Benchmarking Basic OSPF Single Router Control Plane Convergence	RFC 4294 IPv6 Node Requirements	RFC 4576 Using a Link State Advertisement (LSA) Options Bit to Prevent Looping in BGP/MPLS IP Virtual Private Networks (VPNs)
RFC 4062 OSPF Benchmarking Terminology and Concepts	RFC 4305 Cryptographic Algorithm Implementation Requirements for Encapsulating Security Payload (ESP) and Authentication Header (AH)	RFC 4577 OSPF as the Provider/Customer Edge Protocol for BGP/MPLS IP Virtual Private Networks (VPNs)
RFC 4063 Considerations When Using Basic OSPF Convergence Benchmarks	RFC 4306 Internet Key Exchange (IKEv2) Protocol	RFC 4594 Configuration Guidelines for DiffServ Service Classes
RFC 4075 Simple Network Time Protocol (SNTP) Configuration Option for DHCPv6	RFC 4308 Cryptographic Suites for IPsec	RFC 4601 Protocol Independent Multicast - Sparse Mode (PIM-SM): Protocol Specification (Revised)
RFC 4090 Fast Reroute Extensions to RSVP-TE for LSP Tunnels	RFC 4361 Node-specific Client Identifiers for Dynamic Host Configuration Protocol Version Four (DHCPv4)	RFC 4604 Using Internet Group Management Protocol Version 3 (IGMPv3) and Multicast Listener Discovery Protocol Version 2 (MLDv2) for Source-Specific Multicast
RFC 4105 Requirements for Inter-Area MPLS Traffic Engineering	RFC 4364 BGP/MPLS IP Virtual Private Networks (VPNs)	RFC 4605 Internet Group Management Protocol (IGMP)/Multicast Listener Discovery (MLD)-Based Multicast Forwarding ("IGMP/MLD Proxying")
RFC 4109 Algorithms for Internet Key Exchange version 1 (IKEv1)	RFC 4365 Applicability Statement for BGP/MPLS IP Virtual Private Networks (VPNs)	RFC 4607 Source-Specific Multicast for IP
RFC 4113 Management Information Base for the User Datagram Protocol (UDP)	RFC 4377 Operations and Management (OAM) Requirements for Multi-Protocol Label Switched (MPLS) Networks	RFC 4608 Source-Specific Protocol Independent Multicast in 232/8
RFC 4124 Protocol Extensions for Support of DiffServ-aware MPLS Traffic Engineering	RFC 4381 Analyses of the Security of BGP/MPLS IP VPNs	RFC 4610 Anycast-RP Using Protocol Independent Multicast (PIM)
RFC 4125 Maximum Allocation Bandwidth Constraints Model for DiffServ-aware MPLS Traffic Engineering	RFC 4382 MPLS/BGP Layer 3 Virtual Private Network (VPN) Management Information Base	RFC 4618 Encapsulation Methods for Transport of PPP/High-Level Data Link Control (HDLC) over MPLS Networks
RFC 4127 Russian Dolls Bandwidth Constraints Model for DiffServ-aware MPLS Traffic Engineering	RFC 4384 BGP Communities for Data Collection	RFC 4619 Encapsulation Methods for Transport of Frame Relay over Multiprotocol Label Switching (MPLS) Networks
RFC 4133 Entity MIB (Version 3)	RFC 4385 Pseudowire Emulation Edge-to-Edge (PWE3) Control Word for Use over an MPLS PSN	RFC 4632 Classless Inter-domain Routing (CIDR): The Internet Address Assignment and Aggregation Plan
RFC 4182 Removing a Restriction on the use of MPLS Explicit NULL	RFC 4419 Diffie-Hellman Group Exchange for the Secure Shell (SSH) Transport Layer Protocol	
RFC 4213 Basic Transition Mechanisms for IPv6 Hosts and Routers	RFC 4443 Internet Control Message Protocol (ICMPv6) for the Internet Protocol Version 6 (IPv6) Specification	
RFC 4214 Intra-Site Automatic Tunnel Addressing Protocol (ISATAP)	RFC 4444 Management Information Base for Intermediate System to Intermediate System (IS-IS)	
RFC 4221 Multiprotocol Label Switching (MPLS) Management Overview	RFC 4446 IANA Allocations for Pseudowire Edge-to-Edge Emulation (PWE3)	
RFC 4222 Prioritized Treatment of Specific OSPF Version 2 Packets and Congestion Avoidance		

Standards and protocols (continued)

(applies to all products in series)

General protocols (continued)

<p>RFC 4649 Dynamic Host Configuration Protocol for IPv6 (DHCPv6) Relay Agent Remote-ID Option</p> <p>RFC 4659 BGP-MPLS IP Virtual Private Network (VPN) Extension for IPv6 VPN</p> <p>RFC 4664 Framework for Layer 2 Virtual Private Networks (L2VPNs)</p> <p>RFC 4665 Service Requirements for Layer 2 Provider-Provisioned Virtual Private Networks</p> <p>RFC 4717 Encapsulation Methods for Transport of Asynchronous Transfer Mode (ATM) over MPLS Networks</p> <p>RFC 4741 NETCONF Configuration Protocol</p> <p>RFC 4742 Using the NETCONF Configuration Protocol over Secure Shell (SSH)</p> <p>RFC 4743 Using NETCONF over the Simple Object Access Protocol (SOAP)</p> <p>RFC 4750 OSPF Version 2 Management Information Base</p> <p>RFC 4761 Virtual Private LAN Service (VPLS) Using BGP for Auto-Discovery and Signaling</p> <p>RFC 4765 Service Requirements for Layer 2 Provider Provisioned Virtual Private Networks</p> <p>RFC 4781 Graceful Restart Mechanism for BGP with MPLS</p> <p>RFC 4787 Network Address Translation (NAT) Behavioral Requirements for Unicast UDP</p> <p>RFC 4797 Use of Provider Edge to Provider Edge (PE-PE) Generic Routing Encapsulation (GRE) or IP in BGP/MPLS IP Virtual Private Networks</p> <p>RFC 4798 Connecting IPv6 Islands over IPv4 MPLS Using IPv6 Provider Edge Routers (6PE)</p> <p>RFC 4811 OSPF Out-of-Band Link State Database (LSDB) Resynchronization</p> <p>RFC 4812 OSPF Restart Signaling</p> <p>RFC 4813 OSPF Link-Local Signaling</p> <p>RFC 4816 Pseudowire Emulation Edge-to-Edge (PWE3) Asynchronous Transfer Mode (ATM) Transparent Cell Transport Service</p> <p>RFC 4818 RADIUS Delegated-IPv6-Prefix Attribute</p> <p>RFC 4835 Cryptographic Algorithm Implementation Requirements for Encapsulating Security Payload (ESP) and Authentication Header (AH)</p> <p>RFC 4861 Neighbor Discovery for IP version 6 (IPv6)</p> <p>RFC 4862 IPv6 Stateless Address Autoconfiguration</p> <p>RFC 4878 Definitions and Managed Objects for Operations, Administration, and Maintenance (OAM) Functions on</p> <p>RFC 4893 BGP Support for Four-octet AS Number Space</p> <p>RFC 4940 IANA Considerations for OSPF</p>	<p>RFC 4941 Privacy Extensions for Stateless Address Autoconfiguration in IPv6</p> <p>RFC 5004 Avoid BGP Best Path Transitions from One External to Another</p> <p>RFC 5007 DHCPv6 Leasequery</p> <p>RFC 5015 Bidirectional Protocol Independent Multicast (BIDIR-PIM)</p> <p>RFC 5036 LDP Specification</p> <p>RFC 5060 Protocol Independent Multicast MIB</p> <p>RFC 5065 Autonomous System Confederations for BGP</p> <p>RFC 5072 IP Version 6 over PPP</p> <p>RFC 5082 The Generalized TTL Security Mechanism (GTSM)</p> <p>RFC 5085 Pseudowire Virtual Circuit Connectivity Verification (VCCV): A Control Channel for Pseudowires</p> <p>RFC 5086 Structure-Aware Time Division Multiplexed (TDM) Circuit Emulation Service over Packet Switched Network (CESoPSN)</p> <p>RFC 5095 Deprecation of Type 0 Routing Headers in IPv6</p> <p>RFC 5120 M-ISIS: Multi Topology (MT) Routing in Intermediate System to Intermediate Systems (IS-ISs)</p> <p>RFC 5130 A Policy Control Mechanism in IS-IS Using Administrative Tags</p> <p>RFC 5132 IP Multicast MIB</p> <p>RFC 5187 OSPFv3 Graceful Restart</p> <p>RFC 5214 Intra-Site Automatic Tunnel Addressing Protocol (ISATAP)</p> <p>RFC 5240 Protocol Independent Multicast (PIM) Bootstrap Router MIB</p> <p>RFC 5254 Requirements for Multi-Segment Pseudowire Emulation Edge-to-Edge (PWE3)</p> <p>RFC 5277 NETCONF Event Notifications</p> <p>RFC 5280 Internet X.509 Public Key Infrastructure Certificate and Certificate Revocation List (CRL) Profile</p> <p>RFC 5281 Extensible Authentication Protocol Tunneled Transport Layer Security Authenticated Protocol Version 0 (EAP-TLSv0)</p> <p>RFC 5286 Basic Specification for IP Fast Reroute: Loop-Free Alternates</p> <p>RFC 5287 Control Protocol Extensions for the Setup of Time-Division Multiplexing (TDM) Pseudowires in MPLS Networks</p> <p>RFC 5301 Dynamic Hostname Exchange Mechanism for IS-IS</p> <p>RFC 5302 Domain-Wide Prefix Distribution with Two-Level IS-IS</p> <p>RFC 5303 Three-Way Handshake for IS-IS Point-to-Point Adjacencies</p> <p>RFC 5304 Intermediate System to Intermediate System (IS-IS) Cryptographic Authentication</p> <p>RFC 5305 IS-IS Extensions for Traffic Engineering</p> <p>RFC 5306 Restart Signaling for IS-IS</p> <p>RFC 5308 Routing IPv6 with IS-IS</p>	<p>RFC 5309 Point-to-Point Operation over LAN in Link State Routing Protocols</p> <p>RFC 5310 IS-IS Generic Cryptographic Authentication</p> <p>RFC 5359 Session Initiation Protocol Service Examples</p> <p>RFC 5381 Experience of Implementing NETCONF over SOAP</p> <p>RFC 5382 The IP Network Address Translator (NAT)</p> <p>RFC 5398 Autonomous System (AS) Number Reservation for Documentation Use</p> <p>RFC 5415 Control And Provisioning of Wireless Access Points (CAPWAP) Protocol Specification</p> <p>RFC 5416 Control and Provisioning of Wireless Access Points (CAPWAP) Protocol Binding for IEEE 802.11</p> <p>RFC 5443 LDP IGP Synchronization</p> <p>RFC 5492 Capabilities Advertisement with BGP-4</p> <p>RFC 5496 The Reverse Path Forwarding (RPF) Vector TLV</p> <p>RFC 5508 NAT Behavioral Requirements for ICMP</p> <p>RFC 5539 NETCONF over Transport Layer Security (TLS)</p> <p>RFC 5601 Pseudowire (PW) Management Information Base (MIB)</p> <p>RFC 5602 Pseudowire (PW) over MPLS PSN Management Information Base (MIB)</p> <p>RFC 5613 OSPF Link-Local Signaling</p> <p>RFC 5659 An Architecture for Multi-Segment Pseudowire Emulation Edge-to-Edge</p> <p>RFC 5681 TCP Congestion Control</p> <p>RFC 5798 Virtual Router Redundancy Protocol (VRRP) Version 3 for IPv4 and IPv6</p> <p>RFC 5833 Control and Provisioning of Wireless Access Points (CAPWAP) Protocol Base MIB</p> <p>RFC 5834 Control and Provisioning of Wireless Access Points (CAPWAP) Protocol Binding MIB for IEEE 802.11</p> <p>RFC 5880 Bidirectional Forwarding Detection</p> <p>RFC 5881 BFD for IPv4 and IPv6 (Single Hop)</p> <p>RFC 5881 Bidirectional Forwarding Detection (BFD) for IPv4 and IPv6 (Single Hop)</p> <p>RFC 5882 Generic Application of BFD</p> <p>RFC 5883 BFD for Multihop Paths</p> <p>RFC 5905 Network Time Protocol Version 4: Protocol and Algorithms Specification</p> <p>RFC 5969 IPv6 Rapid Deployment on IPv4 Infrastructures (6RD)—Protocol Specification</p> <p>RFC 6037 Cisco Systems' Solution for Multicast in MPLS/BGP IP VPNs</p> <p>RFC 6085 Address Mapping of IPv6 Multicast Packets on Ethernet</p>
--	---	--

Standards and protocols (continued)

(applies to all products in series)

IP multicast	<p>RFC 1112 IGMP RFC 2710 MLD for IPv6 RFC 3376 IGMPv3 (host joins only) RFC 2362 PIM Sparse Mode RFC 2934 PIM MIB for IPv4 RFC 5059 Bootstrap Router (BSR) Mechanism for RFC 3376 IGMPv3 PIM</p>
IPv6	<p>RFC 2080 RIPng for IPv6 RFC 2529 Transmission of IPv6 Packets over IPv4 RFC 2893 Transition Mechanisms for IPv6 Hosts and RFC 2460 IPv6 Specification RFC 2545 Use of MP-BGP-4 for IPv6 RFC 2473 Generic Packet Tunneling in IPv6 RFC 2553 Basic Socket Interface Extensions for IPv6 RFC 2475 IPv6 DiffServ Architecture RFC 2740 OSPFv3 for IPv6 Routers RFC 3056 Connection of IPv6 Domains via IPv4 Clouds RFC 3162 RADIUS and IPv6 RFC 3315 DHCPv6 (client and relay) RFC 5340 OSPF for IPv6</p>
MIBs	<p>RFC 1213 MIB II RFC 2012 SNMPv2 MIB for TCP RFC 2573 SNMP-Notification MIB RFC 1493 Bridge MIB RFC 2013 SNMPv2 MIB for UDP RFC 2574 SNMP USM MIB RFC 1724 RIPv2 MIB RFC 2096 IP Forwarding Table MIB RFC 2674 802.1p and IEEE 802.1Q Bridge MIB RFC 1850 OSPFv2 MIB RFC 2233 Interfaces MIB RFC 2737 Entity MIB (Version 2) RFC 1907 SNMPv2 MIB RFC 2273 SNMP-NOTIFICATION-MIB RFC 2863 The Interfaces Group MIB RFC 2011 SNMPv2 MIB for IP RFC 2571 SNMP Framework MIB RFC 3813 MPLS LSR MIB RFC 2572 SNMP-MPD MIB</p>
Network management	<p>IEEE 802.1D (STP) RFC 1904 SNMPv2 Conformance RFC 2272 SNMPv3 Management Protocol RFC 1098 Simple Network Management Protocol (SNMP) RFC 1905 SNMPv2 Protocol Operations RFC 2273 SNMPv3 Applications RFC 1158 MIB for network RFC 1906 SNMPv2 Transport Mappings RFC 2274 USM for SNMPv3 management of TCP/IP-based internets: MIB-II RFC 1212 Concise MIB definitions RFC 1215 Convention for defining traps for use with the SNMP RFC 1908 Coexistence between Version 1 and Version 2 of the Internet-standard Network Management Framework RFC 2275 VACM for SNMPv3 RFC 2575 SNMPv3 View-based Access Control Model (VACM) RFC 1918 Private Internet Address Allocation RFC 1389 RIPv2 MIB Extension RFC 2037 Entity MIB using SMIv2 RFC 3164 BSD syslog Protocol RFC 3411 An Architecture for Describing Simple Network RFC 1448 Protocol Operations for version 2 of the Simple Network Management Protocol (SNMPv2) RFC 1450 MIB for version 2 of the Simple Network Management Protocol (SNMPv2) RFC 1902 Structure of Management Information for Version 2 of the Simple Network Management Protocol (SNMPv2) RFC 1903 SNMPv2 Textual Conventions RFC 2261 An Architecture for Describing SNMP Management Frameworks RFC 2262 Message Processing and Dispatching for the Simple Network Management Protocol (SNMP) RFC 2263 SNMPv3 Applications RFC 2264 User-based Security Model (USM) for version 3 of the Simple Network Management Protocol (SNMPv3) RFC 2265 View-based Access Control Model (VACM) for the Simple Network Management Protocol (SNMP) Management Protocol (SNMP) Management Frameworks</p>

Standards and protocols (continued)

(applies to all products in series)

Network management (continued)

RFC 3412 Message Processing and Dispatching for the Simple Network Management Protocol (SNMP)
 RFC 3413 Simple Network Management Protocol (SNMP) Applications
 RFC 3414 SNMPv3 User-based Security Model (USM)
 RFC 3415 View-based Access Control Model (VACM) for the Simple Network Management Protocol (SNMP)

OSPF

RFC 1245 OSPF protocol analysis
 RFC 1583 OSPFv2
 RFC 1850 OSPFv2 MIB,
 RFC 1246 Experience with OSPF
 RFC 1587 OSPF NSSA
 RFC 1765 OSPF Database Overflow traps
 RFC 2328 OSPFv2
 RFC 2370 OSPF Opaque LSA Option

QoS/CoS

IEEE 802.1P (CoS)
 RFC 2597 DiffServ Assured Forwarding (AF)
 RFC 3168 The Addition of Explicit Congestion
 RFC 2474 DS Field in the IPv4 and IPv6 Headers
 RFC 2598 DiffServ Expedited Forwarding (EF)
 RFC 2475 DiffServ Architecture
 RFC 2697 A Single Rate Three Color Marker Notification (ECN) to IP
 RFC 3247 Supplemental Information for the New Definition of the EF PHB (Expedited Forwarding Per-Hop Behavior)

Security

IEEE 802.1X Port Based Network Access Control
 RFC 2408 Internet Security Association and Key
 RFC 2865 RADIUS Authentication
 RFC 2082 RIP-2 MD5 Authentication
 RFC 2104 Keyed-Hashing for Message Authentication
 RFC 2138 RADIUS Authentication
 RFC 2139 RADIUS Accounting Management Protocol (ISAKMP)
 RFC 2409 The Internet Key Exchange (IKE)
 RFC 2412 The OAKLEY Key Determination Protocol
 RFC 2459 Internet X.509 Public Key Infrastructure Certificate and CRL Profile
 RFC 2818 HTTP Over TLS
 RFC 2866 RADIUS Accounting
 RFC 3579 RADIUS Support For Extensible Authentication Protocol (EAP)
 RFC 3580 IEEE 802.1X Remote Authentication Dial In User Service (RADIUS) Usage Guidelines

VPN

RFC 1828 IP Authentication using Keyed MD5
 RFC 2405 The ESP DES-CBC Cipher Algorithm With
 RFC 3948 UDP Encapsulation of IPsec ESP Packets
 RFC 1853 IP in IP Tunneling
 RFC 2401 Security Architecture for the Internet Protocol
 RFC 2402 IP Authentication Header
 RFC 2403 The Use of HMAC-MD5-96 within ESP and AH
 RFC 2404 The Use of HMAC-SHA-1-96 within ESP and AH Explicit IV
 RFC 2406 IP Encapsulating Security Payload (ESP)
 RFC 2407 The Internet IP Security Domain of Interpretation for ISAKMP
 RFC 2410 The NULL Encryption Algorithm and Its Use With IPsec
 RFC 2411 IP Security Document Roadmap
 RFC 4301 Security Architecture for the Internet Protocol
 RFC 4302 IP Authentication Header (AH)
 RFC 4303 IP Encapsulating Security Payload (ESP)
 RFC 4305 Cryptographic Algorithm Implementation Requirements for ESP and AH

HP MSR3000 TAA-Compliant Router Series accessories

Transceivers

HP X110 100M SFP LC FX Transceiver (JD102B)
 HP X110 100M SFP LC LX Transceiver (JD120B)
 HP X110 100M SFP LC LH40 Transceiver (JD090A)
 HP X110 100M SFP LC LH80 Transceiver (JD091A)
 HP X120 1G SFP LC SX Transceiver (JD118B)
 HP X120 1G SFP LC LX Transceiver (JD119B)
 HP X125 1G SFP LC LH40 1310nm Transceiver (JD061A)
 HP X120 1G SFP LC LH40 1550nm Transceiver (JD062A)
 HP X125 1G SFP LC LH70 Transceiver (JD063B)
 HP X120 1G SFP LC LH100 Transceiver (JD103A)
 HP X120 1G SFP LC BX 10-U Transceiver (JD098B)
 HP X120 1G SFP LC BX 10-D Transceiver (JD099B)

Cables

HP X200 V.24 DTE 3m Serial Port Cable (JD519A)
 HP X200 V.24 DCE 3m Serial Port Cable (JD521A)
 HP X200 V.35 DTE 3m Serial Port Cable (JD523A)
 HP X200 V.35 DCE 3m Serial Port Cable (JD525A)
 HP X200 X.21 DTE 3m Serial Port Cable (JD527A)
 HP X200 X.21 DCE 3m Serial Port Cable (JD529A)
 HP X260 RS449 3m DTE Serial Port Cable (JF825A)
 HP X260 RS449 3m DCE Serial Port Cable (JF826A)
 HP X260 RS530 3m DTE Serial Port Cable (JF827A)
 HP X260 RS530 3m DCE Serial Port Cable (JF828A)
 HP X260 Auxiliary Router Cable (JD508A)
 HP X260 E1 RJ45 3m Router Cable (JD509A)
 HP X260 E1 RJ45 20m Router Cable (JD517A)
 HP X260 E1 (2) BNC 75 ohm 3m Router Cable (JD175A)
 HP X260 E1 BNC 20m Router Cable (JD514A)
 HP X260 E1 RJ45 BNC 75-120 ohm Conversion Router Cable (JD511A)
 HP X260 2E1 BNC 3m Router Cable (JD643A)
 HP X260 8E1 BNC 75 ohm 3m Router Cable (JD512A)
 HP X260 T1 Router Cable (JD518A)
 HP X260 T1 Voice Router Cable (JD535A)
 HP X260 SIC-8AS RJ45 0.28m Router Cable (JD642A)
 HP X260 mini D-28 to 4-RJ45 0.3m Router Cable (JG263A)
 HP X260 T3/E3 Router Cable (JD531A)
 HP X260 E3-30 E3/T3 Router Cable (JD533A)
 HP X200 Transit Plug D25F MP8(S) Single Cable (JD636A)
 HP X200 Transit RJ45 0.5m Single Cable (JD641A)
 HP X260 E1 RJ45 to 2xBNC 75ohm 3m Router Cable (JH294A)
 HP X260 E1 RJ45 120 ohm 2m Router Cable (JC156A)
 HP X260 E1 RJ45 120 ohm 15m Router Cable (JC151A)
 HP X260 E1 RJ45 120 ohm 30m Router Cable (JC152A)
 HP X260 T1 Router Cable (JD518A)

Power supply

HP RPS 800 Redundant Power Supply (JD183A)
 HP X351 300W 100–240VAC to 12VDC Power Supply (JG527A)

Router modules

HP MSR 9-port 10/100Base-T Switch DSIC Module (JD574B)
 HP MSR 4-port 10/100Base-T Switch SIC Module (JD573B)
 HP MSR 1-port 10/100Base-T SIC Module (JD545B)
 HP MSR 1-port 100Base-X SIC Module (JF280A)
 HP MSR 1-port GbE Combo SIC Module (JD572A)
 HP MSR 2-port FXO SIC Module (JD558A)
 HP MSR 1-port FXO SIC Module (JD559A)
 HP MSR 2-port FXS SIC Module (JD560A)
 HP MSR 1-port FXS SIC Module (JD561A)
 HP MSR 1-port E1 Voice SIC Module (JD575A)
 HP MSR 1-port T1 Voice SIC Module (JD576A)
 HP MSR 2-port FXS/1-port FXO SIC Module (JD632A)
 HP MSR 4-port FXS / 1-port FXO DSIC Module (JG189A)
 HP MSR 2-port ISDN-S/T Voice SIC Module (JF821A)
 HP MSR 1-port E1/Fractional E1 (75ohm) SIC Module (JD634B)
 HP MSR 2-port E1/Fractional E1 (75ohm) SIC Module (JF842A)
 HP MSR 1-port T1/Fractional T1 SIC Module (JD538A)
 HP MSR 1-port Enhanced Sync/Async Serial SIC Module (JD557A)
 HP MSR 1-port ISDN-S/T SIC Module (JD571A)
 HP MSR 8-port Async Serial SIC Module (JF281A)
 HP MSR 16-port Async Serial SIC Module (JG186A)
 HP MSR HSPA/WCDMA SIC Module (JG187A)
 HP MSR HSPA+ / WCDMA SIC Module (JG929A)
 HP MSR 1-port E1 Voice HMIM Module (JG429A)
 HP MSR 1-port T1 Voice HMIM Module (JG430A)
 HP MSR 2-port E1 Voice HMIM Module (JG431A)
 HP MSR 4-port FXS HMIM Module (JG446A)
 HP MSR 4-port FXO HMIM Module (JG447A)
 HP MSR 4-port E and M HMIM Module (JG448A)
 HP MSR 4-port Enhanced Sync/Async Serial HMIM Module (JG442A)
 HP MSR 8-port Enhanced Sync/Async Serial HMIM Module (JG443A)
 HP MSR 2-port E1/CE1/PRI HMIM Module (JG450A)
 HP MSR 4-port E1/CE1/PRI HMIM Module (JG451A)
 HP MSR 4-port E1/Fractional E1 HMIM Module (JG453A)
 HP MSR 8-port E1/CE1/PRI (75ohm) HMIM Module (JG452A)
 HP MSR 2-port T1/CT1/PRI HMIM Module (JG456A)
 HP MSR 4-port T1/Fractional T1 HMIM Module (JG457A)
 HP MSR 1-port E3/CE3/FE3 HMIM Module (JG436A)
 HP MSR 1-port T3/CT3/FT3 HMIM Module (JG435A)
 HP MSR 1-port OC-3c/STM-1c POS HMIM Module (JG438A)
 HP MSR G2 128-channel Voice Processing Module (JG417A)
 HP MSR 1U HMIM Adapter Module (JG416A)
 HP MSR 0.5U HMIM Adapter Module (JG415A)
 HP MSR 8-port 100BASE-FX/1000BASE-X/4-port 1000BASE-T (Combo) L2/L3 HMIM Module (JH238A)
 HP MSR 16-port Enhanced Async Serial HMIM Module (JG445A)
 HP MSR 8-port E1/CE1/T1/CT1/PRI HMIM Module (JH169A)
 HP MSR 8-port E1/Fractional E1/T1/Fractional T1 HMIM Module (JH172A)
 HP MSR Open Application Platform (OAP) with VMware® vSphere MIM Module (JG532A)
 HP MSR Medium Survivable Branch Communication MIM Module powered by Microsoft Lync (JG588A)

Power cords

HP X290 MSR30 1m RPS Cable (JD637A)

Memory

HP X600 1G Compact Flash Card (JC684A)
 HP X600 512M Compact Flash Card (JC685A)
 HP X600 256M Compact Flash Card (JC686A)
 HP X610 4GB DDR3 SDRAM UDIMM Memory (JG530A)

Learn more at
hp.com/networking

Sign up for updates
hp.com/go/getupdated



Share with colleagues



Rate this document

© Copyright 2013, 2015 Hewlett-Packard Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Microsoft and Lync are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries. VMware is a registered trademark or trademark of VMware, Inc. in the United States and/or other jurisdictions. sFlow is a registered trademark of InMon Corp.

