

HSM® V-Press 820

WAREHOUSE
MANAGEMENT SOLUTIONS



A strong disposal station thanks to its powerful motor, its ergonomic design and its sophisticated and innovative technology, the HSM V-Press 820 combines all of the advantages of a baling press into one machine.

- State-of-the-art microprocessor controller and membrane keypad with LED display
- Special retaining claws optimize the compression of the pressing material, increasing both loading volume and bale output
- Quick and easy press assembly
- Configuration:
 - loading flap with hand wheel door lock



<http://goo.gl/hJmrhp>

Specifications

HSM part #	HSM6143-VP820Plus	Cycle time in idle operation (theor.) sec.	23
Pressing power	18.15 tons	Volume throughput in idle operation (theor.) yd.³/hour.	145.2
Motor in Hp	5.36	Press chamber size (H x W x D)	51.1" x 47.2" x 30.7"
Voltage / Frequency	3 x 220V / 60 Hz	Dimensions of machine (H x W x D)	97.2" x 66.92" x 42.3"
Loading aperture (W x H)	47" x 22"	Machine weight	2866 lbs.
Bale weight (depending on material)	551 lbs.		
Bale size (H x W x D)	39.37" x 30.7" x 47.2"		
Hourly output in bales	2-5		
Options		Part number	
Strapping tape	4-fold polyester tape	6212993010	

(All technical specifications are approximate values. Technical and design modifications reserved.)

HSM of America, LLC
419 Boot Road
Downingtown, PA 19335
www.hsmofamerica.com
Customer Service / 800.613.2110

HSM®
Great Products,
Great People.