

# ZuM™ Monaural and Binaural USB Headsets Single Ear Monaural and Dual Ear Binaural USB, LYNC Headsets



Monaural Headset



Binaural Headset

## Comfort and Durability

Call center tested, for durability. The hexagon-shape enhanced structural design gives maximum strength against bending and physical damage. Designed for extensive use, the large speaker chambers cover most ear sizes comfortably.

### Both Headset Models Feature:

- Over-the-Head Monaural and Binaural versions.
- Powerful 40mm speakers for top quality sound.
- Durable structural design that is ideal for extensive use situations.
- Large, comfortable ear pads.
- Bendable microphone arm for infinite adjustments.
- The 5 Watt speaker can generate volume up to 90dB.
- Noise canceling microphone.
- Acoustic shock protection.
- UC compatible: LYNC, Avaya, Cisco, IBM and more.

## Performs well in the Harshest Conditions

Not only are they durable, they provide noise canceling for use in busy environments and padded ear covers offer comfort in situations that require many hours of use. Built-in Acoustic Shock Protection (ASP) provides a circuit-breaker-type protection against sudden loud noise from the speaker source.

	Monaural	Binaural
Part	ZUMUC1	ZUMUC2
UPC	800807320253	800807320277
<b>MSRP</b>	<b>\$69.99</b>	<b>\$79.99</b>

# ZūM™ Monaural and Binaural USB Headsets Single Ear Monaural and Dual Ear Binaural USB, LYNC Headsets

## Package Includes



**Monaural**



**Binaural**



**Controller**

## Specifications

### FEATURES

- Over-the-Head Monaural and Binaural versions
- Powerful 40mm speakers for top quality sound
- Durable structural design
- Large, comfortable ear pads
- Bendable microphone arm for infinite adjustments
- The 5 Watt speaker can generate volume up to 90dB
- Noise canceling microphone
- Acoustic shock protection
- UC compatible: LYNC, Avaya, Cisco, IBM and more

### TECHNICAL SPECIFICATIONS

- Speaker size: 1.57" (40mm) Diam
- Sensitivity: 97dB  $\pm$  3dB (SPL/100mV@1K Hz)
- Microphone Sensitivity: -61dB  $\pm$  3dB
- Impedance: 160 $\Omega$   $\pm$  20%
- Frequency Response: 200–5000Hz

### PHYSICAL SPECIFICATIONS

- Dimensions: 8" x 6.67" x 2.4" (20cm x 17cm x 6cm)
- External Microphone dimension: .23" x .2" (6 x 5mm)
- Weight: 50g
- Cord Length: 5' (1.5m) normal, 9.8' (3m) extended

### CONTROLS

- Volume UP/DOWN
- Microphone ON/OFF

### PACKAGING

- Type: Retail Clamshell Container
- Dimensions: 7.5" x 10" x 2" (190 x 254 x 51mm)

### COMPATIBILITY

