



Clarity Matrix MX55HDX-L

LCD Video Wall System

The Clarity® Matrix® MX55HDX-L is an extreme narrow bezel 55" LCD video wall display that provides outstanding tiled visual performance, supports extended operation, and requires minimal installation space. Designed for 24x7 operation, Clarity Matrix MX55HDX-L features 800 nits brightness, LED backlight technology, and Full HD resolution making it the ideal video wall for high-impact, mission-critical applications. Clarity Matrix MX55HDX-L sets a new benchmark with a tiled bezel width of a mere 1.7mm, creating a near seamless digital canvas.



SPECIFICATION	DETAIL
Planar Part Number	997-8319
Technology	Commercial-grade direct view LCD
Diagonal	55 inches
Aspect Ratio	16:9
Native Resolution Panels	1920 x 1080
Tiled Bezel Width	0.06" (1.7 mm)
Brightness (typ)	800 cd/m ² or nits
Response Time (typ)	8 ms
Contrast ratio (full field)	4000:1
Full viewing angle	178°
Backlight life (1/2 brightness)	50,000 Hrs
Mounted Depth	3.6" wall to front of screen
Acoustic Noise	Fanless operation
Heat load	660 BTU/hr
Operating temperature range	5 - 40 Degrees C
Operating humidity range	20-90% RH non-condensing
Backlight control	Individual and wall control
Backlight sensing and reporting	At display level

Display module position sensing	Auto-sensing integrated
Power Consumption (typ)	194 W
Power supply voltage	100-230V AC ± 10%, 50-60 Hz
Power Status	Diagnostics LEDs, health monitoring and alerts
Safety regulations	Complies with EN60950, FCC Class A, CISPR22/85, CE, EU RoHS
Data Inputs	4 HDMI inputs, 1 DisplayPort input
Control	IR Remote, RS232, Ethernet (optional)
Per Panel Dimensions (Including Mount)	47.72" x 26.85" x 3.54" (1212 mm x 682 mm x 90 mm)
Per Panel Weight (Including Mount)	56 lbs. (26 kg)
Shipping weight	150 lbs (68.04 kg)
Touch Options	Clarity Matrix MultiTouch Kits

For more information, please visit www.planar.com

Specifications are subject to change without notice.

Specification Report Date: 12/28/2017

© Copyright 2017 Planar Systems, Inc. All rights reserved