



19 Inch Rear Mount PCAP Touch Monitor

R19ZH-OV-45P0

REAR MOUNT


GVision's line of rear mount projected capacitive displays are purpose built for system builders who require a rugged and durable touch screen solution that can easily be integrated into any embedded application. It is completely sealed to protect against the elements, which means it can be used either inside or out, and in high-traffic public facing applications.



10-Points
Touch



DVI-D Digital
Input



HDMI Digital
Input



VGA Analog
Input



USB B-Type
Touch



IP65
Protected



LED
Backlight
Unit



3-Year
Warranty

19-Inch **REAL MOUNT PCAP** Touch Monitor



INPUT INTERFACE




Multi Inputs

Gvision's KISOK Open Frame monitor supports both digital and analog inputs to use as normal office desktop monitor with VGA, DVI input or HDMI for commercial digital signage as well.

DIMENSION

Unit: Inch



FEATURES

- **19-Inch** Screen Size
- **1280 x 1024** Resolution
- Video Signal: **VGA** (15 Pin D-Sub) / **DVI** / **HDMI**
- **10-Points** Projective Capacitive **PCAP** Touch Technology
- **IP65** on the Front (Optional)
- **Zero Pressure** Touch Activation
- **LED** Backlight Unit
- **Metal** Enclosure Material
- **3-Year** Warranty

SPECIFICATIONS

DISPLAY	R19ZH-OV-45P0
Screen Size	19 In
Resolution	1280 x 1024
Backlight	LED
Aspect Ratio	5 : 4
Viewing Angle	170° / 160°
Response Time	5ms
Brightness	250cd/m ²
Contrast Ratio	1000 : 1
Color Depth	16.7 M
Display Area (mm)	376.32 x 301.06mm
INTERFACE	
HDMI	1
DVI	1
VGA (15 Pin D-Sub)	1
Audio	1
USB (B-Type)	1
TOUCH TECHNOLOGY	
Material	2 mm Glass
Points / Type	10 Max / Projected Capacitive (PCAP)
Accuracy	2 mm
CABINET	
Material	Plastic Frame / Metal Housing
Color	Black
POWER	
Consumption	20W Max Standby ≤ 0.5W
Electrical Ratings	12VDC ± 5% (Adapter Input AC 100V ~ 240V, 50/60Hz)
TEMPERATURE	
Operating	32° F ~ 104° F (0° C ~ 40° C)
Storage	-4° F ~ 140° F (-20° C ~ 60° C)
HUMIDITY	
Operating	20% ~ 80%
Storage	10% ~ 90%
DIMENSIONS (W×H×D)	
Inch (in)	17.2 x 14.3 x 1.8
Millimeter (mm)	438.6 x 363.7 x 47.0
WEIGHT	
Net Weight	11.0 lbs (5 kg)
COMPLIANT	
Certification	CE / FCC
VESA™	
Mount Size (mm)	100 x 100

Specifications subject to change without any notice