

## SmartOnline SVTX Series 3-Phase 380/400/415V 10kVA 9kW On-Line Double-Conversion UPS, Tower, Extended Run, SNMP Option

MODEL NUMBER: SVT10KX



### Highlights

- On-line double-conversion topology with IGBT technology
- Voltage and Frequency Independent (VFI) operation
- Automatic and Manual Bypass for enhanced reliability
- Optional ECO mode for high-efficiency operation
- Internal batteries and expandable runtime options

### Package Includes

- SVT10KX SmartOnline SVTX Series 3-Phase 380/400/415V 10kVA 9kW On-Line Double-Conversion UPS
- DB9 cable
- Owner's manual

### Description

The SVT10KX SmartOnline® SVTX Series 3-Phase 380/400/415V 10kVA 9kW On-Line Double-Conversion UPS with IGBT technology provides battery backup and AC power protection against power disturbances that can damage electronics or destroy data. It's recommended for critical IT or corporate infrastructure, telecom, LAN/WAN, security and emergency, financial and light industrial applications.

The SVT10KX's VFI design allows continuous operation at any supported voltage at either 50 or 60 Hz. Zero transfer time to battery mode ensures no disruption to the attached loads. Automatic and Manual Bypass keeps connected equipment powered even during overloads and UPS maintenance.

IGBT inverter technology produces output power with less than 2% total harmonic distortion (THD) to keep connected equipment functioning at its peak. A 3:1 crest factor safely supports a variety of loads, even those with wildly fluctuating power demands.

Managing the SVT10KX is simplified through the interactive front-panel LCD interface, which displays critical operating conditions and diagnostic data, such as load levels, available runtime, alarm status, battery charge, and voltage and frequency values. Four LEDs indicate bypass, line, battery and fault modes. A serial port allows connection to Tripp Lite's free local shutdown agent. A built-in card slot supports [WEBCARDLX](#) or [RELAYCARDSV](#) for network interface and remote monitoring and control. The SVT10KX's reduced size and small footprint save valuable space.

### Features

#### VFI True On-Line Double-Conversion 3-Phase UPS System

- Provides fully regulated sine wave AC output for critical telecom, network, security, financial, corporate and light industrial applications
- +/-1% output voltage regulation in online and battery modes
- High 0.9 power factor offers 10kVA/9kW output capacity, allowing for more connected devices
- Selectable 380/400/415V output voltage
- Wide input voltage window (305–478V) minimizes battery use and prolongs battery life

#### Reliable Battery Backup with Expandable Runtime



- Supports half load for 10.5 min. and full load for 3.8 min.
- Zero transfer time suitable for advanced network applications
- Expandable runtime with optional external battery packs, such as Tripp Lite's [BP240V135](#)
- Restarts automatically after lengthy power outages

#### IGBT Inverter Technology

- Produces output power with less than 2% THD to keep connected equipment functioning at its peak
- Low <6% THDi input rating and advanced IGBT rectifier enables 1:1 Generator Sizing, eliminating costly oversizing requirements for generators, breakers and cables

#### Automatic and Manual Bypass

- Increases system reliability
- Allows maintenance without removing power from attached loads

#### ECO Mode

- Operates at efficiency levels as high as 98.8% when input line conditions are favorable

#### SNMP/Web Capability

- Slot for SNMP network interface and relay card for remote monitoring and control options

#### Communications Ports

- DB9 and EPO ports offer local monitoring and shutdown options

#### Small-Footprint Tower Design

- Reduced-size black tower case saves valuable floor space
- Matching external battery cabinets enable extended runtime options

## Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	10000
Output kVA Capacity (kVA)	10
Output kW Capacity (kW)	9
Output Capacity Details	Supports up to 100% load continuously in double conversion mode; Supports 100-110% load for 10 minutes, 110 to 130% load for 1 minute and greater than 130% for 1 second before switching to bypass mode; Inverter mode is automatically restored as load levels are reduced to 70% or less
Power Factor	0.9
Crest Factor	3:1
Nominal Output Voltage(s) Supported	220/380V 3-PH Wye; 230/400V 3-PH Wye; 240/415V 3-PH Wye
Frequency Compatibility	50 / 60 Hz



Output Voltage Regulation (Line Mode)	+/- 1%
Output Voltage Regulation (Economy Line Mode)	+/-11V of selected nominal output voltage (220V: 209-231V; 230V: 219-241; 240V: 229-251V)
Output Voltage Regulation (Battery Mode)	+/- 1%
Output Receptacles	Hardwire
Output AC Waveform (AC Mode)	Pure Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
<b>INPUT</b>	
Rated input current (Maximum Load)	17.4A
Nominal Input Voltage(s) Supported	220/380V 3-PH Wye; 230/400V 3-PH Wye; 240/415V 3-PH Wye
Nominal Input Voltage Description	3-Phase Wye, 4 wire plus ground (L1, L2, L3, N, G)
UPS Input Connection Type	Hardwire
Input Phase	3-Phase
Power Factor (Input)	.99PF (100% load)
THDi	<6%
<b>BATTERY</b>	
Full Load Runtime (min.)	3.8 min (9kW)
Half Load Runtime (min.)	10.5 min. (4.5kW)
Expandable Battery Runtime	Supports extended runtime optional external battery packs
External Battery Pack Compatibility	<a href="#">BP240V135</a>
DC System Voltage (VDC)	240
Battery Recharge Rate (Included Batteries)	4 hours to 90% (Internal batteries)
Expandable Runtime	Yes
<b>VOLTAGE REGULATION</b>	
Voltage Regulation Description	Online, double-conversion power conditioning maintains output within 1% of the selected nominal voltage in online mode
Overvoltage Correction	Corrects overvoltage conditions to 520V (50% load) and 478V (100% load)
Undervoltage Correction	Corrects brownout conditions to 110V (50% load) / 305V (100% load)
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Front Panel LCD Display	LCD DISPLAY: offers a variety of graphical, text and numeric information to indicate a wide range of UPS operation and fault / warning conditions, including current operating mode, alarm status, load level, battery charge, input / output voltage & frequency, estimated runtime and more (see user manual for a detailed listing)



Switches	ON / ENTER BUTTON: turns the UPS on and confirms a selection from the settings menu; OFF / ESC BUTTON: turns off the UPS and returns to the previous item in the settings menu; TEST / UP BUTTON: initiates UPS self-test operation and advances to the next item in the settings menu; MUTE / DOWN BUTTON: silences the audible alarm and advances to the previous item in the settings menu; Press TEST/UP & MUTE/DOWN buttons simultaneously for 1 second to enter or exit the settings menu (See user manual for detailed information)
Audible Alarm	Alarms warn users of a variety of operational conditions: BYPASS MODE (beeps every 2 seconds), BATTERY MODE (beeps every 4 seconds), FAULT MODE (beeps continuously), OVERLOAD (beeps twice per second), OTHER WARNINGS (beeps once per second), FAULT (beeps continuously); All alarms can be silenced, except OVERLOAD & OTHER WARNINGS conditions
LED Indicators	4 LEDs report BYPASS / LINE / BATTERY / FAULT modes
<b>PHYSICAL</b>	
Installation Form Factors Supported with Included Accessories	Tower
Primary Form Factor	Tower
UPS Power Module Dimensions (hwd, in.)	33.9 x 9.8 x 32
UPS Power Module Dimensions (hwd, cm)	86.11 x 24.89 x 81.28
UPS Power Module Weight (lbs.)	260
UPS Power Module Weight (kg)	117.93
UPS Shipping Dimensions (hwd / in.)	41.7 x 14.96 x 36.22
UPS Shipping Dimensions (hwd / cm)	105.92 x 38.00 x 92.00
Shipping Weight (lbs.)	298
Shipping Weight (kg)	135
Cooling Method	Fans
UPS Housing Material	Steel
UPS Power Module Dimensions (Height x Width x Depth, mm)	862 x 250 x 813
UPS Shipping Dimensions (Height x Width x Depth, mm)	1060 x 380 x 920
Primary UPS Height (mm)	861
Primary UPS Width (mm)	249
Primary UPS Depth (mm)	813
Shipping Height (mm)	1059
Shipping Width (mm)	380
Shipping Depth (mm)	920
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	0 to +40C (32-104F)
Storage Temperature Range	0 to +35C (32 to 95F) with battery; -15 to 60C (5 to +140F) without battery



Relative Humidity	5 to 95%, non-condensing
Operating Elevation (ft.)	< 3000ft (Capacity de-rates by 1% for every 330ft over 3000)
Audible Noise	<65dBA front side 1M
Operating Elevation (m)	< 1000m (Capacity de-rates by 1% for every 100m over 1000)
<b>COMMUNICATIONS</b>	
Communications Interface	DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface
Network Monitoring Port Description	Card accessory slot also supports network interface and relay card options
Communications Cable	DB9 cabling included
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	Zero transfer time in ONLINE MODE (0ms); ECONOMY MODE: 7ms from AC to Battery mode / 0.6ms from Battery to AC mode
Low Voltage Transfer to Battery Power (Setpoint)	110V (50% load) / 305V (100% load)
High Voltage Transfer to Battery Power (Setpoint)	520V (50% load) / 478V (100% load)
<b>SPECIAL FEATURES</b>	
Grounding Lug	Yes
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Automatic inverter bypass; Manual bypass switch
Green Energy-Saving Features	High efficiency economy mode operation
<b>CERTIFICATIONS</b>	
UPS Certifications	CE
UPS Certification Details	EN 62040-1-1 (Safety); EN 62040-2 (Category C3)
<b>WARRANTY</b>	
Product Warranty Period (International)	1-year limited warranty

© 2016 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>