

Cisco-Compatible GLC-T SFP Mini Transceiver, 1000Base-TX Copper RJ45, Cat5e, Cat6, 328.08 ft. (100 m)

MODEL NUMBER: **N286-01GTX**



Adds a copper Gigabit Ethernet RJ45 connector to your 10/100/1000 network equipment. Complies with MSA (Multi-Sourcing Agreement) standards. 100% compatible with Cisco networking hardware.

Description

The N286-01GTX Cisco GLC-T Compatible 1000Base-TX Copper RJ45 SFP Mini Transceiver with an RJ45 Ethernet connector functions just like the Cisco® GLC-T transceiver module and is designed to operate with Cisco networking equipment. It also meets or exceeds the GLC-T's original specifications and complies with MSA standards.

This 1000Base-TX copper transceiver is fully hot-pluggable, so you can install it without shutting down the network or rebooting your device. It supports data transfer rates up to 1 Gbps with auto-negotiation up to 328.08-ft. (100 m) and automatic MDI/MDI-X crossover support. Its metallic housing allows low EMI and power dissipation. It supports up to 1.25 Gbps bi-directional communication.

Features

1000Base-TX Copper Transceiver with RJ45 Connector

- Hot-pluggable for installation without rebooting or shutting down
- Data transfer rates up to 1 Gbps
- Transmits up to 328.08-ft. (100 m) with RJ45 cabling
- 10/100/1000 auto-sensing RJ45 port with auto MDI/MDI-X support
- Metallic housing for low EMI and power dissipation
- Supports up to 1.25 Gbps bi-directional communication

Designed for Use with Cisco Networking Equipment

- Functionally equivalent to Cisco GLC-T

Highlights

- Supports data transfer rates up to 1 Gbps
- Auto-sensing RJ45 port with Auto MDI/MDI-X support
- Transmits up to 328.08-ft. (100 m) with RJ45 cabling
- Low EMI and power dissipation
- Supports up to 1.25 Gbps bi-direction communication

System Requirements

For a list of compatible switches, see the Switch Compatibility document in the Resources tab or the Technical Support page.

Package Includes

- N286-01GTX Cisco GLC-T Compatible 1000Base-TX Copper RJ45 SFP Mini Transceiver
- Owner's manual



- Meets or exceeds GLC-T specs
- Complies with MSA standards

Specifications

OVERVIEW	
UPC Code	037332197412
Technology	SFP+/QSFP+/QSFP28
PHYSICAL	
Shipping Dimensions (hwd / cm)	2.79 x 5.59 x 12.19
Shipping Dimensions (hwd / in.)	1.10 x 2.20 x 4.80
Shipping Weight (kg)	0.09
Shipping Weight (lbs.)	0.20
Unit Dimensions (hwd / cm)	0,84 x 1,32 x 5,69
Unit Dimensions (hwd / in.)	0.33 x 0.52 x 2.24
Unit Weight (kg)	0.02
Unit Weight (lbs.)	0.05
ENVIRONMENTAL	
Storage Temperature Range	-40 to 185 F (-40 to 85 C)
Relative Humidity	10 to 85% RH, Non-Condensing
Operating Temperature	32 to 158 F (0 to 70 C)
COMMUNICATIONS	
Signal Range (m)	100
Transmission Distance	100 m
CONNECTIONS	
Side A - Connector 1	SFP+ (MALE)
Side B - Connector 1	RJ45 (FEMALE)
FEATURES & SPECIFICATIONS	
Brand Compatibility	Cisco
SPECIAL FEATURES	
Data Transfer Rate	1Gbps



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>