

DATA SHEET

ARUBA 7000 SERIES MOBILITY CONTROLLER

Extend the digital workplace to branch offices

Aruba 7000 series Mobility Controllers optimize cloud services and secure enterprise applications at branch offices, while reducing the cost and complexity of deploying and managing the network.

Aruba 7000 Series Mobility Controllers optimize cloud services and secure enterprise applications for hybrid WAN at branch offices, while reducing the cost and complexity of deploying and managing the network

The 7000 Series Mobility Controllers combine wireless, wired and hybrid WAN services, support up to 64 APs and 24 Ethernet ports, and feature integrated WAN compression, health checks, zero-touch configuration, and policy-based routing. The 7000 series also unify policy management with third-party security services, making it simpler and more secure to create a digital workplace experience in head-end and branch locations.

Supporting over 4,000 users, the 7000 series performs stateful firewall policy enforcement at up to 8 Gbps. Secure IP tunnels protect WAN traffic across the public and private transport network to the cloud and data center. Additional features include integrated firewall, secure VPN, 3G/4G LTE cellular failover, threat management with content filtering, and local bridging, based on end-user application or IT traffic forwarding requirements.

The 7000 series supports Aruba's Next-Generation Mobility Firewall with AppRF™ technology, which continuously evaluates app usage and performance for over 1,500 apps, including cloud and web-based services like Skype for Business, SharePoint, Box, Salesforce.com and apps that are hidden as encrypted or web traffic. It then automatically makes configuration changes in real-time to ensure optimal bandwidth, priority, and network paths in branch and remote offices to safeguard the best possible user experience

A real-time dashboard makes it easy to identify and correct Quality-of-Service tags, load-balance specific applications across APs, adjust RF management and roaming parameters for latency-sensitive apps, and apply bandwidth contracts per app or application type.



Integration with cloud services such as Palo Alto Networks GlobalProtect and Microsoft Skype for Business make extending security and QoS for mobile unified communications easier and more reliable across the distributed enterprise, while reducing local complexity

The 7000 series handles other enterprise-critical capabilities like authentication, encryption, IPv4 and IPv6 services, Adaptive Radio Management™, ClientMatch™, and RFProtect™ spectrum analysis and wireless intrusion protection.

The 7000 series can be deployed in minutes with zero-touch provisioning via cloud-based Aruba Activate™, enabling IT to deploy branch locations simpler and more efficiently.

PRODUCT SUMMARY

- 7005 Mobility Controller is a compact, fanless entry-level branch platform that can be powered by a power-over-Ethernet (PoE) switch.
- 7008 Mobility Controller is a compact, fanless entry-level branch platform with 8 integrated PoE and PoE+ switch ports for small branch locations with some PoE requirements
- 7010 Mobility Controller is designed for mid-sized branch deployments that require several PoE and PoE+ switch ports.
- 7024 Mobility Controller is designed for mid-sized branch offices that require up to 24 switch ports for unified wired and wireless access.
- 7030 Mobility Controller is ideal for mid- to large- sized branch deployments that require unprecedented scale and performance.

PERFORMANCE AND CAPACITY

Features	7005	7008	7010	7024	7030
Maximum campus AP licenses	16	16	32	32	64
Maximum remote AP licenses	16	16	32	32	64
Maximum concurrent users/devices	1,024	1,024	2,048	2,048	4,096
Maximum VLANs	4,094	4,094	4,094	4,094	4,094
Active firewall sessions	16,384	16,384	32,768	32,768	65,536
Concurrent GRE tunnels	256	256	512	512	1,024
Concurrent IPsec sessions	512	512	1,024	1,024	2,048
Mobility Access Switch tunneled-node ports	512	512	1,024	1,024	2,048
Firewall throughput	2 Gbps	2 Gbps	4 Gbps	4 Gbps	8 Gbps
Encrypted throughput (3DES, AES-CBC)	1.2 Gbps	1.2 Gbps	2.4 Gbps	2.4 Gbps	2.4 Gbps
Encrypted throughput (AES-CCM)	1.6 Gbps	1.6 Gbps	3.4 Gbps	3.4 Gbps	4.0 Gbps

INTERFACES AND INDICATORS

Features	7005	7008	7010	7024	7030
Form factor/footprint	Compact	Compact	1 rack unit	1 rack unit	1 rack unit
Auto-negotiating 10/100/1000BASE-T	4	8	16	24	8 (combo)
Gigabit Ethernet ports (GBIC or SFP)	N/A	N/A	2 SFP	2 SFP+	8 (combo)
USB 2.0	Yes (1)	Yes (2)	Yes (2)	Yes (1)	Yes (1)
Management/status LEDs	Yes	Yes	Yes	Yes	Yes
LINK/ACT and status LEDs	No	No	No	Yes	Yes
LCD panel and navigation buttons	No	No	Yes	Yes	Yes
Console port	Yes (micro USB/RJ-45)	Yes (micro USB/RJ-45)	Yes (micro USB/RJ-45)	Yes (micro USB/RJ-45)	Yes (micro USB/RJ-45)
Out-of-band management port	No	No	Yes	Yes	Yes

PHYSICAL

	7005	7008	7010	7024	7030
Dimensions (H x W x D)	4.1 cm x 20 cm x 20 cm (1.6" x 7.9" x 7.9")	4.2 cm x 20.32 cm x 20.32 cm (1.65" x 8.0" x 8.0")	4.42 cm x 31.75 cm x 33.7 cm (1.74" x 12.75" x 13.3")	4.37 cm x 44.2 cm x 31.3 cm (1.72" x 17.4" x 12.32")	4.4 cm x 30.5 cm x 21.1 cm (1.7" x 12" x 8.3")
Weight	0.92 kg (2.03 lbs)	1.0 kg (2.2 lbs)	3.4 kg (7.5 lbs)	5.127 kg (11.3 lbs)	2.06 kg (4.54 lbs)
MTBF (hours, @ 25C)	323,896	300,000	232,843	311,901	390,679

ENVIRONMENTAL RANGE					
Specification	7005	7008	7010	7024	7030
Operating temperature	0° C to 40° C				
Storage temperature	-40° C to 70° C				
Humidity/storage humidity	10% to 95%, NC				
Operating altitude	10,000 feet				
Acoustic noise ¹	0 dBA (fanless)	0 dBA (fanless)	39.8 – 58.6 dBA	34.3 – 71.2 dBA	29.1 – 57.4 dBA
Maximum power consumption	16.6W (with USB)	126W with PoE (26W without PoE)	190W (with PoE)	450W (with PoE)	55W

¹ Sound power per ETSI 300 753 in accordance with ISO 7779

REGULATORY AND SAFETY COMPLIANCE	
Description	Specification
Safety certifications	UL 60950-1 Second Edition CAN/CSA-C22.2 No. 60950-1 Second Edition EN 60950-1 Second Edition EN 60950:2005 IEC 60950-1 Second Edition NOM (obtained by partners and distributors)
Electromagnetic emissions certifications	FCC Part 15 Class B CE AS/NZS CISPR22 Class B CISPR22 Class A (7010, 7024, 7030), Class B (7005) EN55022 Class A (7010, 7024, 7030), Class B (7005) ICES-003 Class A (7010, 7024, 7030), Class B (7005) VCCI Class A (7010, 7024, 7030), Class B (7005) EN61000-3-2 EN61000-3-3 EN 61000-4-2, EN 61000-4-3, EN 61000-4-4, EN 61000-4-5, EN 61000-4-6, EN 61000-4-8, EN 61000-4-11, AS/NZS 3548 KN22 Class B KCC CNS13438 Class B EN55024/CISPR24 KN24 Industry Canada Class B CE mark, cTUVus, CB, C-tick, Anatel, NOM, MIC
Telco	Common Language Equipment Identifier (CLEI) Code
Regulatory SKU information	ARCN01014(7005), ARCN0103(7010), ARCN7024(7024), ARCN7030(7030)
Minimum ArubaOS Release	7005, AOS 6.4.1.0; 7008, AOS 6.5.0.0; 7010, AOS 6.4.1.0; 7024, AOS 6.4.3.0; 7030, AOS 6.4.1.0

ORDERING INFORMATION	
Part Number	Description
Controllers²	
JW633A	Aruba 7005 (RW) 4-port 10/100/1000BASE-T 16 AP and 1K Client Controller
JW634A	Aruba 7005 (US) 4-port 10/100/1000BASE-T 16 AP and 1K Client Controller
JW635A	Aruba 7005 (RW) FIPS/TAA-compliant 4-port 10/100/1000BASE-T 16 AP and 1K Client Controller
JW636A	Aruba 7005 (US) FIPS/TAA-compliant 4-port 10/100/1000BASE-T 16 AP and 1K Client Controller
JW637A	Aruba 7005 (IL) 4-port 10/100/1000BASE-T 16 AP and 1K Client Controller
JW638A	Aruba 7005 (IL) FIPS/TAA-compliant 4-port 10/100/1000BASE-T 16 AP and 1K Client Controller
JW639A	Aruba 7005 (JP) 4-port 10/100/1000BASE-T 16 AP and 1K Client Controller
JY849A	Aruba 7005 (EG) 4x 10/100/1000BASE-T Ports 16 AP Branch Controller
JW640A	Aruba 7005 (JP) FIPS/TAA-compliant 4-port 10/100/1000BASE-T 16 AP and 1K Client Controller
JX925A	Aruba 7008 (IL) 8p 100W PoE+ 10/100/1000BASE-T 16 AP and 1K Client Controller
JX926A	Aruba 7008 (JP) 8p 100W PoE+ 10/100/1000BASE-T 16 AP and 1K Client Controller
JX927A	Aruba 7008 (RW) 8p 100W PoE+ 10/100/1000BASE-T 16 AP and 1K Client Controller
JX928A	Aruba 7008 (US) 8p 100W PoE+ 10/100/1000BASE-T 16 AP and 1K Client Controller
JX929A	Aruba 7008 (IL) FIPS/TAA 8p 100W PoE+ 10/100/1000BASE-T 16 AP and 1K Client Controller
JX930A	Aruba 7008 (JP) FIPS/TAA 8p 100W PoE+ 10/100/1000BASE-T 16 AP and 1K Client Controller
JX931A	Aruba 7008 (RW) FIPS/TAA 8p 100W PoE+ 10/100/1000BASE-T 16 AP and 1K Client Controller
JX932A	Aruba 7008 (US) FIPS/TAA 8p 100W PoE+ 10/100/1000BASE-T 16 AP and 1K Client Controller
JW678A	Aruba 7010 (RW) 16p 150W PoE+ 10/100/1000BASE-T 1G BASE-X SFP 32 AP and 2K Clients Controller
JW679A	Aruba 7010 (US) 16p 150W PoE+ 10/100/1000BASE-T 1G BASE-X SFP 32 AP and 2K Clients Controller
JY850A	Aruba 7010 (EG) 16x 1000BASE-T + 2x SFP Ports 32 AP Branch Controller
JW702A	Aruba 7010 (RW) FIPS/TAA 16p 150W PoE+ 10/100/1000BASE-T 1GBASE-X SFP 32 AP and 2K Clients Controller
JW703A	Aruba 7010 (US) FIPS/TAA 16p 150W PoE+ 10/100/1000BASE-T 1GBASE-X SFP 32 AP and 2K Clients Controller
JW680A	Aruba 7010(IL) 16p 150W PoE+ 10/100/1000BASE-T 1G BASE-X SFP 32 for AP and 2K Clients Controller
JW704A	Aruba 7010 (IL) FIPS/TAA 16p 150W PoE+ 10/100/1000BASE-T 1G BASE-X SFP 32 AP and 2K Clients Controller
JW681A	Aruba 7010 (JP) 16p 150W PoE+ 10/100/1000BASE-T 1G BASE-X SFP for 32 AP and 2K Clients Controller
JW705A	Aruba 7010 (JP) FIPS/TAA 16p 150W PoE+ 10/100/1000BASE-T 1GBASE-X SFP 32 AP and 2K Clients Controller
JW682A	Aruba 7024 (RW) 24-port 400W PoE+ 10G BASE-X SFP+ 32 AP and 2K Clients Controller
JW706A	Aruba 7024 (RW) FIPS/TAA-compliant 24p 400W PoE+ 10G BASE-X SFP+ 32 AP and 2K Clients Controller
JW683A	Aruba 7024 (US) 24-port 400W PoE+ 10G BASE-X SFP+ 32 AP and 2K Clients Controller
JW707A	Aruba 7024 (US) FIPS/TAA-compliant 24p 400W PoE+ 10G BASE-X SFP+ 32 AP and 2K Clients Controller
JW684A	Aruba 7024 (IL) 24-port 400W PoE+ 10G BASE-X SFP+ 32 AP and 2K Clients Controller
JW708A	Aruba 7024 (IL) FIPS/TAA-compliant 24p 400W PoE+ 10G BASE-X SFP+ 32 AP and 2K Clients Controller
JW685A	Aruba 7024 (JP) 24-port 400W PoE+ 10G BASE-X SFP+ 32 AP and 2K Clients Controller
JW709A	Aruba 7024 (JP) FIPS/TAA-compliant 24p 400W PoE+ 10G BASE-X SFP+ 32 AP and 2K Clients Controller
JW686A	Aruba 7030 (RW) 8p Dual Pers 10/100/1000BASE-T/1GBASE-X SFP 64 AP and 4K Clients Controller
JW687A	Aruba 7030 (US) 8p Dual Pers 10/100/1000BASE-T/1GBASE-X SFP 64 AP and 4K Clients Controller
JW710A	Aruba 7030 (RW) FIPS/TAA 8p Dual Pers 10/100/1000BASE-T/1GBASE-X SFP 64 AP and 4K Clients Controller

² Hardware: 1 year parts/labor; can be extended with support contract. Software: 90 days; can be extended with support contract

ORDERING INFORMATION

Part Number	Description
Controllers²	
JW711A	Aruba 7030 (US) FIPS/TAA 8p Dual Pers 10/100/1000BASE-T/1GBASE-X SFP 64 AP and 4K Clients Controller
JW688A	Aruba 7030 (IL) 8p Dual Pers 10/100/1000BASE-T/1GBASE-X SFP 64 AP and 4K Clients Controller
JY851A	Aruba 7030 (EG) 8x 1000BASE-T or 8xSFP64 AP Branch Controller
JW712A	Aruba 7030 (IL) FIPS/TAA 8p Dual Pers 10/100/1000BASE-T 1GBASE-X SFP 64 AP and 4K Clients Controller
JW689A	Aruba 7030 (JP) 8p Dual Pers 10/100/1000BASE-T/1GBASE-X SFP 64 AP and 4K Clients Controller
JW713A	Aruba 7030 (JP) FIPS/TAA 8p Dual Pers 10/100/1000BASE-T/1GBASE-X SFP 64 AP and 4K Clients Controller
Controller Accessories	
JX989A	AP-AC-12V30A 12V 30W Power Adapter
JW082A	Aruba SPR-RK3-MNT 7205/7024/S2500-xx/S1500-24P/48P Spare Front Rack Mount
JW083A	Aruba SPR-WL2-MNT S2500/S1500 7024 Wall and Rack Mount Kit
JW084A	Aruba 7005-MNT-19 7005 Series 19-inch Rack Mount Kit
JW085A	Aruba 7010-MNT-19 7010 Series Replacement 19-inch Rack Mounting Kit
JW086A	Aruba 7030-MNT-19 7030 Series Replacement 19-inch Rack Mounting Kit
JW087A	SFP-LX 1000BASE-LX SFP 1310nm LC Connector Pluggable GbE XCVR
JW088A	SFP-SX 1000BASE-SX SFP 850nm LC Connector Pluggable GbE XCVR
JW089A	SFP-TX 1000BASE-T SFP Copper GbE RJ-45 Connector Pluggable XCVR
JW090A	SFP-10GE-LRM 10GBASE-LRM SFP+ 1310nm LC Connector Pluggable 10GbE XCVR
JW091A	SFP-10GE-SR 10GBASE-SR SFP+ 850nm Pluggable LC Connector 10GbE XCVR
JW092A	SFP-10GE-LR 10GBASE-LR SFP+ 1310nm Pluggable LC Connector 10GbE XCVR

² Hardware: 1 year parts/labor; can be extended with support contract. Software: 90 days; can be extended with support contract



1344 CROSSMAN AVE | SUNNYVALE, CA 94089
1.844.473.2782 | T: 1.408.227.4500 | FAX: 1.408.227.4550 | INFO@ARUBANETWORKS.COM