

HDMI over Cat5/6 Extender Kit, Box-Style Transmitter/Receiver for Video/Audio, IR, Up to 125 ft. (38 m), TAA

MODEL NUMBER: B126-1A1-IR



Transmitter and receiver work in tandem to extend HDMI and IR signals via Cat5e/6 cable to a projector, monitor or television. Ideal for digital signs, trade shows, classrooms, churches, offices and retail settings.

Description

The B126-1A1-IR HDMI over Cat5/6 Active Extender Kit includes a transmitter unit and a receiver unit that work in tandem to extend HDMI audio/video and IR remote control signals to a projector, monitor or television. The kit is ideal for digital signs, trade shows, classrooms, churches, offices, retail settings and other applications where the source is located farther than conventional cables allow.

HDMI cable (see Tripp Lite's P569-Series) connects a local display and the audio/video source to the transmitter unit and a remote display to the receiver unit. Cat5e/6 cable connects the two units (for best results, use 24 AWG solid-wire Cat5e/6 cable, such as Tripp Lite's N202-Series). Included IR-IN and IR-OUT cables allow you to control the video source, such as a Blu-ray™ player, while standing at the remote display.

The B126-1A1-IR can extend a 1080p (60 Hz) signal up to 125-ft. (38.1 m). In addition to crystal-clear video, the B126-1A1-IR delivers full, rich stereo and 7.1-channel surround sound (multi-channel or PCM) audio. Built-in equalization control lets you fine-tune the image quality at each remote display. Supports 24-bit True Color (8 bits per channel) and HDCP. Easy to set up with no software or drivers to install. Mounts to a wall, rack or pole using the included hardware.

Features

Extends High-Definition Signals

- Extends a 1080p (60 Hz) signal up to 125-ft. (38.1 m)
- IR functionality lets you control your Blu-ray player while standing at the remote display
- Transmitter and receiver connect with one Cat5e/6 cable (for best results, use 24 AWG solid-wire

Highlights

- Supports high-definition video resolutions up to 1080p (60 Hz)
- Supports stereo and 7.1-channel surround sound audio
- Included IR cables allow display-side control of video source
- Plug and play—no software or drivers to install
- Built-in equalization control lets you adjust monitor image

System Requirements

Package Includes

- Transmitter unit
- Receiver unit
- IR-IN cable
- IR-OUT cable
- Screwdriver for adjusting equalization
- (2) External power supplies with NEMA 1-15P plugs (Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A)
- Mounting hardware
- Owner's manual



Cat5e/6 cable, such as Tripp Lite's N202-Series)

- Supports stereo and 7.1-channel surround sound (multi-channel or PCM) audio
- Supports 24-bit True Color (8 bits per channel) and HDCP
- Built-in equalization control lets you adjust the image on the local monitor

Easy to Set Up and Use

- Plug-and-play engineering—no software or drivers to download and install
- Works with all operating systems and HDMI sources
- Units connect quickly to source and displays with HDMI cable, such as Tripp Lite's P569-Series
- Units install on a wall, rack or pole with the included hardware

TAA-Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332191328
Product Type	Extender Kit
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A, 5 ft.
Technology	HDMI; IR; Cat5/5e; Cat6
VIDEO	
Max Supported Video Resolution	1920x1080 (1080p @ 60Hz)
Max 1280 x 720 (720p) Range (ft)	125
Max 1920 x 1080 (1080p) Range (ft)	125
Transmitter Video Input	HDMI
Transmitter - Number of Video Outputs	1
Transmitter - Local Display Output	HDMI
Receiver/Transceiver Video Output	HDMI
Receiver - Number of Video Outputs	1
Signal Range (ft)	125
Signal Range (m)	38
Recommended Cabling	N202-Series Cat6 Patch Cable
Max Supported Color Depth	24-bit True Color
3D Video Supported	Yes



Chroma Sub Sampling	4:4:4
AUDIO	
Audio Input	HDMI; 3.5mm
Audio Output	HDMI
Audio Specification	Stereo Audio
POWER	
Power Source	Transmitter and Receiver (Included)
Power Source Type	AC Adapter
AC Plug Type	NEMA 1-15P
External Power Supply Input Specs (V / Hz / A)	100-240V / 50-60Hz / 0.5A
External Power Supply Output Specs (V / A)	5V/2A
External Power Supply Cord Length (ft.)	4.5
External Power Supply Cord Length (m.)	1.37
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.1 x 7.5mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	FCC; PSE; TUV;RoHS; UL; cUL
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	TX & RX: Green (Power), Orange (Activity)
PHYSICAL	
Color	Black
Included Mounting Accessories	Wallmount
Material of Construction	Steel
Number of Displays	1
Optional Mounting Accessory Notes	Can DIN Mount using Tripp Lite Bracket B110-DIN-02
Form Factor/Mounting Options	Box; Wall-mount
Rackmountable	Yes
Receiver Unit Dimensions (hwd / cm.)	2.6 x 9.2 x 6.4
Receiver Unit Dimensions (hwd / in.)	1 x 3.6 x 2.5
Receiver Unit Weight (kg)	0.09
Receiver Unit Weight (lbs.)	0.2



Shipping Dimensions (hwd / cm)	21.41 x 16.51 x 5.59
Shipping Dimensions (hwd / in.)	8.43 x 6.50 x 2.20
Shipping Weight (kg)	0.82
Shipping Weight (lbs.)	1.80
Transmitter Unit Dimensions (hwd / cm.)	2.6 x 9.2 x 6.4
Transmitter Unit Dimensions (hwd / in.)	1 x 3.6 x 2.5
Transmitter Unit Weight (kg)	0.09
Transmitter Unit Weight (lbs.)	0.2
Unit Packaging Type	Box
Housing	Metal
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 °F (0 to 40 °C)
Storage Temperature Range	5 to 122 °F (-15 to 50 °C)
Relative Humidity	0% to 85%, Non-Condensing
COMMUNICATIONS	
Signal Range (ft.)	125
Signal Range (m)	38
EDID Compatible	Yes
IR Remote Extension Support	Yes
Consumer Electronics Control (CEC) Supported	Yes
USB Extension Support	No
CONNECTIONS	
Side A - Connector 1	(2) HDMI (FEMALE)
Side A - Connector 2	(2) 3.5MM (FEMALE); RJ45 (FEMALE)
Side B - Connector 1	HDMI (FEMALE)
Side B - Connector 2	3.5MM (FEMALE); RJ45 (FEMALE)
FEATURES & SPECIFICATIONS	
HDCP Specification	1.4
Driver Required	No
Recommended Category Cable	Cat5/Cat5e/Cat6 Cables
Built-In Equalizer	Yes



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

STANDARDS & COMPLIANCE	
Certifications	Tested to FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>