


The industry's first wireless tabletop conference phone. MAX Wireless provides the flexibility to hold a conference call when and where it's most convenient – with no cables in the way. MAX Wireless is a perfect fit for offices and small conference rooms, and delivers outstanding audio clarity.



## Applications



Executive Office  
Small Office/Home Office  
Small Conference Room  
Any room without a phone line

## Features



### Superior Audio Performance

- + High-quality full duplex sound enables participants to speak and listen at the same time without sound cutting in and out
- + Distributed Echo Cancellation® effectively eliminates echo
- + Noise cancellation removes background noises from fans, HVAC systems, lights, projectors, etc.
- + Automatic level controls keep participants' audio balanced and consistent
- + First-mic priority eliminates hollow "tunnel" sound by activating only the microphone closest to the person speaking
- + Three microphones provide 360° audio pickup

### Wireless Capabilities


- + Turn any room into a conference room, even one without a phone line
- + Wireless signal range allows use in multiple rooms without moving the base unit
- + Wireless design provides a clean look with no wires on the table or floor
- + 12 hours of talk time allows for lengthy conferences without recharging; 36 hours of standby time reduces recharging frequency; automatic power-save mode conserves battery life
- + Dual-function power supply/charger enables conferencing while charging
- + Digital spread spectrum technology with 64-bit encryption ensures secure conferencing
- + Audible warnings sound when phone is out of range or needs charging
- + Phone paging button allows easy identification of phone's location

### Ease of Use & Control

- + Simple plug-and-play functionality makes installation and configuration a snap
- + Field upgradeable for easy access to latest features
- + Selectable ring tones

## COMPONENTS

**MAX Wireless** is a single conference phone that connects wirelessly to a base unit for use in any small room.



## Functional Specifications

### Echo Cancellation

Tail time: 60 ms x 3

### Noise Cancellation

Dynamic noise cancellation

### Telephone Connection

Analog PBX or PSTN line  
RJ-11C, -12 dBm nominal

### Radio

Standard DECT/DECT 6.0 (NA, Canada, LATAM)  
WDCT (EMEA, APAC)  
ETSI EN 300 175 1-9

### Keypad

Alphanumeric standard keypad

### Loudspeaker

Volume: 90 dBspl A weighted @ 1 ft  
Bandwidth: 200 Hz–3.3 kHz

### Record Output

Connector: 2.5 mm mono audio jack  
Impedance: < 1000 ohms  
Bandwidth: 200 Hz–3.3 kHz  
Dynamic range: 60 dB  
THD < .01%

### Certifications

FCC part 15/ICES-003 Class A  
FCC part 15 Subpart C/RSS-210  
FCC part 68/IC CS-03  
CE  
UL Certified

### Power

Phone unit:  
Custom battery pack with nickel metal hydride  
batteries, 7.2 V 2200 mAh  
12 hours continuous talk time (typical)  
36 hours standby  
Base unit:  
Auto-adjusting power module;  
100-240 VAC; 50/60Hz

### Wireless Range

DECT: 300 ft to 400 ft (91-121 m)  
EU WDCT unit: 50 ft (15 m)  
Note: these ranges depend on environmental  
factors and may vary. The EU unit has a shorter  
range due to regulatory restrictions on power  
output in the 2.4 GHz frequency band in the  
EU.

### Environmental

Operating temperature: 32–118° F (0–48° C)  
Storage temperature: 41–158° F (5–70° C)  
Operating humidity: 15 to 80%  
Storage humidity: 10 to 90%

### Dimensions (W x D x H)

Phone unit: 10.5" x 10.5" x 3"  
(26.7 cm x 26.7 cm x 7.6 cm)  
Base unit: 4.25" x 5.5" x 2.5"  
(10.8 cm x 14 cm x 6.4 cm)

### Weight

Phone unit: 2.7 lb (1.2 kg)  
Base unit: .6 lb (0.27 kg)  
Shipping:  
MAX Wireless  
10 lb (4.5 kg)

### MAX Wireless Includes

Wireless phone unit (1)  
Base unit (1)  
Battery pack (1)  
Power supply/charger (1)  
Power supply retainer (1)  
Telephone cable  
Documentation CD  
Quick start guide

### Part Numbers

910-158-600 (NA, Canada, LATAM)  
910-158-276 (EMEA)  
910-158-406 (Singapore/HK)

## ClearOne Contacts

### North America

Tel: 801-975-7200  
Toll Free: 800-945-7730  
Sales: 800-707-6994  
Fax: 801-977-0087  
sales@clearone.com

### Europe & Oceania

Tel: +44 (0) 1189 036 053  
global@clearone.com

### Asia Pacific

Tel: +852 3590 4526  
global@clearone.com

### Latin America

Tel: 801-974-3621  
global@clearone.com

### Middle East

Tel: +852 3590 4526  
global@clearone.com

Other product names may be registered trademarks of their respective owners who do not necessarily endorse ClearOne or ClearOne's products.  
All rights reserved. Information in this document subject to change without notice. © 2013 ClearOne. 802-158-000 Revision 2.2 July 2013.