HSM Pure 420

Personal / small office shredder

Made for everyday use





- Made for everyday office use by 1 to 6 users
- High quality materials and "Made in Germany" quality for security and durability
- · Cutting rollers made of hardened steel with lifetime warranty
- Powerful motor allows for continuous operation
- Quiet operation minimizes noise development in the workplace
- · Low power consumption in standby mode
- Paper feed with overload protection reduces paper jams
- Automatically switches off if pressure is applied to the safety element
- Light barrier for automatic start/stop
- Mobile on castors
- Removable waste container for effortless emptying
- Separate collecting bag for the sorted separation of the shredder material
- · Level indicator through inspection window
- Timeless machine design in trendy white
- Optional automatic external oiler for cross cut ensures long time cutting performance and quality
- Uses a 11 gallon capacity shred bag; Part #HSM1310













HSM Part#	HSM2341	HSM2343
Cutting type	Strip cut	Cross cut
Cutting size	1/4"	3/16" x 11/8"
Security level DIN 32757-1	2	3
Security level DIN 66399	P-2 / O-2 / T-2 / E-2	P-4 / O-3 / T-4 / E-3 / F-1
Cutting capacity per run in sheets	22 - 24	14 - 16
Cutting Speed	12.8 ft / min	12.8 ft / min
Throat opening	9.5"	9.5"
Motor power (horsepower)	0.67 hp	0.67 hp
Voltage	115 V / 60Hz	115 V / 60Hz
Dimensions (H x W x D)	24.5" x 15.6" x 11.5"	24.5" x 15.6" x 11.5"
Weight	39.6 lbs	45 lbs
Shred-bin volume	9.2 gal	9.2 gal
Cutting capabilities	j)@h=()	

All technical specifications are approximate values. Technical and design modifications reserved.

Great Products, Great People.