

## iQ300

### WM14N190GB

#### Front loading automatic washing machine



**A+++**

iSensoric Washing Machine with iQDrive for highly effective and efficient laundry care.

- ✓ Intelligent, durable and quiet iQdrive motor with 10-year warranty for highly effective and efficient laundry care.
- ✓ With the option speedPerfect, get perfect washing results in up to 65% less time.
- ✓ A+++ -10%: washes 10% more efficient than the requirement for energy efficiency class A+++.
- ✓ High-grade stainless steel drum for 1-7 kg loads.
- ✓ Textile guard re-proofing programme for gentle waterproofing of outdoor textiles.

#### Features

##### Technical Data

Installation type : Freestanding  
 Height of removable worktop (mm) : 850  
 Dimensions of the product (mm) : 848 x 598 x 550  
 Net weight (kg) : 68.0  
 Connection rating (W) : 2300  
 Current (A) : 10  
 Nominal power (kW) : 220-240  
 Frequency (Hz) : 50  
 Approval certificates : CE, VDE  
 Length of electrical supply cord (cm) : 210  
 Washing performance class : A  
 Door opening : Left  
 Wheels : No  
 EAN code : 4242003802298  
 Capacity (kg) : 7.0  
 Energy efficiency : A+++: exceptionally efficient  
 Energy consumption annual (kWh/annum) - NEW (2010/30/EC) : 157  
 Power consumption in off-mode (W) - NEW (2010/30/EC) : 0.12  
 Power consumption in left-on mode - NEW (2010/30/EC) : 0.50  
 Water consumption annual (l/annum) - NEW (2010/30/EC) : 9020  
 Spin drying performance class : B  
 Max. spin speed (rpm) : 1390  
 Average washing time cotton 40C (partial load) - NEW (2010/30/EC) : 200  
 Average washing time cotton 60C (full load) (min) - NEW (2010/30/EC) : 200  
 Average washing time cotton 60C (partial load) - NEW (2010/30/EC) : 200  
 Duration of the left-on mode - NEW (2012/30/EC) (min) : 15  
 Noise level washing (dB) : 54  
 Noise level spinning (dB) : 75  
 Installation type : Freestanding



4 242003 802298

#### Optional accessories

WZ20490	Platform with pull-out
WZ10130	Extension for cold water inlet /Aquastop
WX975600	Floor securing component

## iQ300

### WM14N190GB

#### Front loading automatic washing machine

Features	
<ul style="list-style-type: none"><li>• iSensoric, Extraklasse</li></ul> <p><b>Performance</b></p> <ul style="list-style-type: none"><li>• Energy efficiency class: A+++</li><li>• Capacity: 7 kg</li><li>• Maximum spin speed: 1400 rpm</li><li>• B spin class</li><li>• Energy consumption :157 kWh per year, based on 220 standard washing cycles</li><li>• -10% more economical (157kWh/year) than the standard value (217 kWh/year)</li><li>• Energy consumption: standard 60 °C cotton programme 0.85 kWh full load and 0.69 kWh partial load and 40 °C cotton programme 0.51 kWh partial load</li><li>• Water consumption 9020 litres per year, based on 220 standard washing cycles</li><li>• Cottons 60 Eco and Cottons 40 Eco are the standard washing programmes to which the information in the label relates. These programmes are suitable to clean normally soiled cotton laundry and are the most efficient programmes in terms of combined energy and water consumption.</li><li>• Programme time:60 °C cotton programme 200 min at full load 200 min at partial load and 40 °C cotton programme 200 min partial load</li><li>• Duration of the left-on mode: 15 min</li><li>• Drum volume: 65 litres</li><li>• Weighted power consumption off-mode / left-on mode: 0.12 W / 0.5 W</li><li>• Noise level washing : 54dB (A) re 1pW: Noise level spinning:75dB (A) re 1 pW</li><li>• Noise level spinning:75dB (A) re 1 pW:</li></ul> <p><b>Programmes/functions</b></p> <ul style="list-style-type: none"><li>• Fully electronic control dial for wash programmes, temperature and special programmes</li><li>• Special programmes: Rapid 60, Dark Wash, textile guard re-proofing programme, shirts/blouses, mixed fabrics, hygiene, rapid 15 minute quick wash, Duvet, drum clean with reminder, Standard cold - 40°C, delicates</li><li>• Touch control buttons: start/pause with reload function, spin speed selection, temperature selection, Water &amp; Rinse Plus, speedPerfect/ecoPerfect and 24 hours time delay</li></ul> <p><b>Key features</b></p> <ul style="list-style-type: none"><li>• varioPerfect: speed or energy efficiency with perfect wash performance every time</li><li>• antiVibration Design - for more stability and quietness</li><li>• Reload function: Pause the already running washing machine to add any forgotten items of laundry to the drum.</li></ul>	<p><b>Additional features</b></p> <ul style="list-style-type: none"><li>• iQ Drive</li><li>• Large display for programme progress indication, temperature, spin speed, remaining time, 24 hours end time delay and load recommendation</li><li>• Time delay 24 hours and time remaining indicator</li><li>• autoLoad</li><li>• Multiple water protection</li><li>• Electronic child safety package</li><li>• Foam detection system</li><li>• Out of balance load adjustment</li></ul> <p><b>Technical Information</b></p> <ul style="list-style-type: none"><li>• Dimensions (H X W X D): 84.8 x 59.8 x 55 cm</li><li>• Slide-under installation</li><li>• integrated 32 cm porthole, silver-white with 180° opening door</li></ul>

**iQ300**  
**WM14N190GB**  
**Front loading automatic washing  
machine**

Dimensioned drawings

