

W544BX0GB

AUTOMATIC WASHING MACHINE

FULLY INTEGRABLE

A+++


The extraordinarily quiet and durable built-in washing machine with an 8 kg load capacity, special short cycles and stain removal programmes and projection of time remaining.

- ✓ TimeLight – the time remaining in the programme is projected onto the floor.
- ✓ Special stain removal programmes specifically target grease, tomato and red wine stains.
- ✓ Silence – the programme that runs especially quietly. Ideal for easy-care laundry.
- ✓ Powerful, intelligent, very quiet EcoSilence Drive motor with 10-year-warranty.
- ✓ Even 30% better than an appliance with top energy efficiency.

Features

Technical Data

Construction type : Built-in
Height of removable worktop (mm) : 820
Dimensions of the product (mm) : 818 x 596 x 574
Net weight (kg) : 76.0
Connection rating (W) : 2300
Current (A) : 10
Voltage (V) : 220-240
Frequency (Hz) : 50
Approval certificates : CE, VDE
Length of electrical supply cord (cm) : 225
Washing performance class : A
Door hinge : Left
Wheels : No
EAN code : 4242004212843
Capacity cotton (kg) - NEW (2010/30/EC) : 8.0
Energy efficiency class - NEW (2010/30/EC) : A+++
Energy consumption annual (kWh/annum) - NEW (2010/30/EC) : 137
Power consumption in off-mode (W) - NEW (2010/30/EC) : 0.12
Power consumption in left-on mode - NEW (2010/30/EC) : 0.50
Water consumption annual (l/annum) - NEW (2010/30/EC) : 9900
Spin drying performance class : B
Maximum spin speed (rpm) - NEW (2010/30/EC) : 1355
Average washing time cotton 40C (partial load) - NEW (2010/30/EC) : 255
Average washing time cotton 60C (full load) (min) - NEW (2010/30/EC) : 270
Average washing time cotton 60C (partial load) - NEW (2010/30/EC) : 270
Noise level washing (dB(A) re 1 pW) : 41 dB
Noise level spinning (dB(A) re 1 pW) : 67 dB
Installation type : Full-integrated



4 242004 212843

Optional accessories

Z7060X1 Height-adjustable feet
Z7070X0 Accessory
Z7080X0 Accessory

W544BX0GB

AUTOMATIC WASHING MACHINE

FULLY INTEGRATABLE

Features

Performance

- Capacity: 8 kg
- Energy efficiency class: A+++
- Maximum spin speed: 1400 rpm
- Energy consumption :137 kWh per year, based on 220 standard washing cycles
- Energy consumption: standard 60 °C cotton programme 0.78 kWh full load and 0.58 kWh partial load and 40 °C cotton programme 0.38 kWh partial load
- Weighted power consumption off-mode / left-on mode: 0.12 W / 0.5 W
- Water consumption 9900 litres per year, based on 220 standard washing cycles
- B spin class
- Cottons 60 Eco and Cottons 40 Eco are the standard washing programmes to which the information in the label relates. These programmes are suitable to clean normally soiled cotton laundry and are the most efficient programmes in terms of combined energy and water consumption.
- Programme time:60 °C cotton programme 270 min at full load 270 min at partial load and 40 °C cotton programme 255 min partial load
- Noise level washing : 41 DBdB (A) re 1pW: Noise level spinning:67 DBdB (A) re 1 pW
- Noise level spinning:67 DBdB (A) re 1 pW:

Programmes/functions

- Special programmes: Dark wash, Shirts, Stain - butter/oil, Stain - Red wine, Stain - Tomatoes, Mixed Load, Rapid 15 min / Rapid 30 min, Silent Night wash, Drum clean with reminder, rinse/spin/drain, Delicates/Silk

Key features

- FlexPerfect - actively choose between either saving energy or time
- Touch control buttons: Less Ironing, Time Delay, Temperature, start/pause with reload function, EcoPerfect, SpeedPerfect, Extra Rinse, Spin speed reduction

Additional features

- TimeLight – The time remaining in the program is projected onto the floor.
- Reload Function – lets you add items even after the programme has started.
- Large display for programme progress indication, temperature, spin speed, remaining time, 24 hours end time delay and load recommendation
- EcoSilence Drive
- EcoSilence drive with 10 year warranty
- Aquastop with guarantee
- Intelligent Water System - optimised water consumption during washing cycle
- Foam detection system
- DrumClean with reminder function
- Safeguard monitoring system adjusts load distribution
- package
- Divider for Liquid Detergent
- Buzzer to indicate the end of cycle
- Large white door with 130° opening and 30 cm porthole
- Furniture door is reversible
- Metal door catch

Technical Information

- Continuous automatic load adjustment system
- adjustable base height: 15 cm
- adjustable base depth: 6.5 cm
- Dimensions (H X W X D): 81.8 x 59.6 x 57.4 cm
- Height adjustment with Cardan drive

W544BX0GB
AUTOMATIC WASHING MACHINE
FULLY INTEGRABLE

Dimensioned drawings

