


HD-TVI 2MP IR Dome Camera

VLD1TW 2.8-12mm auto iris varifocal lens, white housing

Features

- Full HD resolution over coax (HD-TVI)
- 30 built-in IR LEDs
- Supports up to Full HD 1080p @ 30 fps
- 3 axis lens mount
- Adapter plate for optional accessories included
- Additional BNC output for 960H analog
- Signal distance up to 1600 ft.¹
- 12VDC operation (power supply not included)
- IP66 compliant, weather resistant
- 5 year warranty²



Specifications

Image Sensor	1/3" 2MP CMOS
Resolution.....	1080p / 720p
Minimum Illumination.....	0 lux (IR on)
S/N Ratio	more than 52dB
Motion Detection.....	Yes
Day/Night.....	IR-cut filter
DNR.....	2D/3D Automatic
Number of IR LEDs	30
IR Range	100' (depending on scene reflection)
Power Supply	12VDC (power supply not included)
Power Consumption	400mA (IR on)
Operating Temperature.....	-4° F - 104° F
Weight	2.1 lbs.
Dimensions.....	5.7" (Dia.) x 4.5" (H)

Optional Accessories



O4JBD
Junction Box



PSW5
12VDC
Power Supply

¹To preserve signal quality and distance, Speco Technologies recommends using coax with a 100% copper center conductor and at least 95% braided copper shield.

²Effective on all new purchases as of 2/1/17. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 3/6/17