


S513M60X0G BLACK DISHWASHER, 60CM ENERGY EFFICIENT DISHWASHER, 60CM FULLY INTEGRATED


A⁺⁺


The dishwasher with cutlery drawer that's flexible to load and displays the time remaining.

- ✓ Flex 2 baskets and cutlery drawer with many adaptable, foldable elements for convenient loading
- ✓ TimeLight – the time remaining in the programme is projected onto the floor
- ✓ Chef 70° – the pro programme for getting stubborn dirt off pots and casserole dishes
- ✓ Quiet dishwashing at just 46 dB
- ✓ Energy efficiency class A++ for very low consumption

Features

Technical Data

Cleaning performance : A
Water consumption (l) : 9.5
Total annual energy consumption (kWh) 220 days : 205
Total annual water consumption (l) 220 days : 2090
Construction type : Built-in
Removable work top : No
Door panel options : Not possible
Height of removable worktop (mm) : 815
Height of the product (mm) : 815
Adjustable feet : Yes - front only
Maximum adjustability feet (mm) : 60
Adjustable plinth : both horizontal and vertical
Net weight (kg) : 34.0
Gross weight (kg) : 37.0
Connection rating (W) : 2400
Current (A) : 13
Voltage (V) : 220-240
Frequency (Hz) : 60; 50
Length of electrical supply cord (cm) : 175
Plug type : GB plug
Length inlet hose (cm) : 165
Length outlet hose (cm) : 190
Hidden heating element : Yes
Water protection system description : Triple water protection 24h : Childlock appliance
Water softener (kWh) : Yes
Adjustable upper basket : Rackmatic 3-stage
Cup Shelf : 2
3rd Rack : 3rd Rack 1.0
Silverware Basket : Standard
Optional accessories : Z7710X0, Z7860X0, Z7860X3, Z7863X1, Z7863X3, Z7880X0
Included accessories 2 : baking-sheet spray head grey, vapor barrier plate
Number of place settings : 14
Brand : Neff
Product name / Commercial code : S513M60X0G
Number of place settings : 14
Energy efficiency class - NEW (2010/30/EC) : A++
Energy consumption annual (kWh/annum) - NEW (2010/30/EC) : 266
Energy consumption (kWh) : 0.93
Power consumption in left-on mode (W) - NEW (2010/30/EC) : 0.10
Power consumption in off-mode (W) - NEW (2010/30/EC) : 0.10
Water consumption annual (l/annum) - NEW (2010/30/EC) : 2660
Drying performance : A
Reference programme : Eco
Total cycle time of reference programme (min) : 210
Duration of the left-on mode - NEW (2012/30/EC) (min) : 0
Noise level (dB(A) re 1 pW) : 46
Installation type : Full-integrated
Panel ready : Yes
Control type : Touch (M) - 3/32

S513M60X0G BLACK DISHWASHER, 60CM ENERGY EFFICIENT DISHWASHER, 60CM FULLY INTEGRATED

Features

Performance

- Energy Efficiency Class: A++
- Capacity: 14 place settings
- Energy consumption in Eco 50 programme: 266 Kwh per year, based on 280 standard cleaning cycles
- Energy consumption in Eco 50 programme: 0.93 Kwh
- Water consumption in Eco 50 programme: 9.5 litres
- Water consumption in Eco 50 programme: 2660 litres per year, based on 280 standard cleaning cycles
- Programme time in Eco 50 programme: 210 minutes
- Noise level dB (A) re 1pW: 46 dB

Programmes/functions

- 6 programmes: Chef 70 °C, Auto 45-65 °C, Eco 50 °C, Glass 40 °C, 1 hour 65 °C, Pre rinse
- 5 cleaning temperatures
- 3 special options: VarioSpeedPlus, HygienePlus, Extra Dry
- Machine Care

Flexible design elements

- Flex 2 basket system
- Variodrawer on third level
- 3 stage Rackmatic height-adjustable top basket
- Silver coloured baskets with handle, with coloured TouchPoints
- 2 foldable plate racks in top basket
- 4 foldable plate racks in bottom basket, 2 foldable cup racks in bottom basket
- 2 foldable cup shelves in top basket 2 foldable cup racks in bottom basket

Innovations and technology

- Neff EfficientSilentDrive
- NeffSparkle - glass care system
- Heat exchanger - Hygienic and efficient drying
- Efficient SilentDrive BLDC motor
- Curved spray arms
- DosageAssist detergent dispenser
- DetergentAware
- AquaSensor®, Load sensor
- Neff AquaStop® with guarantee

Design features

- White TimeLight projection on floor
- Colour of indicators: Red LED indicators
- Large item spray head, including Steam protection plate
- Stainless steel interior
- Push button top controls
- LED salt refill indicator, LED rinse-aid refill indicator
- Alternating spray arms
- Regenerative electronics
- Self-cleaning filter system with 3 piece corrugated filter
- Childproof Door lock
- Time delay (1-24 hours) with Acoustic end of cycle indicator, water fault indicator
- Acoustic end of cycle indicator
- Dimensions (HxWxD): 81.5 x 59.8 x 55cm
- Efficiency information relates to the Eco 50 programme. This programme is suitable for cleaning normally soiled tableware and is the most efficient programme in terms of combined energy and water consumption.

S513M60X0G BLACK
DISHWASHER, 60CM
ENERGY EFFICIENT DISHWASHER, 60CM
FULLY INTEGRATED

Dimensioned drawings

