

ZDT24003FA Dishwasher



Features :

- Energy efficiency (2010/30/EC): A+
- Installation: FI
- Loading capacity: 13 IEC settings
- Noise level: only 47 (dB(A) re 1 pW) (2010/30/EC)
- Water and energy consumption: 11 l, 1.039 kWh for program Eco 50
- Glass protection program
- 5 programmes, 4 temperatures
- Dishwasher programmes: AUTO Wash 45°-70°, Eco 50°, Glass 45°, Intensive 70°, Quick Wash 60°
- Panel with symbols
- Warm water connection up to 60°C
- Delay start options: 3h/6h/9h
- Fuzzy logic detects the load and adjusts water en energy consumption
- Water sensor detects the level of dirt and adjusts water consumption
- Indication for salt refill
- Height adjustable upper basket, even when fully loaded
- Upper basket with Foldable cup shelves
- Lower basket with 2 foldable plate racks
- Cutlery basket
- Aquastop System
- Built-in H(min/max)xWxD (mm): 820 / 880 x 600 x 550
- Automatic door opener

Technical Specs :

- Product Installation : Built_In
- Product Typology : Full_Width(60cm)
- Product Classification : Core
- Installation : FI
- Cabinet type of : 60 FI
- Panel colour : Black
- Door colour : None
- Side walls colour : Rough zinc coated
- Type of timer min. : EDW1103
- Push button functions : Delay start, On/off, Program selection
- Knob/Command functionality : None
- Programmes number of : 5
- Number of temperatures : 4
- Dishwasher programs : AUTO Wash 45°-70°, Eco 50°, Glass 45°, Intensive 70°, Quick Wash 60°
- Indicator programme : LED
- Indicators display : None
- Indicators other : Buzzer, Delay start 3h/6h/9h, End, Program selected, Salt, XtraDry
- Height total : 818
- Width mm : 596
- Depth mm : 555
- Tub material : Stainless steel
- Heating element type of : Interheater
- Inlet hose type of : Aqua control
- Inlet hose length : 150
- Water supply : Cold or hot
- Anti-flood device : Floating switch
- Drying system : AirDry Technology
- Softening regulation : 10 steps
- Top spraying level : None
- Lower spray arm : Standard
- Flat filter material : Stainless steel
- Frequency : 50/60
- Voltage : 200-240
- Connected load (W) : 1550-2200
- Required fuse (A) : 10

Product Description :

Zanussi911 535 205